

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929318

Luminaire Tested: DFN2DIP-HX4F0-080D120US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929318
REPORT IS A COMBINATION OF REPORTS P900972 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D120US940-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16662.5 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 172.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929318

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929318

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2193	2193	2193
5°	2197	2158	2172
10°	2175	2116	2102
15°	2145	2047	1992
20°	2106	1950	1858
25°	2066	1842	1729
30°	2011	1732	1565
35°	1958	1613	1421
40°	1904	1490	1255
45°	1841	1353	1105
50°	1776	1215	959
55°	1708	1068	818
60°	1630	913	674
65°	1539	757	606
70°	1430	610	549
75°	1293	538	500
80°	1094	452	434
85°	765	303	327

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1856 cd/sqm

TEST NUMBER: P929318

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.4	1.7
10°-20°	758.8	4.6
20°-30°	1065.3	6.4
30°-40°	1161.3	7.0
40°-50°	1067.3	6.4
50°-60°	838.3	5.0
60°-70°	545.6	3.3
70°-80°	280.9	1.7
80°-90°	78.1	0.5
90°-100°	119.1	0.7
100°-110°	444.1	2.7
110°-120°	1177.7	7.1
120°-130°	1953.3	11.7
130°-140°	2074.9	12.5
140°-150°	1928.4	11.6
150°-160°	1550.3	9.3
160°-170°	999.0	6.0
170°-180°	343.8	2.1
0°-30°	2100.6	12.6
0°-40°	3261.8	19.6
0°-60°	5167.4	31.0
0°-90°	6072.0	36.4
90°-120°	1740.9	10.4
90°-150°	7697.4	46.2
90°-180°	10591.0	63.6
0°-180°	16662.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2949	2949	2949	2949	2949	
5°	2949	2936	2901	2925	2917	280
15°	2805	2776	2685	2634	2608	790
25°	2546	2461	2285	2175	2135	1171
35°	2194	2058	1823	1655	1596	1373
45°	1794	1615	1335	1145	1081	1385
55°	1364	1156	867	707	657	1219
65°	921	704	464	374	366	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	2	31	52	66	70	16
95°	170	84	102	115	112	201
105°	795	873	160	188	199	849
115°	1503	1547	1613	403	214	1480
125°	2125	2159	2209	2227	2235	1895
135°	2630	2672	2695	2721	2716	2031
145°	3051	3048	3092	3111	3098	1908
155°	3359	3336	3367	3382	3362	1548
165°	3539	3524	3531	3550	3531	1000
175°	3620	3602	3607	3626	3599	345
180°	3612	3612	3612	3612	3612	

TEST NUMBER: P929318

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2949.3	2949.3	2949.3	2949.3	2949.3
2.5°	2962.6	2949.3	2919.9	2946.7	2941.4
5°	2949.3	2936.0	2901.1	2925.2	2917.3
7.5°	2925.2	2909.3	2872.0	2882.5	2869.1
10°	2893.2	2874.6	2821.3	2813.1	2797.2
12.5°	2853.3	2829.2	2757.0	2741.1	2711.7
15°	2805.2	2775.7	2685.1	2634.4	2607.8
17.5°	2749.1	2706.3	2594.2	2535.6	2492.8
20°	2685.1	2631.6	2498.2	2431.7	2372.7
22.5°	2615.7	2554.2	2399.4	2308.8	2268.8
25°	2546.3	2460.8	2284.7	2175.4	2135.2
27.5°	2463.6	2372.7	2177.9	2052.5	1991.0
30°	2375.6	2273.9	2060.4	1924.5	1852.2
32.5°	2290.0	2167.2	1948.6	1788.3	1721.5
35°	2194.1	2057.8	1823.1	1654.9	1596.0
37.5°	2100.6	1953.7	1705.6	1521.2	1454.7
40°	2001.8	1841.8	1582.7	1393.2	1323.8
42.5°	1900.4	1729.7	1460.0	1262.4	1195.8
45°	1793.6	1614.7	1334.6	1144.9	1080.9
47.5°	1692.3	1502.8	1214.5	1024.8	966.2
50°	1580.1	1390.7	1097.1	912.7	856.9
52.5°	1470.6	1270.3	984.9	808.8	758.1
55°	1363.8	1155.7	867.4	707.4	656.7
57.5°	1254.5	1041.0	763.5	614.0	571.1
60°	1142.3	928.8	653.8	517.9	475.2
62.5°	1033.0	819.5	560.4	432.4	411.2
65°	920.9	704.5	464.4	373.8	365.5
67.5°	814.1	597.8	373.8	328.2	320.3
70°	702.0	493.9	309.5	282.9	272.1
72.5°	595.2	397.6	258.9	237.6	232.2
75°	491.0	304.2	213.5	194.8	192.3
77.5°	387.1	216.0	168.2	157.4	152.1
80°	290.8	154.9	128.0	117.5	117.5
82.5°	202.8	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.7	50.7	50.7
87.5°	42.7	21.2	21.2	18.7	18.7
90°	2.5	31.3	52.2	65.5	70.5
92.5°	65.5	54.9	62.7	68.0	70.5
95°	169.7	83.5	101.8	115.2	112.4
97.5°	305.8	91.6	133.2	141.2	143.7
100°	462.8	104.6	149.0	169.7	175.1
102.5°	635.1	630.1	154.2	182.9	190.9
105°	794.6	873.2	159.6	188.1	198.6
107.5°	980.2	1045.4	164.8	193.4	203.9
110°	1158.1	1212.8	457.5	196.2	206.4

TEST NUMBER: P929318

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1325.4	1372.3	1327.9	201.1	209.2
115°	1502.9	1547.4	1612.8	402.6	214.5
117.5°	1657.2	1709.4	1754.1	1380.0	695.3
120°	1829.8	1868.9	1916.1	1947.5	1594.5
122.5°	1976.0	2018.0	2070.4	2085.9	2088.7
125°	2125.0	2159.2	2208.9	2227.1	2234.9
127.5°	2261.0	2297.6	2337.0	2363.1	2365.6
130°	2389.1	2431.1	2459.6	2488.5	2486.0
132.5°	2519.8	2554.0	2582.5	2606.2	2603.7
135°	2629.7	2671.6	2694.9	2721.3	2716.1
137.5°	2744.6	2775.9	2802.3	2828.4	2820.6
140°	2857.0	2878.0	2906.6	2930.2	2917.2
142.5°	2951.3	2969.6	3003.5	3024.2	3011.2
145°	3050.6	3047.9	3092.2	3110.6	3097.5
147.5°	3136.6	3128.9	3173.3	3186.3	3176.1
150°	3220.4	3202.1	3244.0	3259.5	3246.5
152.5°	3290.9	3270.1	3309.2	3325.0	3306.7
155°	3358.8	3335.5	3366.9	3382.5	3361.7
157.5°	3413.8	3393.0	3416.6	3434.9	3413.8
160°	3461.0	3445.2	3461.0	3476.5	3458.2
162.5°	3502.6	3487.1	3500.1	3518.4	3494.9
165°	3539.2	3523.7	3531.4	3549.8	3531.4
167.5°	3568.1	3552.2	3560.3	3578.6	3555.1
170°	3591.6	3575.8	3581.1	3599.4	3575.8
172.5°	3607.2	3591.6	3597.0	3615.3	3591.6
175°	3620.2	3601.9	3607.2	3625.5	3599.4
177.5°	3625.5	3607.2	3610.0	3628.3	3604.8
180°	3612.5	3612.5	3612.5	3612.5	3612.5

TEST NUMBER: P929318

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.46	9.19	9.53	10.26	11.72	4.43	5.17	5.51	6.23	7.69
	3H	10.13	10.79	11.21	11.86	13.34	5.62	6.27	6.70	7.35	8.82
	4H	10.74	11.36	11.83	12.43	13.91	6.06	6.68	7.16	7.76	9.24
	6H	11.15	11.72	12.25	12.81	14.30	6.38	6.95	7.48	8.03	9.52
	8H	11.28	11.82	12.38	12.92	14.40	6.47	7.01	7.57	8.11	9.59
	12H	11.34	11.85	12.45	12.94	14.45	6.51	7.03	7.62	8.12	9.63
4H	2H	8.47	9.09	9.57	10.17	11.65	5.02	5.64	6.12	6.72	8.20
	3H	10.29	10.80	11.39	11.91	13.40	6.36	6.88	7.47	7.98	9.47
	4H	10.98	11.45	12.09	12.55	14.06	6.91	7.38	8.02	8.48	9.99
	6H	11.49	11.89	12.61	13.01	14.52	7.32	7.73	8.44	8.85	10.35
	8H	11.66	12.04	12.78	13.15	14.67	7.45	7.83	8.57	8.94	10.46
	12H	11.75	12.10	12.89	13.22	14.74	7.51	7.85	8.64	8.98	10.50
8H	4H	10.94	11.32	12.05	12.43	13.95	7.18	7.56	8.30	8.67	10.19
	6H	11.50	11.81	12.64	12.97	14.48	7.70	8.01	8.83	9.16	10.68
	8H	11.72	11.99	12.86	13.13	14.66	7.89	8.16	9.03	9.30	10.83
	12H	11.85	12.09	13.00	13.22	14.80	8.01	8.24	9.15	9.37	10.95
12H	4H	10.89	11.23	12.02	12.35	13.88	7.18	7.52	8.31	8.65	10.17
	6H	11.48	11.75	12.62	12.88	14.42	7.75	8.02	8.89	9.15	10.69
	8H	11.69	11.93	12.84	13.06	14.64	7.95	8.19	9.10	9.32	10.90