

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910980

Luminaire Tested: DFN2DIP-HX4F0-100D050US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910980
REPORT IS A COMBINATION OF REPORTS P899329 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D050US850-FLLFL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15886.5 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 128
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910980
CATALOG NUMBER: DFN2DIP-HX4F0-100D050US850-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910980

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69			69
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62	58			58
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52	49			49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41			41
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	35			35
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31			31
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27			27
7	61	48	40	34	58	46	39	33	42	35	31	38	33	29	34	30	26	24			24
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	22			22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21	19			19
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20	18			18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3209	3209	3209
5°	3214	3164	3185
10°	3188	3122	3142
15°	3142	3071	3075
20°	3078	3000	3006
25°	3016	2915	2927
30°	2937	2835	2825
35°	2863	2742	2718
40°	2771	2648	2616
45°	2679	2553	2512
50°	2579	2454	2391
55°	2474	2339	2280
60°	2356	2203	2153
65°	2227	2062	2003
70°	2063	1890	1842
75°	1835	1684	1693
80°	1561	1422	1409
85°	1133	969	937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2679 cd/sqm



TEST NUMBER: P910980

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.1	2.6
10°-20°	1142.7	7.2
20°-30°	1679.4	10.6
30°-40°	1950.5	12.3
40°-50°	1948.1	12.3
50°-60°	1698.7	10.7
60°-70°	1255.7	7.9
70°-80°	710.4	4.5
80°-90°	192.5	1.2
90°-100°	108.5	0.7
100°-110°	344.8	2.2
110°-120°	590.1	3.7
120°-130°	776.0	4.9
130°-140°	871.0	5.5
140°-150°	854.2	5.4
150°-160°	716.5	4.5
160°-170°	475.2	3.0
170°-180°	166.1	1.0
0°-30°	3228.3	20.3
0°-40°	5178.7	32.6
0°-60°	8825.5	55.6
0°-90°	10984.1	69.1
90°-120°	1043.4	6.6
90°-150°	3544.6	22.3
90°-180°	4902.0	30.9
0°-180°	15886.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4315	4315	4315	4315	4315	
5°	4315	4299	4253	4286	4278	410
15°	4108	4083	4029	4046	4025	1157
25°	3718	3685	3614	3622	3614	1711
35°	3208	3166	3100	3075	3054	2003
45°	2610	2581	2518	2473	2456	2014
55°	1975	1950	1900	1851	1830	1766
65°	1332	1307	1266	1228	1208	1317
75°	697	689	668	643	652	744
85°	170	166	162	149	145	190
90°	2	19	52	49	50	15
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P910980

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4315.2	4315.2	4315.2	4315.2	4315.2
2.5°	4340.3	4319.6	4273.8	4315.2	4307.2
5°	4315.2	4298.9	4253.1	4286.2	4278.2
7.5°	4286.2	4261.4	4215.6	4249.1	4240.8
10°	4240.8	4211.8	4162.0	4195.0	4182.7
12.5°	4178.3	4153.6	4103.9	4124.6	4116.2
15°	4107.8	4083.2	4029.0	4045.7	4025.1
17.5°	4020.7	3996.1	3941.8	3962.6	3941.8
20°	3925.1	3900.5	3842.4	3854.7	3838.4
22.5°	3830.0	3792.7	3738.4	3738.4	3730.1
25°	3717.8	3684.8	3614.3	3622.2	3614.3
27.5°	3593.2	3564.1	3510.4	3498.1	3477.4
30°	3469.1	3435.6	3373.5	3361.2	3344.4
32.5°	3336.1	3311.5	3244.9	3219.9	3203.1
35°	3207.6	3166.2	3099.7	3074.6	3053.9
37.5°	3062.3	3024.8	2958.4	2929.3	2908.6
40°	2913.0	2879.5	2813.1	2776.2	2759.4
42.5°	2767.7	2734.2	2668.3	2626.4	2601.8
45°	2610.1	2581.1	2518.5	2473.2	2456.5
47.5°	2456.5	2427.5	2361.0	2315.1	2290.5
50°	2294.5	2273.8	2215.7	2157.6	2136.9
52.5°	2136.9	2107.9	2054.1	2008.4	1979.3
55°	1975.4	1950.3	1900.5	1850.7	1830.1
57.5°	1813.3	1792.6	1738.5	1688.8	1672.0
60°	1651.3	1635.0	1576.9	1531.1	1518.8
62.5°	1493.7	1464.7	1423.3	1381.9	1365.2
65°	1332.1	1307.1	1265.7	1228.2	1207.6
67.5°	1166.2	1145.0	1108.1	1079.1	1062.3
70°	1012.5	995.8	958.4	929.3	913.0
72.5°	854.9	838.2	817.6	788.5	776.1
75°	696.9	689.0	667.8	643.2	651.5
77.5°	556.1	539.3	530.9	518.6	506.3
80°	415.1	410.8	402.3	390.0	381.7
82.5°	282.2	282.2	278.2	261.5	261.5
85°	169.9	166.0	162.0	149.3	145.3
87.5°	74.9	66.4	58.1	45.8	41.4
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P910980

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P910980
 CATALOG NUMBER: DFN2DIP-HX4F0-100D050US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.93	13.99	13.70	14.79	15.75	12.49	13.56	13.27	14.35	15.32
	3H	14.60	15.56	15.39	16.36	17.36	14.13	15.09	14.92	15.89	16.89
	4H	15.20	16.10	16.00	16.92	17.93	14.73	15.63	15.53	16.44	17.45
	6H	15.61	16.44	16.43	17.27	18.29	15.13	15.97	15.95	16.79	17.81
	8H	15.72	16.52	16.55	17.36	18.38	15.25	16.04	16.07	16.88	17.91
	12H	15.78	16.53	16.61	17.37	18.42	15.30	16.05	16.13	16.89	17.94
4H	2H	13.41	14.32	14.22	15.13	16.14	13.07	13.97	13.88	14.78	15.79
	3H	15.30	16.05	16.12	16.90	17.93	14.90	15.66	15.72	16.51	17.53
	4H	16.02	16.71	16.85	17.55	18.61	15.62	16.30	16.45	17.15	18.20
	6H	16.55	17.14	17.40	18.01	19.07	16.14	16.73	16.99	17.60	18.66
	8H	16.70	17.26	17.56	18.12	19.20	16.29	16.85	17.14	17.71	18.78
	12H	16.79	17.29	17.66	18.17	19.25	16.36	16.86	17.24	17.75	18.83
8H	4H	16.23	16.79	17.09	17.66	18.73	15.87	16.43	16.73	17.29	18.37
	6H	16.88	17.34	17.76	18.24	19.31	16.51	16.97	17.39	17.88	18.95
	8H	17.10	17.51	17.99	18.41	19.50	16.73	17.14	17.62	18.04	19.13
	12H	17.24	17.60	18.14	18.49	19.64	16.86	17.22	17.75	18.11	19.25
12H	4H	16.23	16.73	17.10	17.62	18.69	15.88	16.38	16.75	17.26	18.34
	6H	16.91	17.32	17.80	18.22	19.31	16.56	16.96	17.45	17.87	18.95
	8H	17.16	17.52	18.06	18.41	19.55	16.80	17.16	17.70	18.06	19.20