

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928104

Luminaire Tested: DFN2DIP-HX4F0-110D060US850-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928104
REPORT IS A COMBINATION OF REPORTS P900869 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D060US850-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18664.4 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 156.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928104

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928104

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	39	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3529	3529	3529
5°	3535	3481	3504
10°	3507	3434	3457
15°	3456	3378	3383
20°	3386	3300	3307
25°	3317	3206	3219
30°	3231	3119	3108
35°	3149	3016	2990
40°	3048	2913	2878
45°	2947	2809	2763
50°	2837	2699	2631
55°	2722	2573	2509
60°	2591	2423	2369
65°	2450	2268	2204
70°	2269	2079	2026
75°	2018	1853	1863
80°	1717	1565	1550
85°	1247	1066	1031

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2947 cd/sqm

TEST NUMBER: P928104

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.8	2.4
10°-20°	1257.0	6.7
20°-30°	1847.3	9.9
30°-40°	2145.5	11.5
40°-50°	2142.9	11.5
50°-60°	1868.5	10.0
60°-70°	1381.3	7.4
70°-80°	781.5	4.2
80°-90°	210.2	1.1
90°-100°	74.1	0.4
100°-110°	276.0	1.5
110°-120°	732.1	3.9
120°-130°	1214.2	6.5
130°-140°	1289.8	6.9
140°-150°	1198.7	6.4
150°-160°	963.8	5.2
160°-170°	621.0	3.3
170°-180°	213.7	1.1
0°-30°	3551.1	19.0
0°-40°	5696.6	30.5
0°-60°	9708.0	52.0
0°-90°	12081.0	64.7
90°-120°	1082.2	5.8
90°-150°	4785.0	25.6
90°-180°	6583.0	35.3
0°-180°	18664.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4747	4747	4747	4747	4747	
5°	4747	4729	4678	4715	4706	451
15°	4519	4491	4432	4450	4428	1273
25°	4090	4053	3976	3984	3976	1882
35°	3528	3483	3410	3382	3359	2203
45°	2871	2839	2770	2721	2702	2216
55°	2173	2145	2091	2036	2013	1943
65°	1465	1438	1392	1351	1328	1449
75°	766	758	735	708	717	818
85°	187	182	178	164	160	209
90°	2	20	32	41	44	17
95°	106	52	63	72	70	125
105°	494	543	99	117	124	528
115°	934	962	1003	250	133	920
125°	1321	1342	1373	1384	1389	1178
135°	1635	1661	1675	1692	1688	1263
145°	1896	1895	1922	1934	1926	1186
155°	2088	2074	2093	2103	2090	962
165°	2200	2190	2195	2207	2195	622
175°	2250	2239	2242	2254	2238	214
180°	2246	2246	2246	2246	2246	

TEST NUMBER: P928104

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4746.7	4746.7	4746.7	4746.7	4746.7
2.5°	4774.2	4751.5	4701.2	4746.7	4738.0
5°	4746.7	4728.8	4678.4	4714.7	4706.0
7.5°	4714.7	4687.6	4637.3	4674.1	4664.9
10°	4664.9	4632.8	4578.2	4614.4	4600.9
12.5°	4596.1	4569.0	4514.3	4537.0	4527.8
15°	4518.6	4491.4	4431.9	4450.3	4427.6
17.5°	4422.7	4395.6	4336.1	4358.8	4336.1
20°	4317.7	4290.5	4226.6	4240.2	4222.3
22.5°	4213.1	4171.8	4112.3	4112.3	4103.1
25°	4089.5	4053.3	3975.8	3984.5	3975.8
27.5°	3952.5	3920.5	3861.4	3847.9	3825.2
30°	3816.0	3779.1	3710.8	3697.3	3678.9
32.5°	3669.7	3642.6	3569.4	3541.8	3523.4
35°	3528.3	3482.8	3409.6	3382.0	3359.3
37.5°	3368.5	3327.3	3254.2	3222.2	3199.5
40°	3204.3	3167.5	3094.4	3053.7	3035.3
42.5°	3044.5	3007.7	2935.1	2889.1	2862.0
45°	2871.2	2839.2	2770.4	2720.6	2702.2
47.5°	2702.2	2670.3	2597.1	2546.7	2519.5
50°	2524.0	2501.2	2437.2	2373.4	2350.6
52.5°	2350.6	2318.6	2259.6	2209.1	2177.2
55°	2172.9	2145.2	2090.6	2035.8	2013.1
57.5°	1994.6	1971.9	1912.4	1857.6	1839.2
60°	1816.4	1798.6	1734.6	1684.2	1670.7
62.5°	1643.1	1611.2	1565.6	1520.1	1501.7
65°	1465.3	1437.7	1392.2	1351.1	1328.4
67.5°	1282.8	1259.6	1218.9	1187.0	1168.6
70°	1113.8	1095.4	1054.2	1022.3	1004.3
72.5°	940.4	922.0	899.3	867.3	853.7
75°	766.5	757.9	734.6	707.5	716.7
77.5°	611.6	593.2	584.0	570.5	556.9
80°	456.7	451.8	442.6	429.1	419.9
82.5°	310.4	310.4	306.1	287.7	287.7
85°	187.0	182.5	178.2	164.1	159.8
87.5°	82.3	73.1	63.9	50.3	45.5
90°	1.6	19.5	32.4	40.7	43.8
92.5°	40.7	34.2	38.9	42.3	43.8
95°	105.6	51.9	63.3	71.6	69.9
97.5°	190.1	56.9	82.7	87.8	89.4
100°	287.7	65.0	92.6	105.6	108.8
102.5°	394.8	391.7	95.9	113.7	118.7
105°	493.9	542.7	99.1	116.9	123.5
107.5°	609.4	649.9	102.5	120.2	126.8
110°	720.0	753.9	284.5	122.0	128.3

TEST NUMBER: P928104

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	823.9	853.0	825.4	125.0	130.1
115°	934.3	961.9	1002.6	250.3	133.3
117.5°	1030.2	1062.6	1090.4	857.9	432.2
120°	1137.5	1161.8	1191.2	1210.6	991.2
122.5°	1228.3	1254.4	1287.0	1296.6	1298.4
125°	1321.0	1342.2	1373.1	1384.5	1389.2
127.5°	1405.5	1428.3	1452.8	1469.0	1470.5
130°	1485.2	1511.2	1529.0	1546.9	1545.4
132.5°	1566.5	1587.6	1605.4	1620.0	1618.5
135°	1634.8	1660.8	1675.3	1691.7	1688.3
137.5°	1706.1	1725.6	1742.0	1758.2	1753.4
140°	1776.0	1789.1	1806.9	1821.5	1813.4
142.5°	1834.6	1846.0	1867.1	1880.0	1871.9
145°	1896.4	1894.6	1922.2	1933.7	1925.6
147.5°	1949.8	1945.0	1972.6	1980.7	1974.4
150°	2002.0	1990.5	2016.6	2026.3	2018.2
152.5°	2045.8	2032.8	2057.1	2067.0	2055.5
155°	2088.0	2073.5	2093.0	2102.7	2089.7
157.5°	2122.2	2109.2	2123.8	2135.3	2122.2
160°	2151.5	2141.6	2151.5	2161.1	2149.8
162.5°	2177.3	2167.7	2175.7	2187.2	2172.5
165°	2200.1	2190.5	2195.3	2206.7	2195.3
167.5°	2218.0	2208.2	2213.2	2224.7	2209.9
170°	2232.7	2222.9	2226.2	2237.5	2222.9
172.5°	2242.4	2232.7	2236.0	2247.4	2232.7
175°	2250.5	2239.1	2242.4	2253.7	2237.5
177.5°	2253.7	2242.4	2244.1	2255.5	2240.8
180°	2245.6	2245.6	2245.6	2245.6	2245.6

TEST NUMBER: P928104

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.91	13.92	13.73	14.77	15.81	12.48	13.49	13.30	14.33	15.38
	3H	14.59	15.49	15.42	16.34	17.42	14.11	15.02	14.94	15.87	16.94
	4H	15.18	16.04	16.03	16.90	17.98	14.71	15.56	15.56	16.42	17.51
	6H	15.59	16.38	16.45	17.25	18.34	15.11	15.90	15.97	16.77	17.87
	8H	15.70	16.45	16.57	17.34	18.43	15.22	15.98	16.09	16.86	17.96
	12H	15.75	16.47	16.63	17.35	18.47	15.27	15.99	16.15	16.87	17.99
4H	2H	13.39	14.25	14.25	15.11	16.19	13.05	13.91	13.90	14.76	15.85
	3H	15.27	15.99	16.14	16.88	17.98	14.88	15.60	15.75	16.49	17.59
	4H	15.99	16.65	16.87	17.54	18.66	15.59	16.24	16.47	17.13	18.25
	6H	16.52	17.08	17.41	18.00	19.12	16.11	16.67	17.00	17.59	18.71
	8H	16.67	17.20	17.57	18.11	19.25	16.26	16.79	17.16	17.70	18.84
	12H	16.75	17.23	17.67	18.16	19.30	16.33	16.81	17.25	17.73	18.88
8H	4H	16.20	16.73	17.10	17.64	18.78	15.84	16.37	16.74	17.28	18.42
	6H	16.84	17.28	17.77	18.23	19.37	16.48	16.92	17.40	17.87	19.01
	8H	17.07	17.45	18.00	18.39	19.55	16.70	17.08	17.63	18.02	19.18
	12H	17.21	17.55	18.14	18.48	19.69	16.82	17.16	17.76	18.09	19.30
12H	4H	16.20	16.67	17.11	17.60	18.74	15.84	16.32	16.76	17.25	18.39
	6H	16.87	17.26	17.81	18.20	19.36	16.52	16.91	17.46	17.85	19.01
	8H	17.12	17.47	18.06	18.40	19.61	16.77	17.11	17.70	18.04	19.25