

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911001

Luminaire Tested: DFN2DIP-HX4F0-110D060US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911001
REPORT IS A COMBINATION OF REPORTS P899350 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D060US850-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16258.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 146.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911001

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911001

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	94	90	95	92	88	85	81	78	76	71	69	67	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	40	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3749	3749	3749
5°	3755	3690	3713
10°	3718	3618	3593
15°	3667	3499	3406
20°	3600	3334	3177
25°	3531	3150	2956
30°	3438	2961	2675
35°	3347	2757	2429
40°	3255	2547	2146
45°	3147	2313	1890
50°	3036	2077	1639
55°	2920	1825	1399
60°	2786	1562	1152
65°	2632	1293	1037
70°	2445	1043	939
75°	2210	921	854
80°	1870	773	742
85°	1307	518	559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3147 cd/sqm

TEST NUMBER: P911001

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	2.9
10°-20°	1297.2	8.0
20°-30°	1821.2	11.2
30°-40°	1985.2	12.2
40°-50°	1824.6	11.2
50°-60°	1433.0	8.8
60°-70°	932.7	5.7
70°-80°	480.1	3.0
80°-90°	128.6	0.8
90°-100°	130.2	0.8
100°-110°	413.7	2.5
110°-120°	708.0	4.4
120°-130°	931.2	5.7
130°-140°	1045.3	6.4
140°-150°	1025.0	6.3
150°-160°	859.8	5.3
160°-170°	570.2	3.5
170°-180°	199.3	1.2
0°-30°	3590.9	22.1
0°-40°	5576.1	34.3
0°-60°	8833.7	54.3
0°-90°	10375.1	63.8
90°-120°	1252.0	7.7
90°-150°	4253.5	26.2
90°-180°	5883.0	36.2
0°-180°	16258.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5042	5042	5042	5042	5042	
5°	5042	5019	4960	5001	4987	478
15°	4795	4745	4590	4504	4458	1351
25°	4353	4207	3906	3719	3650	2002
35°	3751	3518	3117	2829	2728	2348
45°	3066	2760	2282	1957	1848	2368
55°	2331	1976	1483	1209	1123	2083
65°	1574	1204	794	639	625	1561
75°	839	520	365	333	329	888
85°	196	100	87	87	87	225
90°	2	23	62	58	60	16
95°	93	110	114	114	110	103
105°	382	387	391	394	394	403
115°	710	721	718	716	710	703
125°	1034	1049	1044	1039	1037	924
135°	1337	1356	1360	1358	1353	1033
145°	1623	1636	1646	1648	1641	1014
155°	1856	1861	1866	1875	1870	854
165°	2019	2017	2017	2030	2021	569
175°	2101	2096	2092	2104	2094	200
180°	2104	2104	2104	2104	2104	

TEST NUMBER: P911001

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5041.8	5041.8	5041.8	5041.8	5041.8
2.5°	5064.6	5041.8	4991.5	5037.5	5028.3
5°	5041.8	5019.1	4959.6	5000.7	4987.2
7.5°	5000.7	4973.5	4909.7	4927.6	4904.8
10°	4946.0	4914.0	4823.0	4809.0	4781.9
12.5°	4877.7	4836.6	4713.1	4686.0	4635.6
15°	4795.4	4745.1	4590.2	4503.5	4458.0
17.5°	4699.6	4626.5	4434.8	4334.5	4261.4
20°	4590.2	4498.7	4270.6	4156.9	4056.2
22.5°	4471.6	4366.5	4101.7	3946.8	3878.5
25°	4352.9	4206.8	3905.7	3718.8	3650.1
27.5°	4211.6	4056.2	3723.1	3508.7	3403.6
30°	4061.0	3887.3	3522.3	3289.8	3166.4
32.5°	3914.9	3704.7	3331.0	3057.1	2942.8
35°	3750.7	3517.9	3116.6	2829.1	2728.4
37.5°	3591.1	3339.8	2915.7	2600.5	2486.8
40°	3422.0	3148.6	2705.6	2381.7	2263.1
42.5°	3248.7	2956.8	2496.0	2158.1	2044.3
45°	3066.3	2760.3	2281.5	1957.2	1847.8
47.5°	2892.9	2569.1	2076.3	1751.9	1651.7
50°	2701.2	2377.4	1875.4	1560.3	1464.9
52.5°	2513.9	2171.6	1683.7	1382.6	1295.9
55°	2331.3	1975.6	1482.7	1209.3	1122.6
57.5°	2144.6	1779.5	1305.1	1049.6	976.4
60°	1952.8	1587.9	1117.8	885.4	812.3
62.5°	1766.0	1401.0	958.1	739.3	702.9
65°	1574.2	1204.4	793.9	639.0	624.9
67.5°	1391.8	1021.9	639.0	561.0	547.5
70°	1200.0	844.3	529.1	483.6	465.2
72.5°	1017.5	679.7	442.5	406.1	396.9
75°	839.4	519.9	365.0	333.0	328.7
77.5°	661.7	369.4	287.6	269.2	259.9
80°	497.2	264.8	218.8	201.0	201.0
82.5°	346.6	178.1	150.6	141.4	141.4
85°	196.1	100.3	86.6	86.6	86.6
87.5°	73.1	36.3	36.3	31.9	31.9
90°	1.9	22.8	62.2	58.3	60.2
92.5°	39.4	53.3	55.2	57.1	57.1
95°	92.6	110.3	113.6	113.6	110.3
97.5°	154.2	170.7	177.7	177.7	177.7
100°	225.2	239.8	244.9	244.9	243.0
102.5°	300.1	310.9	317.8	319.7	317.8
105°	381.9	387.0	390.8	394.0	394.0
107.5°	463.1	470.8	470.8	472.0	463.1
110°	541.9	551.9	551.9	551.9	546.8

TEST NUMBER: P911001

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.8	637.6	635.7	630.6	626.8
115°	710.5	720.7	717.5	715.6	710.5
117.5°	793.7	807.7	798.7	793.7	788.6
120°	877.4	891.4	877.4	877.4	871.7
122.5°	953.5	971.3	962.4	957.4	953.5
125°	1033.5	1049.3	1044.2	1038.6	1036.7
127.5°	1111.6	1131.2	1124.2	1116.7	1111.6
130°	1184.5	1207.4	1204.2	1200.4	1193.4
132.5°	1266.4	1284.1	1285.3	1276.5	1271.4
135°	1336.8	1356.4	1360.2	1358.3	1353.2
137.5°	1415.4	1431.3	1434.5	1433.2	1425.6
140°	1484.6	1500.5	1509.3	1509.3	1502.4
142.5°	1555.6	1571.5	1576.6	1578.4	1571.5
145°	1622.9	1635.6	1645.8	1647.6	1640.7
147.5°	1683.1	1699.0	1706.6	1709.7	1702.8
150°	1745.3	1756.1	1763.1	1768.7	1763.1
152.5°	1800.5	1811.3	1820.2	1827.2	1820.2
155°	1855.7	1860.8	1866.4	1875.4	1869.7
157.5°	1903.3	1907.1	1910.3	1923.0	1914.1
160°	1945.9	1949.6	1951.5	1962.3	1954.7
162.5°	1985.1	1985.1	1987.0	1999.1	1990.2
165°	2018.7	2016.8	2016.8	2029.6	2020.7
167.5°	2049.2	2043.6	2043.6	2056.2	2047.3
170°	2072.1	2067.0	2065.1	2077.7	2067.0
172.5°	2087.9	2082.8	2080.9	2093.6	2082.8
175°	2100.6	2095.6	2091.7	2104.4	2093.6
177.5°	2107.5	2102.6	2098.7	2109.4	2098.7
180°	2104.4	2104.4	2104.4	2104.4	2104.4

TEST NUMBER: P911001

CATALOG NUMBER: DFN2DIP-HX4F0-110D060US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.94	13.90	13.78	14.75	15.81	8.91	9.87	9.75	10.72	11.79
	3H	14.63	15.48	15.48	16.35	17.44	10.11	10.97	10.96	11.83	12.92
	4H	15.24	16.05	16.11	16.92	18.02	10.57	11.38	11.44	12.25	13.35
	6H	15.67	16.41	16.55	17.29	18.41	10.90	11.64	11.78	12.52	13.63
	8H	15.80	16.51	16.69	17.40	18.52	10.99	11.70	11.88	12.60	13.71
	12H	15.87	16.54	16.76	17.43	18.57	11.04	11.72	11.93	12.60	13.74
4H	2H	12.97	13.78	13.84	14.65	15.75	9.52	10.33	10.39	11.20	12.30
	3H	14.82	15.49	15.70	16.39	17.50	10.89	11.56	11.77	12.46	13.58
	4H	15.51	16.12	16.41	17.02	18.16	11.44	12.05	12.33	12.95	14.09
	6H	16.04	16.56	16.94	17.48	18.63	11.87	12.40	12.78	13.32	14.46
	8H	16.21	16.71	17.12	17.62	18.78	12.00	12.49	12.91	13.41	14.57
	12H	16.32	16.76	17.24	17.69	18.86	12.07	12.52	13.00	13.45	14.61
8H	4H	15.49	15.98	16.40	16.90	18.06	11.73	12.22	12.64	13.14	14.30
	6H	16.06	16.47	17.00	17.43	18.58	12.26	12.66	13.19	13.62	14.78
	8H	16.28	16.64	17.23	17.59	18.76	12.45	12.81	13.40	13.76	14.93
	12H	16.43	16.74	17.37	17.68	18.91	12.58	12.89	13.53	13.83	15.06
12H	4H	15.45	15.89	16.38	16.83	17.99	11.74	12.18	12.67	13.12	14.28
	6H	16.04	16.40	16.98	17.35	18.52	12.31	12.67	13.25	13.62	14.79
	8H	16.27	16.58	17.21	17.52	18.75	12.53	12.84	13.47	13.78	15.01