

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929420

Luminaire Tested: DFN2DIP-HX4F0-110D110US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929420
REPORT IS A COMBINATION OF REPORTS P900959 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D110US940-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19427.7 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 199.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929420

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929420

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2839	2839	2839
5°	2844	2800	2818
10°	2821	2762	2780
15°	2780	2717	2721
20°	2724	2654	2660
25°	2668	2579	2589
30°	2599	2509	2500
35°	2533	2426	2405
40°	2451	2343	2315
45°	2370	2259	2223
50°	2282	2171	2116
55°	2189	2070	2018
60°	2084	1949	1905
65°	1970	1824	1772
70°	1825	1672	1630
75°	1623	1490	1498
80°	1381	1258	1246
85°	1003	857	829

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2370 cd/sqm

TEST NUMBER: P929420

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.3	1.8
10°-20°	1011.1	5.2
20°-30°	1485.8	7.6
30°-40°	1725.7	8.9
40°-50°	1723.6	8.9
50°-60°	1502.9	7.7
60°-70°	1111.0	5.7
70°-80°	628.6	3.2
80°-90°	171.7	0.9
90°-100°	109.2	0.6
100°-110°	407.0	2.1
110°-120°	1079.6	5.6
120°-130°	1790.5	9.2
130°-140°	1902.0	9.8
140°-150°	1767.7	9.1
150°-160°	1421.2	7.3
160°-170°	915.7	4.7
170°-180°	315.2	1.6
0°-30°	2856.2	14.7
0°-40°	4582.0	23.6
0°-60°	7808.4	40.2
0°-90°	9719.7	50.0
90°-120°	1595.8	8.2
90°-150°	7055.9	36.3
90°-180°	9708.0	50.0
0°-180°	19427.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3818	3818	3818	3818	3818	
5°	3818	3804	3763	3792	3785	362
15°	3634	3613	3565	3580	3561	1024
25°	3289	3260	3198	3205	3198	1514
35°	2838	2801	2742	2720	2702	1772
45°	2309	2284	2228	2188	2173	1782
55°	1748	1726	1682	1637	1619	1563
65°	1179	1156	1120	1087	1068	1165
75°	617	610	591	569	576	658
85°	150	147	143	132	128	168
90°	2	29	48	60	65	18
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1378	1418	1478	369	197	1356
125°	1948	1979	2025	2042	2049	1737
135°	2411	2449	2470	2495	2490	1862
145°	2796	2794	2834	2851	2839	1749
155°	3079	3058	3086	3101	3082	1419
165°	3244	3230	3237	3254	3237	917
175°	3318	3302	3307	3323	3300	316
180°	3312	3312	3312	3312	3312	

TEST NUMBER: P929420

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3817.9	3817.9	3817.9	3817.9	3817.9
2.5°	3840.1	3821.8	3781.3	3817.9	3810.9
5°	3817.9	3803.5	3763.0	3792.2	3785.2
7.5°	3792.2	3770.4	3729.9	3759.5	3752.1
10°	3752.1	3726.3	3682.4	3711.5	3700.6
12.5°	3696.8	3675.0	3631.0	3649.3	3641.9
15°	3634.5	3612.6	3564.7	3579.5	3561.2
17.5°	3557.3	3535.5	3487.6	3505.9	3487.6
20°	3472.8	3451.0	3399.6	3410.5	3396.1
22.5°	3388.7	3355.5	3307.6	3307.6	3300.2
25°	3289.3	3260.2	3197.8	3204.9	3197.8
27.5°	3179.1	3153.4	3105.9	3095.0	3076.7
30°	3069.3	3039.7	2984.7	2973.8	2959.0
32.5°	2951.6	2929.9	2871.0	2848.8	2834.0
35°	2837.9	2801.3	2742.5	2720.2	2702.0
37.5°	2709.4	2676.3	2617.5	2591.7	2573.4
40°	2577.3	2547.7	2488.9	2456.2	2441.4
42.5°	2448.8	2419.2	2360.8	2323.7	2302.0
45°	2309.4	2283.6	2228.3	2188.3	2173.4
47.5°	2173.4	2147.8	2088.9	2048.4	2026.5
50°	2030.1	2011.8	1960.3	1909.0	1890.7
52.5°	1890.7	1864.9	1817.4	1776.9	1751.2
55°	1747.7	1725.5	1681.5	1637.4	1619.2
57.5°	1604.4	1586.1	1538.2	1494.1	1479.3
60°	1461.0	1446.6	1395.2	1354.7	1343.8
62.5°	1321.6	1295.9	1259.2	1222.7	1207.9
65°	1178.6	1156.4	1119.8	1086.7	1068.4
67.5°	1031.8	1013.1	980.4	954.7	939.9
70°	895.8	881.0	847.9	822.2	807.8
72.5°	756.4	741.6	723.3	697.6	686.7
75°	616.6	609.6	590.9	569.1	576.5
77.5°	491.9	477.1	469.7	458.8	448.0
80°	367.3	363.4	356.0	345.1	337.7
82.5°	249.7	249.7	246.2	231.4	231.4
85°	150.4	146.8	143.3	132.0	128.5
87.5°	66.2	58.8	51.4	40.5	36.6
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.4	64.6
95°	155.7	76.5	93.3	105.5	103.0
97.5°	280.3	83.9	122.0	129.4	131.7
100°	424.2	95.9	136.6	155.7	160.5
102.5°	582.1	577.6	141.4	167.6	175.0
105°	728.4	800.4	146.3	172.4	182.1
107.5°	898.6	958.3	151.1	177.2	187.0
110°	1061.6	1111.7	419.4	179.8	189.2

TEST NUMBER: P929420

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1215.0	1257.9	1217.2	184.4	191.8
115°	1377.7	1418.4	1478.5	369.0	196.6
117.5°	1519.2	1567.0	1607.9	1265.0	637.3
120°	1677.3	1713.2	1756.4	1785.2	1461.6
122.5°	1811.4	1849.7	1897.8	1912.1	1914.7
125°	1947.9	1979.3	2024.8	2041.5	2048.7
127.5°	2072.6	2106.1	2142.2	2166.1	2168.5
130°	2190.0	2228.5	2254.6	2281.1	2278.9
132.5°	2309.8	2341.1	2367.4	2389.0	2386.7
135°	2410.6	2449.0	2470.3	2494.6	2489.7
137.5°	2515.9	2544.6	2568.8	2592.7	2585.6
140°	2618.9	2638.2	2664.4	2686.0	2674.0
142.5°	2705.3	2722.1	2753.2	2772.2	2760.3
145°	2796.4	2793.8	2834.5	2851.4	2839.4
147.5°	2875.3	2868.1	2908.8	2920.8	2911.4
150°	2952.1	2935.3	2973.7	2987.9	2976.0
152.5°	3016.7	2997.6	3033.4	3048.0	3031.2
155°	3079.0	3057.6	3086.3	3100.6	3081.5
157.5°	3129.3	3110.2	3131.9	3148.7	3129.3
160°	3172.6	3158.0	3172.6	3186.8	3170.0
162.5°	3210.7	3196.5	3208.4	3225.2	3203.6
165°	3244.3	3230.0	3237.2	3253.9	3237.2
167.5°	3270.7	3256.2	3263.6	3280.4	3258.8
170°	3292.4	3277.8	3282.6	3299.5	3277.8
172.5°	3306.6	3292.4	3297.2	3314.0	3292.4
175°	3318.5	3301.7	3306.6	3323.4	3299.5
177.5°	3323.4	3306.6	3309.1	3325.9	3304.3
180°	3311.5	3311.5	3311.5	3311.5	3311.5

TEST NUMBER: P929420

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.90	11.76	11.86	12.73	14.01	10.47	11.33	11.43	12.30	13.57
	3H	12.56	13.33	13.53	14.32	15.61	12.09	12.86	13.06	13.84	15.14
	4H	13.15	13.88	14.13	14.87	16.17	12.68	13.41	13.66	14.39	15.70
	6H	13.55	14.23	14.54	15.22	16.53	13.08	13.75	14.07	14.74	16.05
	8H	13.66	14.30	14.66	15.31	16.62	13.18	13.82	14.18	14.83	16.14
	12H	13.71	14.32	14.71	15.32	16.65	13.22	13.83	14.23	14.84	16.17
4H	2H	11.36	12.09	12.35	13.08	14.38	11.02	11.75	12.01	12.74	14.04
	3H	13.23	13.84	14.23	14.86	16.17	12.84	13.45	13.83	14.46	15.78
	4H	13.95	14.50	14.95	15.51	16.85	13.54	14.10	14.55	15.11	16.44
	6H	14.46	14.94	15.48	15.97	17.31	14.05	14.53	15.07	15.56	16.90
	8H	14.61	15.06	15.63	16.08	17.44	14.20	14.65	15.22	15.67	17.02
	12H	14.69	15.09	15.72	16.13	17.49	14.26	14.67	15.30	15.71	17.06
8H	4H	14.14	14.59	15.16	15.62	16.97	13.78	14.23	14.80	15.26	16.61
	6H	14.78	15.15	15.82	16.21	17.56	14.41	14.78	15.45	15.85	17.20
	8H	15.00	15.32	16.05	16.38	17.74	14.63	14.95	15.68	16.01	17.37
	12H	15.13	15.42	16.18	16.46	17.87	14.74	15.03	15.80	16.08	17.49
12H	4H	14.13	14.53	15.17	15.57	16.93	13.78	14.18	14.81	15.22	16.58
	6H	14.81	15.13	15.86	16.18	17.55	14.45	14.78	15.50	15.83	17.20
	8H	15.05	15.34	16.10	16.38	17.79	14.69	14.98	15.75	16.02	17.44

END OF REPORT