

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929454

Luminaire Tested: DFN2DIP-HX4F0-120D100US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929454
REPORT IS A COMBINATION OF REPORTS P900944 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D100US940-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17929.2 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 202.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929454

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US940-RLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929454

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3290	3290	3290
5°	3295	3238	3258
10°	3263	3174	3152
15°	3218	3070	2989
20°	3159	2926	2788
25°	3098	2764	2593
30°	3017	2598	2347
35°	2937	2419	2131
40°	2856	2235	1883
45°	2762	2029	1658
50°	2664	1823	1439
55°	2562	1601	1227
60°	2445	1370	1011
65°	2309	1135	910
70°	2145	916	824
75°	1939	808	750
80°	1641	679	651
85°	1147	455	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2762 cd/sqm

TEST NUMBER: P929454

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.6	2.3
10°-20°	1138.2	6.3
20°-30°	1598.0	8.9
30°-40°	1741.9	9.7
40°-50°	1601.0	8.9
50°-60°	1257.3	7.0
60°-70°	818.4	4.6
70°-80°	421.3	2.3
80°-90°	112.8	0.6
90°-100°	99.3	0.6
100°-110°	370.0	2.1
110°-120°	981.4	5.5
120°-130°	1627.8	9.1
130°-140°	1729.1	9.6
140°-150°	1607.0	9.0
150°-160°	1292.0	7.2
160°-170°	832.5	4.6
170°-180°	286.5	1.6
0°-30°	3150.8	17.6
0°-40°	4892.8	27.3
0°-60°	7751.1	43.2
0°-90°	9103.7	50.8
90°-120°	1450.7	8.1
90°-150°	6414.5	35.8
90°-180°	8826.0	49.2
0°-180°	17929.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4424	4424	4424	4424	4424	
5°	4424	4404	4352	4388	4376	419
15°	4208	4164	4028	3952	3912	1186
25°	3820	3691	3427	3263	3203	1757
35°	3291	3087	2735	2482	2394	2060
45°	2690	2422	2002	1717	1621	2078
55°	2046	1734	1301	1061	985	1828
65°	1381	1057	697	561	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	198
90°	2	26	43	55	59	17
95°	142	70	85	96	94	168
105°	662	728	133	157	166	708
115°	1252	1290	1344	336	179	1233
125°	1771	1799	1841	1856	1862	1579
135°	2192	2226	2246	2268	2263	1693
145°	2542	2540	2577	2592	2581	1590
155°	2799	2780	2806	2819	2801	1290
165°	2949	2936	2943	2958	2943	833
175°	3017	3002	3006	3021	3000	287
180°	3010	3010	3010	3010	3010	

TEST NUMBER: P929454

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US940-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4424.0	4424.0	4424.0	4424.0	4424.0
2.5°	4443.9	4424.0	4379.8	4420.1	4412.0
5°	4424.0	4404.0	4351.7	4387.8	4376.0
7.5°	4387.8	4364.0	4308.0	4323.7	4303.7
10°	4339.8	4311.8	4231.9	4219.6	4195.9
12.5°	4279.9	4243.9	4135.5	4111.8	4067.6
15°	4207.7	4163.6	4027.6	3951.6	3911.7
17.5°	4123.6	4059.5	3891.3	3803.4	3739.3
20°	4027.6	3947.4	3747.3	3647.5	3559.1
22.5°	3923.6	3831.4	3599.0	3463.1	3403.2
25°	3819.5	3691.2	3427.0	3263.0	3202.7
27.5°	3695.5	3559.1	3266.9	3078.7	2986.5
30°	3563.4	3410.9	3090.6	2886.7	2778.4
32.5°	3435.1	3250.7	2922.8	2682.4	2582.2
35°	3291.1	3086.8	2734.6	2482.3	2393.9
37.5°	3150.9	2930.5	2558.3	2281.8	2182.0
40°	3002.7	2762.7	2374.1	2089.9	1985.8
42.5°	2850.6	2594.5	2190.1	1893.6	1793.8
45°	2690.5	2422.0	2001.9	1717.4	1621.3
47.5°	2538.4	2254.3	1821.8	1537.3	1449.3
50°	2370.2	2086.0	1645.6	1369.0	1285.4
52.5°	2205.8	1905.5	1477.3	1213.1	1137.1
55°	2045.7	1733.5	1301.1	1061.0	985.0
57.5°	1881.7	1561.4	1145.1	920.9	856.8
60°	1713.5	1393.2	980.8	776.9	712.8
62.5°	1549.6	1229.3	840.6	648.7	616.7
65°	1381.4	1056.8	696.7	560.7	548.4
67.5°	1221.2	896.6	560.7	492.3	480.4
70°	1053.0	740.8	464.3	424.3	408.2
72.5°	892.9	596.4	388.2	356.4	348.3
75°	736.5	456.2	320.3	292.2	288.4
77.5°	580.7	324.1	252.3	236.2	228.1
80°	436.3	232.4	192.0	176.3	176.3
82.5°	304.2	156.3	132.1	124.0	124.0
85°	172.1	88.0	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	2.1	26.1	43.4	54.6	58.7
92.5°	54.6	45.8	52.3	56.6	58.7
95°	141.5	69.6	84.8	96.0	93.7
97.5°	254.8	76.3	111.0	117.7	119.8
100°	385.7	87.1	124.2	141.5	145.9
102.5°	529.2	525.1	128.5	152.4	159.0
105°	662.2	727.6	133.0	156.7	165.6
107.5°	816.9	871.2	137.4	161.2	169.9
110°	965.1	1010.6	381.2	163.5	172.0

TEST NUMBER: P929454

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1104.5	1143.5	1106.6	167.6	174.4
115°	1252.5	1289.5	1344.1	335.5	178.8
117.5°	1381.0	1424.5	1461.7	1150.1	579.4
120°	1524.9	1557.4	1596.8	1622.9	1328.8
122.5°	1646.7	1681.6	1725.3	1738.2	1740.6
125°	1770.9	1799.3	1840.7	1856.0	1862.4
127.5°	1884.2	1914.7	1947.5	1969.3	1971.3
130°	1990.9	2025.9	2049.7	2073.7	2071.7
132.5°	2099.9	2128.3	2152.1	2171.8	2169.7
135°	2191.5	2226.3	2245.8	2267.7	2263.4
137.5°	2287.2	2313.3	2335.3	2357.0	2350.5
140°	2380.7	2398.4	2422.1	2441.8	2431.0
142.5°	2459.4	2474.7	2502.9	2520.2	2509.4
145°	2542.2	2539.9	2576.9	2592.2	2581.3
147.5°	2613.8	2607.4	2644.3	2655.2	2646.7
150°	2683.7	2668.4	2703.4	2716.3	2705.4
152.5°	2742.4	2725.1	2757.7	2770.8	2755.6
155°	2799.1	2779.7	2805.8	2818.7	2801.4
157.5°	2844.9	2827.6	2847.2	2862.4	2844.9
160°	2884.2	2871.0	2884.2	2897.1	2881.9
162.5°	2918.8	2905.9	2916.8	2932.0	2912.4
165°	2949.3	2936.4	2942.9	2958.1	2942.9
167.5°	2973.4	2960.2	2967.0	2982.2	2962.5
170°	2993.0	2979.9	2984.3	2999.5	2979.9
172.5°	3006.0	2993.0	2997.5	3012.7	2993.0
175°	3016.8	3001.6	3006.0	3021.3	2999.5
177.5°	3021.3	3006.0	3008.4	3023.6	3003.9
180°	3010.4	3010.4	3010.4	3010.4	3010.4

TEST NUMBER: P929454

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.36	12.19	12.31	13.16	14.42	7.33	8.17	8.29	9.14	10.40
	3H	13.04	13.78	14.00	14.76	16.05	8.52	9.27	9.49	10.25	11.53
	4H	13.65	14.35	14.63	15.33	16.63	8.97	9.68	9.96	10.66	11.96
	6H	14.07	14.72	15.06	15.71	17.01	9.30	9.95	10.29	10.93	12.24
	8H	14.20	14.81	15.20	15.82	17.12	9.39	10.01	10.39	11.01	12.31
	12H	14.26	14.85	15.26	15.84	17.17	9.43	10.02	10.44	11.02	12.34
4H	2H	11.38	12.08	12.37	13.06	14.36	7.93	8.63	8.92	9.62	10.91
	3H	13.21	13.80	14.21	14.81	16.11	9.28	9.87	10.28	10.88	12.19
	4H	13.90	14.44	14.91	15.44	16.77	9.83	10.37	10.84	11.37	12.70
	6H	14.42	14.88	15.43	15.91	17.23	10.25	10.71	11.27	11.74	13.07
	8H	14.59	15.02	15.61	16.04	17.39	10.38	10.81	11.40	11.83	13.17
	12H	14.69	15.08	15.73	16.11	17.46	10.45	10.84	11.48	11.87	13.22
8H	4H	13.87	14.30	14.89	15.32	16.66	10.11	10.54	11.13	11.56	12.90
	6H	14.44	14.79	15.48	15.85	17.20	10.63	10.99	11.67	12.05	13.39
	8H	14.65	14.97	15.70	16.02	17.37	10.82	11.14	11.87	12.18	13.54
	12H	14.79	15.07	15.85	16.11	17.51	10.95	11.22	12.00	12.26	13.67
12H	4H	13.82	14.21	14.86	15.25	16.59	10.12	10.50	11.15	11.54	12.89
	6H	14.41	14.73	15.46	15.77	17.13	10.68	10.99	11.73	12.04	13.40
	8H	14.63	14.91	15.69	15.95	17.35	10.89	11.17	11.95	12.21	13.61

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8