

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911027

Luminaire Tested: DFN2DIP-HX4F0-120D100US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911027
REPORT IS A COMBINATION OF REPORTS P899424 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D100US850-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21126.4 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 183.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911027

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911027

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4090	4090	4090
5°	4097	4025	4051
10°	4056	3947	3919
15°	4001	3817	3716
20°	3927	3637	3466
25°	3852	3436	3224
30°	3751	3230	2918
35°	3652	3008	2649
40°	3551	2778	2341
45°	3433	2523	2061
50°	3312	2266	1788
55°	3186	1991	1526
60°	3039	1703	1256
65°	2871	1411	1131
70°	2667	1138	1024
75°	2411	1004	932
80°	2040	844	809
85°	1426	565	609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3433 cd/sqm

TEST NUMBER: P911027

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	2.4
10°-20°	1415.1	6.7
20°-30°	1986.8	9.4
30°-40°	2165.7	10.3
40°-50°	1990.5	9.4
50°-60°	1563.2	7.4
60°-70°	1017.5	4.8
70°-80°	523.8	2.5
80°-90°	143.7	0.7
90°-100°	217.0	1.0
100°-110°	689.6	3.3
110°-120°	1180.1	5.6
120°-130°	1552.0	7.3
130°-140°	1742.1	8.2
140°-150°	1708.3	8.1
150°-160°	1433.0	6.8
160°-170°	950.4	4.5
170°-180°	332.2	1.6
0°-30°	3917.3	18.5
0°-40°	6083.0	28.8
0°-60°	9636.8	45.6
0°-90°	11321.7	53.6
90°-120°	2086.7	9.9
90°-150°	7089.1	33.6
90°-180°	9805.0	46.4
0°-180°	21126.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	3	38	104	97	100	21
95°	154	184	189	189	184	172
105°	637	645	651	657	657	672
115°	1184	1201	1196	1193	1184	1171
125°	1722	1749	1740	1731	1728	1539
135°	2228	2261	2267	2264	2255	1722
145°	2705	2726	2743	2746	2734	1690
155°	3093	3101	3111	3126	3116	1424
165°	3365	3361	3361	3383	3368	949
175°	3501	3493	3486	3507	3489	333
180°	3507	3507	3507	3507	3507	

TEST NUMBER: P911027

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	3.2	38.0	103.6	97.3	100.5
92.5°	65.5	88.8	92.0	95.2	95.2
95°	154.4	184.0	189.3	189.3	184.0
97.5°	257.0	284.5	296.1	296.1	296.1
100°	375.4	399.7	408.1	408.1	405.0
102.5°	500.2	518.1	529.8	532.9	529.8
105°	636.6	645.0	651.3	656.6	656.6
107.5°	771.9	784.6	784.6	786.7	771.9
110°	903.1	919.9	919.9	919.9	911.5

TEST NUMBER: P911027

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1044.7	1062.6	1059.5	1051.0	1044.7
115°	1184.3	1201.2	1195.9	1192.7	1184.3
117.5°	1322.8	1346.1	1331.2	1322.8	1314.3
120°	1462.3	1485.6	1462.3	1462.3	1452.9
122.5°	1589.2	1618.8	1604.1	1595.6	1589.2
125°	1722.5	1748.9	1740.5	1730.9	1727.8
127.5°	1852.6	1885.3	1873.7	1861.0	1852.6
130°	1974.1	2012.2	2007.0	2000.5	1989.0
132.5°	2110.5	2140.1	2142.3	2127.5	2119.0
135°	2227.9	2260.7	2267.0	2263.9	2255.4
137.5°	2359.1	2385.5	2390.8	2388.7	2375.9
140°	2474.3	2500.7	2515.5	2515.5	2503.9
142.5°	2592.7	2619.1	2627.6	2630.8	2619.1
145°	2704.7	2725.9	2742.9	2746.0	2734.4
147.5°	2805.2	2831.7	2844.4	2849.7	2838.0
150°	2908.9	2926.9	2938.5	2947.9	2938.5
152.5°	3000.8	3018.8	3033.7	3045.3	3033.7
155°	3092.9	3101.3	3110.9	3125.6	3116.1
157.5°	3172.2	3178.5	3183.8	3204.9	3190.1
160°	3243.0	3249.4	3252.5	3270.4	3257.8
162.5°	3308.6	3308.6	3311.7	3331.8	3317.0
165°	3364.6	3361.4	3361.4	3382.6	3367.8
167.5°	3415.4	3405.8	3405.8	3427.0	3412.2
170°	3453.4	3445.0	3441.8	3463.0	3445.0
172.5°	3479.8	3471.4	3468.2	3489.4	3471.4
175°	3501.0	3492.6	3486.3	3507.3	3489.4
177.5°	3512.6	3504.2	3497.8	3515.8	3497.8
180°	3507.3	3507.3	3507.3	3507.3	3507.3

TEST NUMBER: P911027

CATALOG NUMBER: DFN2DIP-HX4F0-120D100US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.37	13.23	13.30	14.18	15.40	8.34	9.20	9.28	10.15	11.37
	3H	14.05	14.82	14.99	15.77	17.02	9.54	10.30	10.48	11.26	12.50
	4H	14.66	15.39	15.62	16.35	17.60	9.99	10.72	10.95	11.67	12.93
	6H	15.08	15.75	16.05	16.72	17.99	10.31	10.98	11.28	11.95	13.21
	8H	15.21	15.85	16.19	16.83	18.09	10.40	11.04	11.38	12.02	13.29
	12H	15.28	15.88	16.26	16.86	18.14	10.45	11.06	11.43	12.03	13.32
4H	2H	12.39	13.12	13.36	14.08	15.33	8.94	9.67	9.91	10.63	11.88
	3H	14.23	14.83	15.20	15.82	17.09	10.30	10.90	11.27	11.89	13.16
	4H	14.92	15.47	15.90	16.45	17.75	10.85	11.40	11.83	12.38	13.67
	6H	15.44	15.91	16.43	16.92	18.21	11.27	11.74	12.27	12.75	14.04
	8H	15.61	16.06	16.61	17.06	18.36	11.40	11.84	12.40	12.84	14.15
	12H	15.71	16.11	16.72	17.12	18.43	11.47	11.87	12.48	12.88	14.19
8H	4H	14.89	15.33	15.89	16.33	17.64	11.13	11.57	12.13	12.57	13.88
	6H	15.46	15.82	16.48	16.86	18.17	11.65	12.02	12.67	13.06	14.36
	8H	15.68	16.00	16.70	17.03	18.35	11.85	12.17	12.87	13.20	14.52
	12H	15.82	16.10	16.85	17.12	18.49	11.97	12.25	13.00	13.27	14.64
12H	4H	14.84	15.24	15.86	16.26	17.57	11.14	11.54	12.15	12.55	13.86
	6H	15.43	15.76	16.46	16.78	18.11	11.70	12.02	12.73	13.05	14.37
	8H	15.66	15.94	16.69	16.96	18.33	11.92	12.20	12.95	13.22	14.59

END OF REPORT