

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928170

Luminaire Tested: DFN2DIP-HX4F0-040D040US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928170
REPORT IS A COMBINATION OF REPORTS P900820 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D040US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5829.1 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928170

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928170

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	974	974	974
5°	975	958	964
10°	966	940	933
15°	952	909	884
20°	935	866	825
25°	917	818	768
30°	893	769	695
35°	869	716	631
40°	845	661	557
45°	817	601	491
50°	788	539	426
55°	758	474	363
60°	723	406	299
65°	683	336	269
70°	635	271	244
75°	574	239	222
80°	485	201	193
85°	339	135	145

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 817 cd/sqm

TEST NUMBER: P928170

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	2.1
10°-20°	336.9	5.8
20°-30°	473.0	8.1
30°-40°	515.5	8.8
40°-50°	473.8	8.1
50°-60°	372.1	6.4
60°-70°	242.2	4.2
70°-80°	124.7	2.1
80°-90°	33.7	0.6
90°-100°	35.2	0.6
100°-110°	131.4	2.3
110°-120°	348.6	6.0
120°-130°	578.1	9.9
130°-140°	614.1	10.5
140°-150°	570.7	9.8
150°-160°	458.8	7.9
160°-170°	295.7	5.1
170°-180°	101.8	1.7
0°-30°	932.5	16.0
0°-40°	1448.1	24.8
0°-60°	2294.1	39.4
0°-90°	2694.7	46.2
90°-120°	515.2	8.8
90°-150°	2278.1	39.1
90°-180°	3134.0	53.8
0°-180°	5829.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	9	15	19	21	5
95°	50	25	30	34	33	59
105°	235	258	47	56	59	251
115°	445	458	477	119	64	438
125°	629	639	654	659	662	561
135°	778	791	798	805	804	601
145°	903	902	915	921	917	565
155°	994	987	996	1001	995	458
165°	1048	1043	1045	1051	1045	296
175°	1071	1066	1068	1073	1065	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P928170

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.7	9.3	15.4	19.4	20.8
92.5°	19.4	16.2	18.5	20.1	20.8
95°	50.2	24.7	30.1	34.1	33.3
97.5°	90.5	27.1	39.4	41.8	42.5
100°	136.9	31.0	44.1	50.2	51.8
102.5°	187.9	186.5	45.6	54.1	56.5
105°	235.1	258.4	47.2	55.7	58.8
107.5°	290.1	309.4	48.8	57.3	60.4
110°	342.8	358.9	135.4	58.1	61.1



TEST NUMBER: P928170

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	406.1	393.0	59.6	61.9
115°	444.8	457.9	477.3	119.1	63.5
117.5°	490.5	505.9	519.2	408.4	205.8
120°	541.6	553.1	567.1	576.4	472.0
122.5°	584.8	597.2	612.8	617.4	618.2
125°	628.9	639.1	653.7	659.2	661.5
127.5°	669.2	680.0	691.7	699.4	700.1
130°	707.1	719.5	727.9	736.5	735.8
132.5°	745.7	755.9	764.4	771.3	770.6
135°	778.3	790.7	797.6	805.4	803.9
137.5°	812.3	821.5	829.4	837.1	834.8
140°	845.5	851.8	860.3	867.2	863.4
142.5°	873.5	878.9	888.9	895.0	891.2
145°	902.9	902.1	915.2	920.6	916.7
147.5°	928.3	926.0	939.2	943.0	940.0
150°	953.1	947.7	960.1	964.7	960.9
152.5°	974.0	967.8	979.4	984.1	978.7
155°	994.1	987.2	996.5	1001.1	994.9
157.5°	1010.4	1004.2	1011.2	1016.6	1010.4
160°	1024.3	1019.6	1024.3	1028.9	1023.5
162.5°	1036.6	1032.1	1035.9	1041.3	1034.4
165°	1047.5	1042.9	1045.2	1050.6	1045.2
167.5°	1056.1	1051.3	1053.8	1059.1	1052.2
170°	1063.0	1058.3	1059.9	1065.3	1058.3
172.5°	1067.6	1063.0	1064.6	1070.0	1063.0
175°	1071.4	1066.0	1067.6	1073.0	1065.3
177.5°	1073.0	1067.6	1068.4	1073.9	1066.9
180°	1069.2	1069.2	1069.2	1069.2	1069.2

TEST NUMBER: P928170

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.69	7.49	7.69	8.49	9.82	2.66	3.46	3.66	4.47	5.79
	3H	8.37	9.08	9.37	10.09	11.44	3.85	4.57	4.86	5.58	6.93
	4H	8.98	9.65	9.99	10.67	12.02	4.30	4.98	5.32	5.99	7.35
	6H	9.40	10.02	10.43	11.04	12.41	4.62	5.25	5.65	6.27	7.63
	8H	9.52	10.12	10.56	11.15	12.51	4.72	5.31	5.75	6.34	7.71
	12H	9.58	10.15	10.62	11.18	12.56	4.76	5.32	5.80	6.35	7.74
4H	2H	6.71	7.38	7.73	8.40	9.75	3.26	3.93	4.28	4.95	6.30
	3H	8.53	9.10	9.57	10.14	11.51	4.61	5.17	5.64	6.21	7.58
	4H	9.23	9.74	10.27	10.78	12.17	5.15	5.67	6.20	6.70	8.10
	6H	9.74	10.18	10.79	11.24	12.63	5.57	6.02	6.62	7.07	8.46
	8H	9.92	10.33	10.97	11.38	12.78	5.70	6.12	6.76	7.17	8.57
	12H	10.01	10.38	11.08	11.45	12.86	5.77	6.14	6.84	7.21	8.61
8H	4H	9.19	9.60	10.24	10.66	12.06	5.43	5.85	6.48	6.90	8.30
	6H	9.76	10.10	10.83	11.19	12.59	5.95	6.29	7.03	7.39	8.79
	8H	9.98	10.27	11.06	11.35	12.77	6.15	6.44	7.23	7.52	8.94
	12H	10.11	10.38	11.20	11.45	12.91	6.26	6.53	7.35	7.60	9.06
12H	4H	9.14	9.52	10.21	10.58	11.99	5.44	5.81	6.51	6.87	8.28
	6H	9.73	10.03	10.82	11.11	12.53	6.00	6.30	7.08	7.38	8.80
	8H	9.95	10.22	11.04	11.29	12.75	6.21	6.48	7.30	7.55	9.01

END OF REPORT