

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928180

Luminaire Tested: DFN2DIP-HX4F0-040D070US927-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928180
REPORT IS A COMBINATION OF REPORTS P900873 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D070US927-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8624.8 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928180

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928180

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	917	917	917
5°	918	904	910
10°	911	892	898
15°	897	877	878
20°	879	857	859
25°	861	833	836
30°	839	810	807
35°	818	783	777
40°	792	756	747
45°	765	729	718
50°	737	701	683
55°	707	668	651
60°	673	629	615
65°	636	589	572
70°	589	540	526
75°	524	481	484
80°	446	406	403
85°	323	277	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 961 cd/sqm

TEST NUMBER: P928180

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	1.3
10°-20°	326.4	3.8
20°-30°	479.7	5.6
30°-40°	557.2	6.5
40°-50°	556.5	6.5
50°-60°	485.2	5.6
60°-70°	358.7	4.2
70°-80°	202.9	2.4
80°-90°	56.9	0.7
90°-100°	61.7	0.7
100°-110°	230.0	2.7
110°-120°	610.0	7.1
120°-130°	1011.7	11.7
130°-140°	1074.6	12.5
140°-150°	998.8	11.6
150°-160°	803.0	9.3
160°-170°	517.4	6.0
170°-180°	178.1	2.1
0°-30°	922.2	10.7
0°-40°	1479.4	17.2
0°-60°	2521.1	29.2
0°-90°	3139.6	36.4
90°-120°	901.6	10.5
90°-150°	3986.8	46.2
90°-180°	5485.0	63.6
0°-180°	8624.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1224	1222	117
15°	1173	1166	1151	1156	1150	330
25°	1062	1053	1032	1035	1032	489
35°	916	904	886	878	872	572
45°	746	737	720	706	702	575
55°	564	557	543	529	523	504
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	48	47	46	43	42	54
90°	1	16	27	34	36	8
95°	88	43	53	60	58	104
105°	412	452	83	97	103	440
115°	778	801	835	208	111	766
125°	1101	1118	1144	1154	1158	982
135°	1362	1384	1396	1409	1407	1052
145°	1580	1579	1602	1611	1604	988
155°	1740	1728	1744	1752	1741	802
165°	1833	1825	1829	1838	1829	518
175°	1875	1866	1868	1878	1864	178
180°	1871	1871	1871	1871	1871	

TEST NUMBER: P928180

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.7	1232.7	1232.7	1232.7	1232.7
2.5°	1239.9	1233.9	1220.9	1232.7	1230.5
5°	1232.7	1228.0	1214.9	1224.4	1222.1
7.5°	1224.4	1217.3	1204.2	1213.8	1211.4
10°	1211.4	1203.1	1189.0	1198.4	1194.8
12.5°	1193.5	1186.5	1172.3	1178.3	1175.8
15°	1173.4	1166.4	1150.9	1155.7	1149.8
17.5°	1148.6	1141.5	1126.1	1131.9	1126.1
20°	1121.2	1114.2	1097.6	1101.1	1096.5
22.5°	1094.1	1083.4	1067.9	1067.9	1065.6
25°	1062.0	1052.6	1032.5	1034.7	1032.5
27.5°	1026.4	1018.1	1002.8	999.3	993.4
30°	991.0	981.4	963.7	960.1	955.4
32.5°	953.0	946.0	927.0	919.8	915.0
35°	916.3	904.5	885.5	878.3	872.4
37.5°	874.8	864.1	845.1	836.8	830.9
40°	832.2	822.6	803.6	793.0	788.3
42.5°	790.7	781.1	762.2	750.3	743.2
45°	745.6	737.4	719.5	706.5	701.7
47.5°	701.7	693.4	674.5	661.4	654.4
50°	655.5	649.5	633.0	616.3	610.4
52.5°	610.4	602.2	586.8	573.7	565.4
55°	564.3	557.1	542.9	528.7	522.8
57.5°	518.0	512.1	496.6	482.4	477.7
60°	471.7	467.0	450.5	437.4	433.9
62.5°	426.7	418.4	406.6	394.7	390.0
65°	380.6	373.3	361.5	350.9	345.0
67.5°	333.1	327.1	316.6	308.2	303.5
70°	289.2	284.5	273.8	265.5	260.8
72.5°	244.3	239.4	233.6	225.2	221.7
75°	199.1	196.8	190.8	183.7	186.1
77.5°	158.8	154.0	151.7	148.1	144.6
80°	118.6	117.3	114.9	111.4	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.5	47.4	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	1.3	16.2	27.0	33.9	36.5
92.5°	33.9	28.4	32.5	35.2	36.5
95°	87.9	43.2	52.7	59.6	58.2
97.5°	158.3	47.4	69.0	73.2	74.4
100°	239.7	54.2	77.1	87.9	90.7
102.5°	328.9	326.4	79.9	94.7	98.8
105°	411.6	452.2	82.6	97.4	102.9
107.5°	507.7	541.5	85.4	100.2	105.7
110°	599.9	628.1	237.0	101.6	106.9

TEST NUMBER: P928180

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	686.5	710.7	687.8	104.1	108.3
115°	778.5	801.4	835.3	208.5	111.1
117.5°	858.4	885.4	908.5	714.8	360.1
120°	947.7	968.0	992.5	1008.7	825.9
122.5°	1023.4	1045.1	1072.4	1080.4	1081.8
125°	1100.6	1118.3	1144.0	1153.5	1157.5
127.5°	1171.1	1190.0	1210.4	1224.0	1225.2
130°	1237.4	1259.1	1273.9	1288.9	1287.6
132.5°	1305.1	1322.8	1337.6	1349.8	1348.5
135°	1362.0	1383.7	1395.8	1409.4	1406.8
137.5°	1421.5	1437.8	1451.4	1465.0	1460.9
140°	1479.7	1490.6	1505.4	1517.6	1510.9
142.5°	1528.6	1538.1	1555.6	1566.3	1559.6
145°	1580.0	1578.6	1601.6	1611.1	1604.4
147.5°	1624.6	1620.6	1643.6	1650.3	1645.0
150°	1668.0	1658.5	1680.2	1688.2	1681.5
152.5°	1704.5	1693.7	1714.0	1722.1	1712.7
155°	1739.7	1727.6	1743.8	1751.9	1741.1
157.5°	1768.1	1757.4	1769.6	1779.1	1768.1
160°	1792.6	1784.4	1792.6	1800.6	1791.1
162.5°	1814.2	1806.1	1812.8	1822.3	1810.1
165°	1833.1	1825.1	1829.0	1838.5	1829.0
167.5°	1848.1	1839.8	1844.0	1853.5	1841.3
170°	1860.2	1852.1	1854.8	1864.3	1852.1
172.5°	1868.3	1860.2	1863.0	1872.4	1860.2
175°	1875.1	1865.6	1868.3	1877.8	1864.3
177.5°	1877.8	1868.3	1869.8	1879.3	1867.0
180°	1871.0	1871.0	1871.0	1871.0	1871.0

TEST NUMBER: P928180

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.56	6.31	6.63	7.38	8.84	5.13	5.88	6.20	6.95	8.40
	3H	7.22	7.89	8.29	8.97	10.44	6.74	7.42	7.82	8.49	9.96
	4H	7.80	8.44	8.89	9.52	10.99	7.33	7.96	8.41	9.04	10.52
	6H	8.19	8.78	9.29	9.86	11.35	7.72	8.31	8.81	9.39	10.88
	8H	8.30	8.86	9.40	9.95	11.44	7.82	8.38	8.92	9.48	10.96
	12H	8.34	8.87	9.44	9.96	11.47	7.86	8.39	8.96	9.48	10.99
4H	2H	6.01	6.65	7.11	7.73	9.21	5.67	6.31	6.76	7.38	8.86
	3H	7.87	8.40	8.97	9.51	11.00	7.48	8.01	8.58	9.11	10.60
	4H	8.58	9.07	9.68	10.16	11.68	8.17	8.66	9.28	9.76	11.27
	6H	9.09	9.51	10.20	10.63	12.13	8.68	9.10	9.79	10.22	11.72
	8H	9.24	9.63	10.35	10.74	12.26	8.82	9.22	9.94	10.33	11.85
	12H	9.31	9.66	10.43	10.78	12.31	8.88	9.24	10.01	10.36	11.89
8H	4H	8.77	9.16	9.88	10.27	11.79	8.41	8.80	9.52	9.91	11.43
	6H	9.40	9.72	10.53	10.87	12.39	9.03	9.36	10.17	10.51	12.03
	8H	9.62	9.90	10.76	11.03	12.57	9.25	9.53	10.39	10.66	12.20
	12H	9.74	9.99	10.89	11.12	12.69	9.36	9.61	10.50	10.74	12.31
12H	4H	8.75	9.10	9.88	10.23	11.75	8.40	8.75	9.53	9.87	11.40
	6H	9.43	9.71	10.57	10.84	12.38	9.07	9.36	10.21	10.49	12.03
	8H	9.66	9.91	10.81	11.04	12.61	9.31	9.55	10.45	10.68	12.26