

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928208

Luminaire Tested: DFN2DIP-HX4F0-050D050US927-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928208
REPORT IS A COMBINATION OF REPORTS P900839 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D050US927-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7840.8 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928208

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928208

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1146	1146	1146
5°	1148	1130	1137
10°	1138	1115	1122
15°	1122	1097	1098
20°	1099	1071	1073
25°	1077	1041	1045
30°	1049	1012	1009
35°	1022	979	971
40°	989	945	934
45°	957	912	897
50°	921	876	854
55°	884	835	814
60°	841	787	769
65°	795	736	715
70°	736	675	658
75°	655	602	605
80°	558	508	503
85°	405	346	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 957 cd/sqm

TEST NUMBER: P928208

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	1.8
10°-20°	408.0	5.2
20°-30°	599.7	7.6
30°-40°	696.5	8.9
40°-50°	695.6	8.9
50°-60°	606.6	7.7
60°-70°	448.4	5.7
70°-80°	253.7	3.2
80°-90°	69.3	0.9
90°-100°	44.1	0.6
100°-110°	164.3	2.1
110°-120°	435.7	5.6
120°-130°	722.6	9.2
130°-140°	767.6	9.8
140°-150°	713.4	9.1
150°-160°	573.6	7.3
160°-170°	369.6	4.7
170°-180°	127.2	1.6
0°-30°	1152.7	14.7
0°-40°	1849.2	23.6
0°-60°	3151.4	40.2
0°-90°	3922.8	50.0
90°-120°	644.1	8.2
90°-150°	2847.7	36.3
90°-180°	3918.0	50.0
0°-180°	7840.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1530	1528	146
15°	1467	1458	1439	1445	1437	413
25°	1328	1316	1291	1293	1291	611
35°	1145	1131	1107	1098	1090	715
45°	932	922	899	883	877	719
55°	705	696	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	1	12	19	24	26	7
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	572	597	149	79	547
125°	786	799	817	824	827	701
135°	973	988	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1251	1244	573
165°	1309	1304	1306	1313	1306	370
175°	1339	1332	1334	1341	1332	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P928208

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1540.8	1540.8	1540.8	1540.8	1540.8
2.5°	1549.8	1542.4	1526.1	1540.8	1538.1
5°	1540.8	1535.1	1518.7	1530.5	1527.7
7.5°	1530.5	1521.7	1505.4	1517.3	1514.3
10°	1514.3	1503.9	1486.2	1497.9	1493.6
12.5°	1492.0	1483.2	1465.4	1472.8	1469.8
15°	1466.8	1458.0	1438.7	1444.7	1437.2
17.5°	1435.7	1426.9	1407.5	1414.9	1407.5
20°	1401.6	1392.8	1372.1	1376.4	1370.6
22.5°	1367.6	1354.2	1334.9	1334.9	1331.9
25°	1327.6	1315.7	1290.6	1293.4	1290.6
27.5°	1283.0	1272.7	1253.5	1249.1	1241.7
30°	1238.7	1226.8	1204.6	1200.2	1194.3
32.5°	1191.2	1182.5	1158.7	1149.7	1143.8
35°	1145.3	1130.6	1106.8	1097.9	1090.5
37.5°	1093.4	1080.1	1056.4	1046.0	1038.6
40°	1040.2	1028.3	1004.5	991.3	985.3
42.5°	988.3	976.4	952.8	937.8	929.0
45°	932.0	921.7	899.3	883.2	877.1
47.5°	877.1	866.8	843.1	826.7	817.9
50°	819.3	812.0	791.2	770.5	763.0
52.5°	763.0	752.6	733.5	717.2	706.8
55°	705.4	696.4	678.6	660.8	653.5
57.5°	647.5	640.1	620.8	603.0	597.0
60°	589.6	583.9	563.1	546.7	542.4
62.5°	533.4	523.0	508.2	493.4	487.5
65°	475.7	466.7	451.9	438.6	431.2
67.5°	416.4	408.9	395.7	385.3	379.3
70°	361.5	355.6	342.2	331.8	326.1
72.5°	305.3	299.3	291.9	281.6	277.1
75°	248.8	246.0	238.5	229.7	232.7
77.5°	198.6	192.5	189.6	185.2	180.8
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.7	100.7	99.3	93.4	93.4
85°	60.7	59.2	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.1
100°	171.2	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.6	70.6
105°	294.0	323.1	59.0	69.6	73.5
107.5°	362.7	386.7	61.0	71.5	75.5
110°	428.5	448.7	169.3	72.5	76.3

TEST NUMBER: P928208

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.3	507.7	491.3	74.4	77.4
115°	556.1	572.5	596.7	149.0	79.4
117.5°	613.1	632.4	649.0	510.5	257.2
120°	676.9	691.4	708.8	720.5	589.9
122.5°	731.0	746.5	765.9	771.7	772.8
125°	786.1	798.8	817.2	823.9	826.8
127.5°	836.4	850.0	864.6	874.2	875.2
130°	883.9	899.4	909.9	920.6	919.7
132.5°	932.3	944.9	955.4	964.2	963.2
135°	972.9	988.4	997.0	1006.8	1004.8
137.5°	1015.3	1027.0	1036.7	1046.4	1043.5
140°	1056.9	1064.8	1075.3	1084.0	1079.3
142.5°	1091.9	1098.7	1111.2	1118.9	1114.0
145°	1128.6	1127.6	1144.0	1150.8	1145.9
147.5°	1160.4	1157.5	1174.0	1178.8	1175.0
150°	1191.4	1184.7	1200.1	1205.9	1201.1
152.5°	1217.5	1209.8	1224.3	1230.1	1223.3
155°	1242.6	1234.0	1245.6	1251.4	1243.7
157.5°	1262.9	1255.2	1264.0	1270.8	1262.9
160°	1280.4	1274.6	1280.4	1286.1	1279.4
162.5°	1295.8	1290.1	1294.8	1301.7	1292.9
165°	1309.3	1303.6	1306.5	1313.2	1306.5
167.5°	1320.0	1314.2	1317.2	1323.9	1315.2
170°	1328.7	1322.9	1324.9	1331.6	1322.9
172.5°	1334.5	1328.7	1330.7	1337.5	1328.7
175°	1339.4	1332.5	1334.5	1341.3	1331.6
177.5°	1341.3	1334.5	1335.5	1342.3	1333.6
180°	1336.4	1336.4	1336.4	1336.4	1336.4

TEST NUMBER: P928208

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.75	8.61	8.71	9.58	10.85	7.32	8.18	8.27	9.15	10.42
	3H	9.41	10.18	10.38	11.16	12.46	8.94	9.71	9.90	10.69	11.98
	4H	10.00	10.73	10.98	11.71	13.02	9.52	10.26	10.51	11.24	12.54
	6H	10.40	11.07	11.39	12.06	13.38	9.92	10.60	10.92	11.59	12.90
	8H	10.50	11.15	11.50	12.15	13.46	10.03	10.67	11.03	11.68	12.99
	12H	10.55	11.16	11.56	12.16	13.50	10.07	10.68	11.08	11.68	13.02
4H	2H	8.21	8.94	9.20	9.93	11.23	7.87	8.60	8.85	9.58	10.88
	3H	10.08	10.69	11.07	11.70	13.02	9.68	10.30	10.68	11.31	12.62
	4H	10.79	11.35	11.80	12.36	13.70	10.39	10.95	11.39	11.95	13.29
	6H	11.31	11.79	12.33	12.82	14.16	10.90	11.38	11.92	12.41	13.75
	8H	11.46	11.91	12.48	12.93	14.28	11.05	11.50	12.07	12.52	13.87
	12H	11.53	11.94	12.57	12.98	14.33	11.11	11.52	12.15	12.56	13.91
8H	4H	10.99	11.44	12.01	12.46	13.81	10.63	11.08	11.65	12.10	13.45
	6H	11.62	11.99	12.67	13.06	14.41	11.26	11.63	12.30	12.70	14.05
	8H	11.84	12.17	12.89	13.22	14.59	11.48	11.80	12.53	12.85	14.22
	12H	11.98	12.26	13.03	13.31	14.72	11.59	11.88	12.65	12.93	14.34
12H	4H	10.98	11.38	12.01	12.42	13.78	10.62	11.03	11.66	12.07	13.43
	6H	11.65	11.98	12.70	13.03	14.40	11.30	11.63	12.35	12.68	14.05
	8H	11.90	12.18	12.95	13.23	14.64	11.54	11.83	12.59	12.87	14.28

END OF REPORT