

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924629

Luminaire Tested: DFN2DIP-HX4F0-100D090US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924629
REPORT IS A COMBINATION OF REPORTS P899402 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D090US950-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15707.6 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 150.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924629

CATALOG NUMBER: DFN2DIP-HX4F0-100D090US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924629

CATALOG NUMBER: DFN2DIP-HX4F0-100D090US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	99	94	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	34	32
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	64	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2932	2932	2932
5°	2937	2886	2904
10°	2908	2829	2810
15°	2868	2736	2664
20°	2815	2607	2484
25°	2761	2463	2311
30°	2689	2315	2092
35°	2618	2156	1899
40°	2545	1992	1678
45°	2461	1809	1478
50°	2374	1624	1282
55°	2284	1427	1094
60°	2179	1221	901
65°	2058	1012	811
70°	1912	816	734
75°	1728	720	668
80°	1462	605	580
85°	1022	405	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2461 cd/sqm

TEST NUMBER: P924629

CATALOG NUMBER: DFN2DIP-HX4F0-100D090US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.5	2.4
10°-20°	1014.4	6.5
20°-30°	1424.2	9.1
30°-40°	1552.5	9.9
40°-50°	1426.9	9.1
50°-60°	1120.6	7.1
60°-70°	729.4	4.6
70°-80°	375.5	2.4
80°-90°	103.6	0.7
90°-100°	168.0	1.1
100°-110°	533.9	3.4
110°-120°	913.7	5.8
120°-130°	1201.6	7.6
130°-140°	1348.7	8.6
140°-150°	1322.6	8.4
150°-160°	1109.5	7.1
160°-170°	735.8	4.7
170°-180°	257.2	1.6
0°-30°	2808.2	17.9
0°-40°	4360.7	27.8
0°-60°	6908.2	44.0
0°-90°	8116.7	51.7
90°-120°	1615.6	10.3
90°-150°	5488.5	34.9
90°-180°	7591.0	48.3
0°-180°	15707.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3943	3943	3943	3943	3943	
5°	3943	3925	3878	3911	3900	374
15°	3750	3711	3590	3522	3486	1057
25°	3404	3290	3054	2908	2854	1566
35°	2933	2751	2437	2212	2134	1836
45°	2398	2159	1784	1531	1445	1852
55°	1823	1545	1160	946	878	1629
65°	1231	942	621	500	489	1221
75°	656	407	285	260	257	694
85°	153	78	68	68	68	176
90°	2	30	80	75	78	15
95°	120	142	146	146	142	133
105°	493	499	504	508	508	520
115°	917	930	926	924	917	907
125°	1334	1354	1348	1340	1338	1192
135°	1725	1750	1755	1753	1746	1333
145°	2094	2110	2124	2126	2117	1308
155°	2394	2401	2408	2420	2413	1102
165°	2605	2602	2602	2619	2607	735
175°	2710	2704	2699	2716	2702	258
180°	2716	2716	2716	2716	2716	

TEST NUMBER: P924629

CATALOG NUMBER: DFN2DIP-HX4F0-100D090US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3942.9	3942.9	3942.9	3942.9	3942.9
2.5°	3960.6	3942.9	3903.5	3939.4	3932.3
5°	3942.9	3925.0	3878.5	3910.7	3900.0
7.5°	3910.7	3889.5	3839.5	3853.5	3835.7
10°	3867.9	3842.9	3771.7	3760.8	3739.6
12.5°	3814.6	3782.3	3685.8	3664.6	3625.2
15°	3750.2	3710.8	3589.6	3521.9	3486.3
17.5°	3675.2	3618.0	3468.2	3389.8	3332.6
20°	3589.6	3518.1	3339.8	3250.9	3172.0
22.5°	3496.9	3414.7	3207.6	3086.6	3033.1
25°	3404.2	3289.9	3054.3	2908.2	2854.5
27.5°	3293.6	3172.0	2911.6	2743.9	2661.8
30°	3175.9	3039.9	2754.5	2572.8	2476.3
32.5°	3061.6	2897.2	2605.0	2390.7	2301.3
35°	2933.2	2751.1	2437.3	2212.4	2133.6
37.5°	2808.3	2611.8	2280.2	2033.7	1944.7
40°	2676.2	2462.3	2115.9	1862.6	1769.9
42.5°	2540.6	2312.3	1952.0	1687.7	1598.7
45°	2397.9	2158.6	1784.3	1530.6	1445.0
47.5°	2262.4	2009.1	1623.7	1370.0	1291.7
50°	2112.4	1859.2	1466.6	1220.2	1145.6
52.5°	1965.9	1698.3	1316.7	1081.2	1013.4
55°	1823.2	1545.0	1159.6	945.7	877.9
57.5°	1677.1	1391.6	1020.7	820.7	763.6
60°	1527.2	1241.7	874.2	692.4	635.3
62.5°	1381.0	1095.6	749.2	578.1	549.7
65°	1231.1	941.9	620.9	499.7	488.7
67.5°	1088.4	799.2	499.7	438.7	428.2
70°	938.4	660.3	413.7	378.2	363.9
72.5°	795.7	531.5	346.0	317.6	310.4
75°	656.4	406.6	285.4	260.4	257.0
77.5°	517.5	288.9	224.9	210.5	203.3
80°	388.8	207.1	171.1	157.1	157.1
82.5°	271.0	139.3	117.7	110.6	110.6
85°	153.3	78.3	67.7	67.7	67.7
87.5°	57.1	28.4	28.4	25.0	25.0
90°	2.5	29.5	80.2	75.3	77.8
92.5°	50.8	68.8	71.3	73.6	73.6
95°	119.5	142.4	146.5	146.5	142.4
97.5°	198.9	220.2	229.2	229.2	229.2
100°	290.6	309.5	316.0	316.0	313.6
102.5°	387.2	401.2	410.1	412.6	410.1
105°	492.8	499.3	504.3	508.4	508.4
107.5°	597.6	607.4	607.4	609.0	597.6
110°	699.1	712.3	712.3	712.3	705.7

TEST NUMBER: P924629

CATALOG NUMBER: DFN2DIP-HX4F0-100D090US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	808.8	822.7	820.2	813.8	808.8
115°	916.9	930.0	925.9	923.5	916.9
117.5°	1024.1	1042.1	1030.7	1024.1	1017.5
120°	1132.2	1150.1	1132.2	1132.2	1124.8
122.5°	1230.4	1253.4	1241.9	1235.3	1230.4
125°	1333.6	1354.0	1347.5	1340.1	1337.7
127.5°	1434.2	1459.6	1450.7	1440.8	1434.2
130°	1528.4	1557.9	1553.8	1548.8	1539.9
132.5°	1634.0	1656.9	1658.5	1647.1	1640.6
135°	1724.8	1750.2	1755.2	1752.7	1746.2
137.5°	1826.3	1846.8	1851.0	1849.3	1839.5
140°	1915.6	1936.0	1947.5	1947.5	1938.5
142.5°	2007.3	2027.7	2034.3	2036.8	2027.7
145°	2094.1	2110.4	2123.5	2126.0	2117.0
147.5°	2171.9	2192.3	2202.1	2206.2	2197.3
150°	2252.1	2266.0	2275.0	2282.3	2275.0
152.5°	2323.3	2337.2	2348.7	2357.7	2348.7
155°	2394.5	2401.0	2408.5	2419.9	2412.6
157.5°	2455.9	2460.8	2464.9	2481.3	2469.8
160°	2510.7	2515.7	2518.2	2532.0	2522.2
162.5°	2561.5	2561.5	2564.0	2579.5	2568.1
165°	2604.9	2602.4	2602.4	2618.8	2607.4
167.5°	2644.2	2636.9	2636.9	2653.2	2641.7
170°	2673.7	2667.1	2664.7	2681.0	2667.1
172.5°	2694.1	2687.6	2685.1	2701.5	2687.6
175°	2710.5	2703.9	2699.1	2715.5	2701.5
177.5°	2719.5	2713.0	2708.0	2722.0	2708.0
180°	2715.5	2715.5	2715.5	2715.5	2715.5

TEST NUMBER: P924629

CATALOG NUMBER: DFN2DIP-HX4F0-100D090US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.04	11.88	11.99	12.84	14.09	7.01	7.86	7.96	8.82	10.07
	3H	12.72	13.47	13.68	14.44	15.72	8.20	8.96	9.16	9.93	11.20
	4H	13.33	14.04	14.30	15.02	16.30	8.66	9.37	9.63	10.34	11.62
	6H	13.75	14.41	14.74	15.39	16.68	8.98	9.64	9.96	10.61	11.91
	8H	13.88	14.50	14.87	15.50	16.79	9.07	9.70	10.06	10.69	11.98
	12H	13.94	14.53	14.94	15.52	16.84	9.12	9.71	10.11	10.70	12.01
4H	2H	11.06	11.77	12.04	12.75	14.03	7.61	8.32	8.59	9.30	10.58
	3H	12.89	13.48	13.88	14.49	15.78	8.96	9.56	9.95	10.56	11.85
	4H	13.58	14.13	14.58	15.12	16.44	9.51	10.05	10.51	11.05	12.37
	6H	14.10	14.57	15.11	15.59	16.90	9.93	10.40	10.94	11.42	12.74
	8H	14.28	14.71	15.29	15.73	17.06	10.07	10.50	11.08	11.51	12.84
	12H	14.37	14.77	15.40	15.79	17.13	10.13	10.52	11.16	11.55	12.89
8H	4H	13.55	13.99	14.56	15.00	16.33	9.79	10.23	10.81	11.24	12.57
	6H	14.12	14.48	15.16	15.54	16.86	10.32	10.67	11.35	11.73	13.06
	8H	14.34	14.65	15.38	15.70	17.04	10.51	10.82	11.55	11.87	13.21
	12H	14.48	14.76	15.52	15.79	17.18	10.63	10.91	11.68	11.94	13.33
12H	4H	13.51	13.90	14.54	14.93	16.26	9.80	10.19	10.83	11.22	12.56
	6H	14.10	14.41	15.14	15.45	16.80	10.37	10.68	11.41	11.72	13.07
	8H	14.32	14.60	15.36	15.63	17.02	10.58	10.86	11.62	11.89	13.28