

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928246

Luminaire Tested: DFN2DIP-HX4F0-060D050US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928246
REPORT IS A COMBINATION OF REPORTS P900842 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D050US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7959.6 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 91.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928246

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928246

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1460	1460	1460
5°	1463	1437	1446
10°	1448	1409	1399
15°	1429	1363	1327
20°	1402	1299	1238
25°	1376	1227	1151
30°	1339	1153	1042
35°	1304	1074	946
40°	1268	992	836
45°	1226	901	736
50°	1183	809	639
55°	1138	711	545
60°	1085	608	449
65°	1025	504	404
70°	952	406	366
75°	861	359	333
80°	728	301	289
85°	509	202	217

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1226 cd/sqm

TEST NUMBER: P928246

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	2.3
10°-20°	505.3	6.3
20°-30°	709.4	8.9
30°-40°	773.3	9.7
40°-50°	710.8	8.9
50°-60°	558.2	7.0
60°-70°	363.3	4.6
70°-80°	187.0	2.3
80°-90°	50.1	0.6
90°-100°	44.1	0.6
100°-110°	164.3	2.1
110°-120°	435.7	5.5
120°-130°	722.6	9.1
130°-140°	767.6	9.6
140°-150°	713.4	9.0
150°-160°	573.6	7.2
160°-170°	369.6	4.6
170°-180°	127.2	1.6
0°-30°	1398.8	17.6
0°-40°	2172.1	27.3
0°-60°	3441.1	43.2
0°-90°	4041.5	50.8
90°-120°	644.1	8.1
90°-150°	2847.7	35.8
90°-180°	3918.0	49.2
0°-180°	7959.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1955	1932	1948	1943	186
15°	1868	1848	1788	1754	1736	526
25°	1696	1639	1521	1449	1422	780
35°	1461	1370	1214	1102	1063	914
45°	1194	1075	889	762	720	922
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	202	142	130	128	346
85°	76	39	34	34	34	88
90°	1	12	19	24	26	7
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	572	597	149	79	547
125°	786	799	817	824	827	701
135°	973	988	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1251	1244	573
165°	1309	1304	1306	1313	1306	370
175°	1339	1332	1334	1341	1332	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P928246

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.0	1964.0	1964.0	1964.0	1964.0
2.5°	1972.9	1964.0	1944.4	1962.3	1958.7
5°	1964.0	1955.1	1931.9	1948.0	1942.7
7.5°	1948.0	1937.4	1912.5	1919.5	1910.6
10°	1926.6	1914.2	1878.8	1873.3	1862.7
12.5°	1900.1	1884.0	1835.9	1825.4	1805.8
15°	1868.0	1848.4	1788.0	1754.3	1736.5
17.5°	1830.7	1802.2	1727.5	1688.5	1660.0
20°	1788.0	1752.4	1663.6	1619.2	1580.0
22.5°	1741.8	1700.9	1597.8	1537.4	1510.8
25°	1695.7	1638.7	1521.4	1448.6	1421.9
27.5°	1640.6	1580.0	1450.3	1366.8	1325.9
30°	1581.9	1514.2	1372.1	1281.5	1233.5
32.5°	1525.0	1443.2	1297.6	1190.9	1146.3
35°	1461.1	1370.4	1214.1	1102.0	1062.8
37.5°	1398.8	1300.9	1135.8	1013.0	968.7
40°	1333.0	1226.5	1053.9	927.7	881.6
42.5°	1265.5	1151.8	972.3	840.6	796.4
45°	1194.4	1075.2	888.8	762.4	719.8
47.5°	1126.9	1000.8	808.8	682.5	643.4
50°	1052.3	926.1	730.5	607.8	570.6
52.5°	979.2	845.9	655.9	538.6	504.8
55°	908.2	769.6	577.6	471.1	437.3
57.5°	835.4	693.2	508.4	408.8	380.3
60°	760.7	618.6	435.4	344.9	316.4
62.5°	687.9	545.8	373.2	288.0	273.8
65°	613.2	469.2	309.3	248.9	243.5
67.5°	542.1	398.1	248.9	218.6	213.3
70°	467.4	328.8	206.1	188.4	181.2
72.5°	396.4	264.8	172.3	158.2	154.6
75°	327.0	202.5	142.2	129.7	128.1
77.5°	257.8	143.9	112.0	104.9	101.3
80°	193.6	103.1	85.2	78.2	78.2
82.5°	135.0	69.4	58.6	55.0	55.0
85°	76.3	39.0	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.1
100°	171.2	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.6	70.6
105°	294.0	323.1	59.0	69.6	73.5
107.5°	362.7	386.7	61.0	71.5	75.5
110°	428.5	448.7	169.3	72.5	76.3

TEST NUMBER: P928246

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.3	507.7	491.3	74.4	77.4
115°	556.1	572.5	596.7	149.0	79.4
117.5°	613.1	632.4	649.0	510.5	257.2
120°	676.9	691.4	708.8	720.5	589.9
122.5°	731.0	746.5	765.9	771.7	772.8
125°	786.1	798.8	817.2	823.9	826.8
127.5°	836.4	850.0	864.6	874.2	875.2
130°	883.9	899.4	909.9	920.6	919.7
132.5°	932.3	944.9	955.4	964.2	963.2
135°	972.9	988.4	997.0	1006.8	1004.8
137.5°	1015.3	1027.0	1036.7	1046.4	1043.5
140°	1056.9	1064.8	1075.3	1084.0	1079.3
142.5°	1091.9	1098.7	1111.2	1118.9	1114.0
145°	1128.6	1127.6	1144.0	1150.8	1145.9
147.5°	1160.4	1157.5	1174.0	1178.8	1175.0
150°	1191.4	1184.7	1200.1	1205.9	1201.1
152.5°	1217.5	1209.8	1224.3	1230.1	1223.3
155°	1242.6	1234.0	1245.6	1251.4	1243.7
157.5°	1262.9	1255.2	1264.0	1270.8	1262.9
160°	1280.4	1274.6	1280.4	1286.1	1279.4
162.5°	1295.8	1290.1	1294.8	1301.7	1292.9
165°	1309.3	1303.6	1306.5	1313.2	1306.5
167.5°	1320.0	1314.2	1317.2	1323.9	1315.2
170°	1328.7	1322.9	1324.9	1331.6	1322.9
172.5°	1334.5	1328.7	1330.7	1337.5	1328.7
175°	1339.4	1332.5	1334.5	1341.3	1331.6
177.5°	1341.3	1334.5	1335.5	1342.3	1333.6
180°	1336.4	1336.4	1336.4	1336.4	1336.4

TEST NUMBER: P928246

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.54	9.37	9.49	10.34	11.60	4.51	5.35	5.47	6.31	7.58
	3H	10.21	10.96	11.18	11.94	13.23	5.70	6.45	6.67	7.42	8.71
	4H	10.82	11.53	11.81	12.51	13.81	6.15	6.86	7.13	7.84	9.13
	6H	11.25	11.90	12.24	12.88	14.19	6.48	7.13	7.47	8.11	9.42
	8H	11.37	11.99	12.37	13.00	14.30	6.57	7.19	7.57	8.19	9.49
	12H	11.44	12.02	12.44	13.02	14.35	6.61	7.20	7.61	8.20	9.52
4H	2H	8.56	9.26	9.54	10.24	11.54	5.11	5.81	6.09	6.79	8.09
	3H	10.39	10.97	11.38	11.98	13.29	6.46	7.05	7.46	8.06	9.36
	4H	11.08	11.62	12.08	12.62	13.95	7.01	7.54	8.01	8.55	9.88
	6H	11.60	12.06	12.61	13.08	14.41	7.43	7.89	8.45	8.92	10.25
	8H	11.77	12.20	12.79	13.22	14.57	7.56	7.99	8.58	9.01	10.35
	12H	11.87	12.26	12.90	13.29	14.64	7.63	8.01	8.66	9.05	10.40
8H	4H	11.05	11.48	12.07	12.50	13.84	7.29	7.72	8.31	8.74	10.08
	6H	11.62	11.97	12.66	13.03	14.37	7.81	8.17	8.85	9.23	10.57
	8H	11.83	12.15	12.88	13.19	14.55	8.00	8.32	9.05	9.36	10.72
	12H	11.97	12.25	13.02	13.29	14.69	8.12	8.40	9.18	9.44	10.84
12H	4H	11.00	11.39	12.04	12.42	13.77	7.29	7.68	8.33	8.72	10.07
	6H	11.59	11.90	12.64	12.95	14.31	7.86	8.17	8.91	9.22	10.58
	8H	11.81	12.09	12.87	13.13	14.53	8.07	8.35	9.12	9.39	10.79