

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928260

Luminaire Tested: DFN2DIP-HX4F0-060D090US927-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928260
REPORT IS A COMBINATION OF REPORTS P900913 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D090US927-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11761.2 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928260

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928260

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1375	1375	1375
5°	1377	1356	1365
10°	1366	1338	1346
15°	1346	1316	1318
20°	1319	1285	1288
25°	1292	1249	1254
30°	1259	1215	1211
35°	1227	1175	1165
40°	1187	1135	1121
45°	1148	1094	1076
50°	1105	1052	1025
55°	1060	1002	977
60°	1010	944	923
65°	954	884	858
70°	884	810	789
75°	786	722	726
80°	669	609	603
85°	485	415	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1235 cd/sqm

TEST NUMBER: P928260

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	1.5
10°-20°	489.7	4.2
20°-30°	719.6	6.1
30°-40°	835.8	7.1
40°-50°	834.7	7.1
50°-60°	727.9	6.2
60°-70°	538.1	4.6
70°-80°	304.4	2.6
80°-90°	84.6	0.7
90°-100°	79.3	0.7
100°-110°	295.7	2.5
110°-120°	784.2	6.7
120°-130°	1300.7	11.1
130°-140°	1381.7	11.7
140°-150°	1284.1	10.9
150°-160°	1032.4	8.8
160°-170°	665.2	5.7
170°-180°	229.0	1.9
0°-30°	1383.3	11.8
0°-40°	2219.1	18.9
0°-60°	3781.7	32.2
0°-90°	4708.7	40.0
90°-120°	1159.3	9.9
90°-150°	5125.8	43.6
90°-180°	7052.0	60.0
0°-180°	11761.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1822	1837	1833	176
15°	1760	1750	1726	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1374	1357	1328	1317	1308	858
45°	1118	1106	1079	1060	1053	863
55°	846	836	814	793	784	757
65°	571	560	542	526	517	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	81
90°	2	21	35	44	47	11
95°	113	56	68	77	75	134
105°	529	582	106	125	132	565
115°	1001	1030	1074	268	143	985
125°	1415	1438	1471	1483	1488	1262
135°	1751	1779	1795	1812	1809	1353
145°	2032	2030	2059	2071	2063	1271
155°	2237	2221	2242	2252	2239	1031
165°	2357	2346	2352	2364	2352	666
175°	2411	2399	2402	2414	2397	229
180°	2406	2406	2406	2406	2406	

TEST NUMBER: P928260

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.0	1849.0	1849.0	1849.0	1849.0
2.5°	1859.8	1850.9	1831.3	1849.0	1845.6
5°	1849.0	1842.0	1822.4	1836.6	1833.2
7.5°	1836.6	1826.0	1806.4	1820.7	1817.2
10°	1817.2	1804.7	1783.3	1797.5	1792.2
12.5°	1790.4	1779.8	1758.5	1767.3	1763.8
15°	1760.1	1749.6	1726.4	1733.6	1724.7
17.5°	1722.8	1712.3	1689.1	1697.9	1689.1
20°	1681.9	1671.4	1646.4	1651.7	1644.7
22.5°	1641.2	1625.1	1601.9	1601.9	1598.3
25°	1593.0	1578.9	1548.7	1552.1	1548.7
27.5°	1539.6	1527.2	1504.2	1498.9	1490.1
30°	1486.5	1472.1	1445.6	1440.3	1433.0
32.5°	1429.5	1418.9	1390.4	1379.7	1372.5
35°	1374.4	1356.7	1328.2	1317.4	1308.5
37.5°	1312.2	1296.1	1267.7	1255.2	1246.3
40°	1248.2	1233.9	1205.4	1189.6	1182.4
42.5°	1185.9	1171.6	1143.3	1125.4	1114.8
45°	1118.5	1105.9	1079.2	1059.8	1052.6
47.5°	1052.6	1040.1	1011.7	992.1	981.4
50°	983.2	974.3	949.4	924.5	915.6
52.5°	915.6	903.2	880.1	860.6	848.2
55°	846.4	835.6	814.3	793.0	784.2
57.5°	777.0	768.2	745.0	723.7	716.4
60°	707.6	700.6	675.7	656.1	650.8
62.5°	640.0	627.6	609.8	592.1	585.0
65°	570.8	560.1	542.4	526.3	517.4
67.5°	499.7	490.6	474.8	462.4	455.2
70°	433.9	426.7	410.7	398.2	391.2
72.5°	366.3	359.2	350.3	337.9	332.6
75°	298.6	295.3	286.1	275.6	279.2
77.5°	238.2	231.1	227.5	222.2	216.9
80°	177.9	176.0	172.4	167.1	163.5
82.5°	120.9	120.9	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.8
97.5°	203.6	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.2	113.1	116.6
102.5°	422.9	419.6	102.7	121.7	127.1
105°	529.1	581.5	106.2	125.3	132.3
107.5°	652.8	696.2	109.8	128.8	135.8
110°	771.2	807.6	304.7	130.6	137.5

TEST NUMBER: P928260

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	882.6	913.8	884.3	133.9	139.3
115°	1000.9	1030.4	1074.0	268.1	142.8
117.5°	1103.6	1138.3	1168.0	919.0	463.0
120°	1218.5	1244.5	1276.0	1296.8	1061.8
122.5°	1315.9	1343.8	1378.7	1389.0	1390.9
125°	1415.1	1437.8	1470.9	1483.1	1488.2
127.5°	1505.6	1530.0	1556.3	1573.6	1575.3
130°	1591.0	1618.9	1637.9	1657.1	1655.5
132.5°	1678.0	1700.7	1719.7	1735.5	1733.8
135°	1751.2	1779.1	1794.6	1812.2	1808.7
137.5°	1827.7	1848.5	1866.1	1883.5	1878.3
140°	1902.5	1916.6	1935.6	1951.3	1942.6
142.5°	1965.3	1977.5	2000.0	2013.9	2005.3
145°	2031.5	2029.6	2059.2	2071.4	2062.7
147.5°	2088.7	2083.6	2113.1	2121.8	2115.0
150°	2144.6	2132.4	2160.3	2170.6	2161.9
152.5°	2191.5	2177.6	2203.7	2214.2	2202.0
155°	2236.8	2221.2	2242.1	2252.4	2238.6
157.5°	2273.4	2259.5	2275.2	2287.4	2273.4
160°	2304.7	2294.2	2304.7	2315.1	2302.9
162.5°	2332.4	2322.1	2330.8	2343.0	2327.3
165°	2356.8	2346.5	2351.7	2363.9	2351.7
167.5°	2376.1	2365.5	2370.9	2383.0	2367.4
170°	2391.8	2381.2	2384.7	2396.9	2381.2
172.5°	2402.1	2391.8	2395.2	2407.4	2391.8
175°	2410.8	2398.6	2402.1	2414.3	2396.9
177.5°	2414.3	2402.1	2404.0	2416.2	2400.5
180°	2405.6	2405.6	2405.6	2405.6	2405.6

TEST NUMBER: P928260

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.38	8.16	8.42	9.20	10.61	6.95	7.73	7.99	8.77	10.18
	3H	9.04	9.73	10.08	10.79	12.21	8.56	9.26	9.61	10.31	11.74
	4H	9.62	10.28	10.68	11.34	12.77	9.15	9.81	10.21	10.86	12.30
	6H	10.02	10.63	11.09	11.69	13.13	9.54	10.15	10.61	11.21	12.65
	8H	10.12	10.70	11.19	11.77	13.21	9.64	10.22	10.72	11.30	12.74
	12H	10.17	10.72	11.24	11.79	13.25	9.68	10.24	10.76	11.30	12.77
4H	2H	7.83	8.50	8.90	9.55	10.98	7.49	8.15	8.56	9.21	10.64
	3H	9.69	10.25	10.77	11.33	12.77	9.30	9.85	10.37	10.94	12.38
	4H	10.41	10.91	11.49	11.99	13.45	10.00	10.51	11.08	11.58	13.05
	6H	10.92	11.35	12.01	12.45	13.91	10.51	10.94	11.60	12.04	13.50
	8H	11.07	11.47	12.15	12.56	14.04	10.65	11.06	11.74	12.15	13.62
	12H	11.13	11.50	12.24	12.60	14.09	10.71	11.08	11.82	12.18	13.66
8H	4H	10.60	11.00	11.68	12.09	13.57	10.24	10.64	11.32	11.73	13.21
	6H	11.23	11.56	12.34	12.69	14.17	10.86	11.20	11.97	12.33	13.80
	8H	11.45	11.74	12.56	12.85	14.35	11.08	11.37	12.19	12.48	13.98
	12H	11.57	11.83	12.70	12.94	14.47	11.19	11.45	12.31	12.56	14.09
12H	4H	10.58	10.95	11.68	12.05	13.53	10.23	10.59	11.33	11.70	13.18
	6H	11.25	11.55	12.37	12.66	14.16	10.90	11.20	12.02	12.31	13.80
	8H	11.49	11.75	12.62	12.86	14.39	11.14	11.39	12.26	12.50	14.03

END OF REPORT