

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902861

Luminaire Tested: DFN2DIP-PN2F0-020D050US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902861
REPORT IS A COMBINATION OF REPORTS P901011 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D050US830-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6531.9 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902861

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902861

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1589	1589	1589
5°	1589	1563	1575
10°	1573	1539	1551
15°	1547	1510	1515
20°	1514	1471	1479
25°	1480	1426	1437
30°	1438	1383	1385
35°	1399	1334	1330
40°	1350	1284	1277
45°	1302	1233	1223
50°	1249	1180	1161
55°	1193	1118	1102
60°	1130	1046	1036
65°	1061	971	958
70°	973	878	873
75°	852	768	791
80°	706	627	641
85°	477	396	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1460 cd/sqm

TEST NUMBER: P902861

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.1
10°-20°	194.2	3.0
20°-30°	285.5	4.4
30°-40°	331.5	5.1
40°-50°	331.1	5.1
50°-60°	288.7	4.4
60°-70°	213.4	3.3
70°-80°	120.8	1.8
80°-90°	34.7	0.5
90°-100°	52.5	0.8
100°-110°	195.5	3.0
110°-120°	518.5	7.9
120°-130°	860.0	13.2
130°-140°	913.5	14.0
140°-150°	849.0	13.0
150°-160°	682.6	10.4
160°-170°	439.8	6.7
170°-180°	151.4	2.3
0°-30°	548.7	8.4
0°-40°	880.3	13.5
0°-60°	1500.2	23.0
0°-90°	1869.0	28.6
90°-120°	766.5	11.7
90°-150°	3389.0	51.9
90°-180°	4663.0	71.4
0°-180°	6531.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	14	23	29	31	6
95°	75	37	45	51	50	89
105°	350	384	70	83	88	374
115°	662	681	710	177	94	651
125°	936	951	972	980	984	834
135°	1158	1176	1186	1198	1196	894
145°	1343	1342	1361	1370	1364	840
155°	1479	1469	1482	1489	1480	681
165°	1558	1551	1555	1563	1555	440
175°	1594	1586	1588	1596	1585	152
180°	1590	1590	1590	1590	1590	

TEST NUMBER: P902861

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	1.1	13.8	23.0	28.8	31.0
92.5°	28.8	24.2	27.6	30.0	31.0
95°	74.7	36.8	44.9	50.7	49.5
97.5°	134.6	40.3	58.6	62.2	63.2
100°	203.8	46.1	65.6	74.7	77.1
102.5°	279.7	277.4	68.0	80.5	84.1
105°	349.9	384.5	70.2	82.8	87.5
107.5°	431.6	460.2	72.6	85.1	89.8
110°	509.9	534.0	201.4	86.3	90.9

TEST NUMBER: P902861

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.5	604.2	584.7	88.6	92.1
115°	661.8	681.3	710.1	177.3	94.4
117.5°	729.6	752.6	772.3	607.6	306.1
120°	805.6	822.8	843.6	857.4	702.0
122.5°	870.0	888.4	911.5	918.4	919.6
125°	935.6	950.6	972.5	980.5	984.0
127.5°	995.4	1011.5	1029.0	1040.4	1041.5
130°	1051.9	1070.4	1082.9	1095.6	1094.6
132.5°	1109.5	1124.5	1137.0	1147.5	1146.3
135°	1157.8	1176.3	1186.5	1198.2	1195.8
137.5°	1208.3	1222.2	1233.8	1245.3	1241.9
140°	1257.8	1267.2	1279.7	1290.1	1284.4
142.5°	1299.4	1307.5	1322.4	1331.5	1325.8
145°	1343.1	1341.9	1361.4	1369.5	1363.8
147.5°	1381.0	1377.5	1397.1	1402.9	1398.4
150°	1417.9	1409.9	1428.2	1435.1	1429.4
152.5°	1448.9	1439.7	1457.0	1464.0	1455.9
155°	1478.8	1468.6	1482.3	1489.2	1480.1
157.5°	1503.0	1493.8	1504.2	1512.3	1503.0
160°	1523.8	1516.8	1523.8	1530.6	1522.6
162.5°	1542.1	1535.3	1541.0	1549.1	1538.7
165°	1558.2	1551.4	1554.8	1562.8	1554.8
167.5°	1570.9	1564.0	1567.5	1575.6	1565.2
170°	1581.3	1574.3	1576.7	1584.7	1574.3
172.5°	1588.2	1581.3	1583.7	1591.7	1581.3
175°	1593.9	1585.8	1588.2	1596.2	1584.7
177.5°	1596.2	1588.2	1589.4	1597.4	1587.1
180°	1590.4	1590.4	1590.4	1590.4	1590.4

TEST NUMBER: P902861

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.36	7.05	7.48	8.17	9.72	5.92	6.62	7.04	7.73	9.28
	3H	7.98	8.61	9.11	9.73	11.29	7.51	8.13	8.63	9.25	10.82
	4H	8.55	9.14	9.69	10.27	11.84	8.07	8.66	9.21	9.79	11.35
	6H	8.93	9.47	10.07	10.60	12.18	8.44	8.99	9.59	10.11	11.69
	8H	9.02	9.54	10.17	10.68	12.25	8.53	9.05	9.68	10.19	11.77
	12H	9.05	9.55	10.21	10.68	12.28	8.56	9.05	9.72	10.19	11.78
4H	2H	6.79	7.38	7.94	8.50	10.07	6.44	7.03	7.59	8.16	9.72
	3H	8.61	9.11	9.77	10.26	11.84	8.22	8.71	9.37	9.86	11.44
	4H	9.31	9.76	10.46	10.90	12.50	8.89	9.35	10.05	10.49	12.09
	6H	9.79	10.18	10.95	11.34	12.93	9.37	9.76	10.53	10.92	12.51
	8H	9.93	10.29	11.09	11.45	13.05	9.50	9.87	10.66	11.02	12.63
	12H	9.98	10.31	11.16	11.48	13.09	9.55	9.88	10.73	11.04	12.66
8H	4H	9.48	9.84	10.64	11.00	12.60	9.11	9.47	10.27	10.63	12.23
	6H	10.08	10.38	11.26	11.57	13.18	9.70	10.00	10.88	11.20	12.80
	8H	10.28	10.55	11.47	11.72	13.34	9.90	10.16	11.09	11.34	12.96
	12H	10.39	10.62	11.58	11.79	13.45	10.00	10.23	11.19	11.40	13.06
12H	4H	9.45	9.78	10.63	10.95	12.56	9.09	9.42	10.27	10.59	12.20
	6H	10.10	10.36	11.29	11.54	13.16	9.74	10.00	10.92	11.17	12.80
	8H	10.32	10.55	11.51	11.72	13.38	9.95	10.18	11.14	11.35	13.01

END OF REPORT