

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928278

Luminaire Tested: DFN2DIP-HX4F0-070D040US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928278
REPORT IS A COMBINATION OF REPORTS P900826 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D040US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7848.7 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 96.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928278

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928278

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	32	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1704	1704	1704
5°	1707	1677	1688
10°	1690	1644	1633
15°	1667	1590	1548
20°	1636	1515	1444
25°	1605	1431	1343
30°	1563	1345	1216
35°	1521	1253	1104
40°	1479	1157	975
45°	1430	1051	859
50°	1380	944	745
55°	1327	829	636
60°	1266	710	523
65°	1196	588	471
70°	1111	474	426
75°	1004	418	388
80°	850	352	337
85°	594	236	254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1430 cd/sqm

TEST NUMBER: P928278

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	2.7
10°-20°	589.5	7.5
20°-30°	827.7	10.5
30°-40°	902.2	11.5
40°-50°	829.2	10.6
50°-60°	651.2	8.3
60°-70°	423.9	5.4
70°-80°	218.2	2.8
80°-90°	57.6	0.7
90°-100°	35.2	0.4
100°-110°	131.4	1.7
110°-120°	348.6	4.4
120°-130°	578.1	7.4
130°-140°	614.1	7.8
140°-150°	570.7	7.3
150°-160°	458.8	5.8
160°-170°	295.7	3.8
170°-180°	101.8	1.3
0°-30°	1631.9	20.8
0°-40°	2534.1	32.3
0°-60°	4014.6	51.2
0°-90°	4714.2	60.1
90°-120°	515.2	6.6
90°-150°	2278.1	29.0
90°-180°	3134.0	39.9
0°-180°	7848.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2291	2291	2291	2291	2291	
5°	2291	2281	2254	2273	2266	217
15°	2179	2156	2086	2047	2026	614
25°	1978	1912	1775	1690	1659	910
35°	1704	1599	1416	1286	1240	1067
45°	1394	1254	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	715	547	361	290	284	709
75°	382	236	166	151	149	403
85°	89	46	39	39	39	102
90°	1	9	15	19	21	7
95°	50	25	30	34	33	59
105°	235	258	47	56	59	251
115°	445	458	477	119	64	438
125°	629	639	654	659	662	561
135°	778	791	798	805	804	601
145°	903	902	915	921	917	565
155°	994	987	996	1001	995	458
165°	1048	1043	1045	1051	1045	296
175°	1071	1066	1068	1073	1065	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P928278

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.3	2291.3	2291.3	2291.3	2291.3
2.5°	2301.6	2291.3	2268.4	2289.4	2285.2
5°	2291.3	2281.0	2254.0	2272.6	2266.5
7.5°	2272.6	2260.3	2231.3	2239.4	2229.1
10°	2247.8	2233.3	2191.9	2185.5	2173.2
12.5°	2216.7	2198.0	2142.0	2129.6	2106.7
15°	2179.3	2156.5	2086.0	2046.7	2026.0
17.5°	2135.8	2102.6	2015.5	1969.9	1936.7
20°	2086.0	2044.5	1940.9	1889.2	1843.4
22.5°	2032.2	1984.4	1864.1	1793.6	1762.7
25°	1978.3	1911.8	1775.0	1690.0	1658.8
27.5°	1914.0	1843.4	1692.0	1594.6	1546.9
30°	1845.6	1766.6	1600.7	1495.1	1439.1
32.5°	1779.1	1683.7	1513.8	1389.3	1337.4
35°	1704.5	1598.7	1416.4	1285.7	1240.0
37.5°	1632.0	1517.8	1325.1	1181.8	1130.2
40°	1555.2	1430.9	1229.6	1082.4	1028.5
42.5°	1476.4	1343.8	1134.3	980.7	929.1
45°	1393.5	1254.4	1036.9	889.5	839.8
47.5°	1314.7	1167.6	943.6	796.2	750.7
50°	1227.6	1080.4	852.3	709.1	665.8
52.5°	1142.5	986.9	765.2	628.3	588.9
55°	1059.5	897.8	673.8	549.6	510.2
57.5°	974.6	808.7	593.1	476.9	443.8
60°	887.5	721.6	508.0	402.4	369.2
62.5°	802.5	636.7	435.4	336.0	319.4
65°	715.4	547.4	360.8	290.4	284.0
67.5°	632.5	464.4	290.4	254.9	248.8
70°	545.4	383.6	240.5	219.8	211.4
72.5°	462.4	308.9	201.1	184.6	180.4
75°	381.5	236.3	165.8	151.4	149.4
77.5°	300.7	167.8	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.5	80.9	68.4	64.2	64.2
85°	89.1	45.5	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	0.7	9.3	15.4	19.4	20.8
92.5°	19.4	16.2	18.5	20.1	20.8
95°	50.2	24.7	30.1	34.1	33.3
97.5°	90.5	27.1	39.4	41.8	42.5
100°	136.9	31.0	44.1	50.2	51.8
102.5°	187.9	186.5	45.6	54.1	56.5
105°	235.1	258.4	47.2	55.7	58.8
107.5°	290.1	309.4	48.8	57.3	60.4
110°	342.8	358.9	135.4	58.1	61.1

TEST NUMBER: P928278

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	406.1	393.0	59.6	61.9
115°	444.8	457.9	477.3	119.1	63.5
117.5°	490.5	505.9	519.2	408.4	205.8
120°	541.6	553.1	567.1	576.4	472.0
122.5°	584.8	597.2	612.8	617.4	618.2
125°	628.9	639.1	653.7	659.2	661.5
127.5°	669.2	680.0	691.7	699.4	700.1
130°	707.1	719.5	727.9	736.5	735.8
132.5°	745.7	755.9	764.4	771.3	770.6
135°	778.3	790.7	797.6	805.4	803.9
137.5°	812.3	821.5	829.4	837.1	834.8
140°	845.5	851.8	860.3	867.2	863.4
142.5°	873.5	878.9	888.9	895.0	891.2
145°	902.9	902.1	915.2	920.6	916.7
147.5°	928.3	926.0	939.2	943.0	940.0
150°	953.1	947.7	960.1	964.7	960.9
152.5°	974.0	967.8	979.4	984.1	978.7
155°	994.1	987.2	996.5	1001.1	994.9
157.5°	1010.4	1004.2	1011.2	1016.6	1010.4
160°	1024.3	1019.6	1024.3	1028.9	1023.5
162.5°	1036.6	1032.1	1035.9	1041.3	1034.4
165°	1047.5	1042.9	1045.2	1050.6	1045.2
167.5°	1056.1	1051.3	1053.8	1059.1	1052.2
170°	1063.0	1058.3	1059.9	1065.3	1058.3
172.5°	1067.6	1063.0	1064.6	1070.0	1063.0
175°	1071.4	1066.0	1067.6	1073.0	1065.3
177.5°	1073.0	1067.6	1068.4	1073.9	1066.9
180°	1069.2	1069.2	1069.2	1069.2	1069.2

TEST NUMBER: P928278

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.89	10.81	10.76	11.70	12.82	5.86	6.78	6.74	7.67	8.79
	3H	11.58	12.40	12.46	13.30	14.45	7.06	7.88	7.95	8.78	9.93
	4H	12.19	12.96	13.09	13.87	15.03	7.52	8.29	8.42	9.20	10.36
	6H	12.62	13.33	13.53	14.24	15.41	7.84	8.56	8.76	9.47	10.64
	8H	12.75	13.42	13.67	14.35	15.52	7.94	8.62	8.86	9.55	10.72
	12H	12.81	13.46	13.74	14.38	15.57	7.98	8.63	8.91	9.55	10.75
4H	2H	9.92	10.70	10.83	11.60	12.76	6.47	7.25	7.38	8.15	9.31
	3H	11.76	12.40	12.67	13.34	14.51	7.83	8.47	8.75	9.41	10.58
	4H	12.45	13.04	13.38	13.97	15.17	8.38	8.97	9.31	9.90	11.10
	6H	12.98	13.48	13.92	14.44	15.64	8.81	9.31	9.75	10.27	11.47
	8H	13.15	13.63	14.10	14.57	15.79	8.94	9.41	9.88	10.36	11.58
	12H	13.25	13.68	14.21	14.64	15.86	9.01	9.44	9.97	10.40	11.62
8H	4H	12.43	12.90	13.37	13.85	15.06	8.67	9.14	9.61	10.09	11.30
	6H	13.00	13.39	13.97	14.38	15.59	9.19	9.58	10.16	10.58	11.79
	8H	13.22	13.56	14.20	14.54	15.77	9.39	9.73	10.37	10.71	11.94
	12H	13.36	13.66	14.34	14.64	15.92	9.51	9.82	10.49	10.79	12.07
12H	4H	12.39	12.81	13.35	13.78	15.00	8.68	9.10	9.64	10.07	11.29
	6H	12.98	13.32	13.95	14.30	15.53	9.24	9.59	10.22	10.57	11.80
	8H	13.20	13.50	14.18	14.48	15.76	9.46	9.76	10.44	10.74	12.02