

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928288

Luminaire Tested: DFN2DIP-HX4F0-070D070US927-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928288
REPORT IS A COMBINATION OF REPORTS P900879 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D070US927-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10977.1 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928288

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928288

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1604	1604	1604
5°	1607	1582	1592
10°	1594	1561	1571
15°	1571	1535	1537
20°	1539	1500	1503
25°	1508	1457	1463
30°	1468	1418	1412
35°	1431	1371	1359
40°	1385	1324	1308
45°	1339	1276	1256
50°	1289	1227	1195
55°	1237	1169	1140
60°	1178	1101	1077
65°	1113	1031	1002
70°	1031	945	921
75°	917	842	846
80°	780	711	704
85°	567	485	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1339 cd/sqm

TEST NUMBER: P928288

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	1.8
10°-20°	571.3	5.2
20°-30°	839.5	7.6
30°-40°	975.1	8.9
40°-50°	973.8	8.9
50°-60°	849.2	7.7
60°-70°	627.7	5.7
70°-80°	355.2	3.2
80°-90°	97.1	0.9
90°-100°	61.7	0.6
100°-110°	230.0	2.1
110°-120°	610.0	5.6
120°-130°	1011.7	9.2
130°-140°	1074.6	9.8
140°-150°	998.8	9.1
150°-160°	803.0	7.3
160°-170°	517.4	4.7
170°-180°	178.1	1.6
0°-30°	1613.8	14.7
0°-40°	2588.9	23.6
0°-60°	4411.9	40.2
0°-90°	5491.9	50.0
90°-120°	901.6	8.2
90°-150°	3986.8	36.3
90°-180°	5485.0	50.0
0°-180°	10977.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2157	2157	2157	2157	2157	
5°	2157	2149	2126	2143	2139	205
15°	2054	2041	2014	2022	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1236	1228	1007
55°	988	975	950	925	915	883
65°	666	653	633	614	604	658
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	1	16	27	34	36	10
95°	88	43	53	60	58	104
105°	412	452	83	97	103	440
115°	778	801	835	208	111	766
125°	1101	1118	1144	1154	1158	982
135°	1362	1384	1396	1409	1407	1052
145°	1580	1579	1602	1611	1604	988
155°	1740	1728	1744	1752	1741	802
165°	1833	1825	1829	1838	1829	518
175°	1875	1866	1868	1878	1864	178
180°	1871	1871	1871	1871	1871	

TEST NUMBER: P928288

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.2	2157.2	2157.2	2157.2	2157.2
2.5°	2169.8	2159.4	2136.5	2157.2	2153.2
5°	2157.2	2149.1	2126.2	2142.7	2138.7
7.5°	2142.7	2130.3	2107.4	2124.2	2120.0
10°	2120.0	2105.5	2080.6	2097.1	2091.0
12.5°	2088.7	2076.5	2051.6	2061.9	2057.7
15°	2053.6	2041.2	2014.1	2022.5	2012.2
17.5°	2009.9	1997.7	1970.6	1981.0	1970.6
20°	1962.2	1949.9	1920.8	1927.0	1918.9
22.5°	1914.7	1896.0	1868.9	1868.9	1864.7
25°	1858.6	1842.0	1806.9	1810.8	1806.9
27.5°	1796.3	1781.8	1754.9	1748.7	1738.4
30°	1734.2	1717.5	1686.5	1680.3	1671.9
32.5°	1667.7	1655.4	1622.2	1609.7	1601.3
35°	1603.5	1582.8	1549.5	1537.0	1526.7
37.5°	1530.9	1512.2	1478.9	1464.4	1454.0
40°	1456.3	1439.5	1406.3	1387.8	1379.4
42.5°	1383.6	1366.9	1333.9	1313.0	1300.6
45°	1304.8	1290.3	1259.0	1236.4	1228.0
47.5°	1228.0	1213.5	1180.2	1157.3	1145.1
50°	1147.1	1136.7	1107.6	1078.6	1068.2
52.5°	1068.2	1053.8	1026.9	1004.0	989.4
55°	987.5	975.0	950.1	925.2	914.8
57.5°	906.5	896.1	869.1	844.2	835.9
60°	825.5	817.3	788.4	765.5	759.3
62.5°	746.7	732.2	711.5	690.9	682.5
65°	666.0	653.4	632.7	614.0	603.7
67.5°	583.0	572.5	553.9	539.4	531.0
70°	506.2	497.9	479.1	464.6	456.4
72.5°	427.4	419.0	408.7	394.2	388.0
75°	348.4	344.4	333.8	321.6	325.7
77.5°	278.0	269.6	265.4	259.2	253.1
80°	207.5	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	1.3	16.2	27.0	33.9	36.5
92.5°	33.9	28.4	32.5	35.2	36.5
95°	87.9	43.2	52.7	59.6	58.2
97.5°	158.3	47.4	69.0	73.2	74.4
100°	239.7	54.2	77.1	87.9	90.7
102.5°	328.9	326.4	79.9	94.7	98.8
105°	411.6	452.2	82.6	97.4	102.9
107.5°	507.7	541.5	85.4	100.2	105.7
110°	599.9	628.1	237.0	101.6	106.9

TEST NUMBER: P928288

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	686.5	710.7	687.8	104.1	108.3
115°	778.5	801.4	835.3	208.5	111.1
117.5°	858.4	885.4	908.5	714.8	360.1
120°	947.7	968.0	992.5	1008.7	825.9
122.5°	1023.4	1045.1	1072.4	1080.4	1081.8
125°	1100.6	1118.3	1144.0	1153.5	1157.5
127.5°	1171.1	1190.0	1210.4	1224.0	1225.2
130°	1237.4	1259.1	1273.9	1288.9	1287.6
132.5°	1305.1	1322.8	1337.6	1349.8	1348.5
135°	1362.0	1383.7	1395.8	1409.4	1406.8
137.5°	1421.5	1437.8	1451.4	1465.0	1460.9
140°	1479.7	1490.6	1505.4	1517.6	1510.9
142.5°	1528.6	1538.1	1555.6	1566.3	1559.6
145°	1580.0	1578.6	1601.6	1611.1	1604.4
147.5°	1624.6	1620.6	1643.6	1650.3	1645.0
150°	1668.0	1658.5	1680.2	1688.2	1681.5
152.5°	1704.5	1693.7	1714.0	1722.1	1712.7
155°	1739.7	1727.6	1743.8	1751.9	1741.1
157.5°	1768.1	1757.4	1769.6	1779.1	1768.1
160°	1792.6	1784.4	1792.6	1800.6	1791.1
162.5°	1814.2	1806.1	1812.8	1822.3	1810.1
165°	1833.1	1825.1	1829.0	1838.5	1829.0
167.5°	1848.1	1839.8	1844.0	1853.5	1841.3
170°	1860.2	1852.1	1854.8	1864.3	1852.1
172.5°	1868.3	1860.2	1863.0	1872.4	1860.2
175°	1875.1	1865.6	1868.3	1877.8	1864.3
177.5°	1877.8	1868.3	1869.8	1879.3	1867.0
180°	1871.0	1871.0	1871.0	1871.0	1871.0

TEST NUMBER: P928288

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.92	9.78	9.87	10.75	12.02	8.49	9.35	9.44	10.32	11.59
	3H	10.58	11.35	11.55	12.33	13.63	10.11	10.88	11.07	11.86	13.15
	4H	11.17	11.90	12.15	12.88	14.19	10.69	11.42	11.68	12.41	13.71
	6H	11.57	12.24	12.56	13.23	14.55	11.09	11.77	12.08	12.76	14.07
	8H	11.67	12.31	12.67	13.32	14.63	11.20	11.84	12.20	12.85	14.16
	12H	11.72	12.33	12.73	13.33	14.67	11.24	11.85	12.24	12.85	14.19
4H	2H	9.38	10.11	10.37	11.10	12.40	9.03	9.77	10.02	10.75	12.05
	3H	11.25	11.86	12.24	12.87	14.19	10.85	11.46	11.85	12.48	13.79
	4H	11.96	12.52	12.97	13.53	14.87	11.56	12.11	12.56	13.12	14.46
	6H	12.48	12.96	13.49	13.99	15.33	12.07	12.55	13.08	13.58	14.92
	8H	12.63	13.08	13.65	14.10	15.45	12.22	12.67	13.23	13.69	15.04
	12H	12.70	13.11	13.74	14.15	15.50	12.28	12.69	13.32	13.72	15.08
8H	4H	12.16	12.61	13.18	13.63	14.98	11.80	12.25	12.82	13.27	14.62
	6H	12.79	13.16	13.83	14.23	15.58	12.43	12.80	13.47	13.87	15.21
	8H	13.01	13.34	14.06	14.39	15.76	12.64	12.97	13.69	14.02	15.39
	12H	13.15	13.43	14.20	14.48	15.89	12.76	13.05	13.82	14.09	15.51
12H	4H	12.15	12.55	13.18	13.59	14.95	11.79	12.20	12.83	13.24	14.59
	6H	12.82	13.15	13.87	14.20	15.57	12.47	12.80	13.52	13.85	15.22
	8H	13.07	13.35	14.12	14.40	15.81	12.71	13.00	13.76	14.04	15.45