

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928298

Luminaire Tested: DFN2DIP-HX4F0-070D090US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928298
REPORT IS A COMBINATION OF REPORTS P900916 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D090US927-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11769.1 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928298
CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P928298

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40	40	40	40	35
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	35	35	35	30
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	34	32	30	30	30	30	25
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	26	26	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	23	23	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	20	20	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	18	18	18	16
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	18	16	16	16	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15	15	15	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14	14	14	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1704	1704	1704
5°	1707	1677	1688
10°	1690	1644	1633
15°	1667	1590	1548
20°	1636	1515	1444
25°	1605	1431	1343
30°	1563	1345	1216
35°	1521	1253	1104
40°	1479	1157	975
45°	1430	1051	859
50°	1380	944	745
55°	1327	829	636
60°	1266	710	523
65°	1196	588	471
70°	1111	474	426
75°	1004	418	388
80°	850	352	337
85°	594	236	254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1430 cd/sqm



TEST NUMBER: P928298

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	1.8
10°-20°	589.5	5.0
20°-30°	827.7	7.0
30°-40°	902.2	7.7
40°-50°	829.2	7.0
50°-60°	651.2	5.5
60°-70°	423.9	3.6
70°-80°	218.2	1.9
80°-90°	59.9	0.5
90°-100°	79.3	0.7
100°-110°	295.7	2.5
110°-120°	784.2	6.7
120°-130°	1300.7	11.1
130°-140°	1381.7	11.7
140°-150°	1284.1	10.9
150°-160°	1032.4	8.8
160°-170°	665.2	5.7
170°-180°	229.0	1.9
0°-30°	1631.9	13.9
0°-40°	2534.1	21.5
0°-60°	4014.6	34.1
0°-90°	4716.6	40.1
90°-120°	1159.3	9.9
90°-150°	5125.8	43.6
90°-180°	7052.0	59.9
0°-180°	11769.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2291	2291	2291	2291	2291	
5°	2291	2281	2254	2273	2266	217
15°	2179	2156	2086	2047	2026	614
25°	1978	1912	1775	1690	1659	910
35°	1704	1599	1416	1286	1240	1067
45°	1394	1254	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	715	547	361	290	284	709
75°	382	236	166	151	149	403
85°	89	46	39	39	39	102
90°	2	21	35	44	47	11
95°	113	56	68	77	75	134
105°	529	582	106	125	132	565
115°	1001	1030	1074	268	143	985
125°	1415	1438	1471	1483	1488	1262
135°	1751	1779	1795	1812	1809	1353
145°	2032	2030	2059	2071	2063	1271
155°	2237	2221	2242	2252	2239	1031
165°	2357	2346	2352	2364	2352	666
175°	2411	2399	2402	2414	2397	229
180°	2406	2406	2406	2406	2406	



TEST NUMBER: P928298

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.3	2291.3	2291.3	2291.3	2291.3
2.5°	2301.6	2291.3	2268.4	2289.4	2285.2
5°	2291.3	2281.0	2254.0	2272.6	2266.5
7.5°	2272.6	2260.3	2231.3	2239.4	2229.1
10°	2247.8	2233.3	2191.9	2185.5	2173.2
12.5°	2216.7	2198.0	2142.0	2129.6	2106.7
15°	2179.3	2156.5	2086.0	2046.7	2026.0
17.5°	2135.8	2102.6	2015.5	1969.9	1936.7
20°	2086.0	2044.5	1940.9	1889.2	1843.4
22.5°	2032.2	1984.4	1864.1	1793.6	1762.7
25°	1978.3	1911.8	1775.0	1690.0	1658.8
27.5°	1914.0	1843.4	1692.0	1594.6	1546.9
30°	1845.6	1766.6	1600.7	1495.1	1439.1
32.5°	1779.1	1683.7	1513.8	1389.3	1337.4
35°	1704.5	1598.7	1416.4	1285.7	1240.0
37.5°	1632.0	1517.8	1325.1	1181.8	1130.2
40°	1555.2	1430.9	1229.6	1082.4	1028.5
42.5°	1476.4	1343.8	1134.3	980.7	929.1
45°	1393.5	1254.4	1036.9	889.5	839.8
47.5°	1314.7	1167.6	943.6	796.2	750.7
50°	1227.6	1080.4	852.3	709.1	665.8
52.5°	1142.5	986.9	765.2	628.3	588.9
55°	1059.5	897.8	673.8	549.6	510.2
57.5°	974.6	808.7	593.1	476.9	443.8
60°	887.5	721.6	508.0	402.4	369.2
62.5°	802.5	636.7	435.4	336.0	319.4
65°	715.4	547.4	360.8	290.4	284.0
67.5°	632.5	464.4	290.4	254.9	248.8
70°	545.4	383.6	240.5	219.8	211.4
72.5°	462.4	308.9	201.1	184.6	180.4
75°	381.5	236.3	165.8	151.4	149.4
77.5°	300.7	167.8	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.5	80.9	68.4	64.2	64.2
85°	89.1	45.5	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.8
97.5°	203.6	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.2	113.1	116.6
102.5°	422.9	419.6	102.7	121.7	127.1
105°	529.1	581.5	106.2	125.3	132.3
107.5°	652.8	696.2	109.8	128.8	135.8
110°	771.2	807.6	304.7	130.6	137.5



TEST NUMBER: P928298

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	882.6	913.8	884.3	133.9	139.3
115°	1000.9	1030.4	1074.0	268.1	142.8
117.5°	1103.6	1138.3	1168.0	919.0	463.0
120°	1218.5	1244.5	1276.0	1296.8	1061.8
122.5°	1315.9	1343.8	1378.7	1389.0	1390.9
125°	1415.1	1437.8	1470.9	1483.1	1488.2
127.5°	1505.6	1530.0	1556.3	1573.6	1575.3
130°	1591.0	1618.9	1637.9	1657.1	1655.5
132.5°	1678.0	1700.7	1719.7	1735.5	1733.8
135°	1751.2	1779.1	1794.6	1812.2	1808.7
137.5°	1827.7	1848.5	1866.1	1883.5	1878.3
140°	1902.5	1916.6	1935.6	1951.3	1942.6
142.5°	1965.3	1977.5	2000.0	2013.9	2005.3
145°	2031.5	2029.6	2059.2	2071.4	2062.7
147.5°	2088.7	2083.6	2113.1	2121.8	2115.0
150°	2144.6	2132.4	2160.3	2170.6	2161.9
152.5°	2191.5	2177.6	2203.7	2214.2	2202.0
155°	2236.8	2221.2	2242.1	2252.4	2238.6
157.5°	2273.4	2259.5	2275.2	2287.4	2273.4
160°	2304.7	2294.2	2304.7	2315.1	2302.9
162.5°	2332.4	2322.1	2330.8	2343.0	2327.3
165°	2356.8	2346.5	2351.7	2363.9	2351.7
167.5°	2376.1	2365.5	2370.9	2383.0	2367.4
170°	2391.8	2381.2	2384.7	2396.9	2381.2
172.5°	2402.1	2391.8	2395.2	2407.4	2391.8
175°	2410.8	2398.6	2402.1	2414.3	2396.9
177.5°	2414.3	2402.1	2404.0	2416.2	2400.5
180°	2405.6	2405.6	2405.6	2405.6	2405.6



TEST NUMBER: P928298
 CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.00	8.75	9.04	9.80	11.21	3.97	4.72	5.01	5.77	7.18
	3H	9.67	10.34	10.72	11.40	12.83	5.15	5.83	6.21	6.88	8.31
	4H	10.27	10.91	11.34	11.97	13.41	5.60	6.24	6.67	7.30	8.73
	6H	10.69	11.28	11.77	12.34	13.79	5.92	6.51	7.00	7.57	9.02
	8H	10.82	11.38	11.90	12.45	13.89	6.01	6.57	7.09	7.65	9.09
	12H	10.88	11.41	11.96	12.48	13.94	6.05	6.58	7.14	7.65	9.12
4H	2H	8.01	8.65	9.08	9.70	11.14	4.56	5.20	5.63	6.25	7.69
	3H	9.83	10.36	10.91	11.45	12.89	5.90	6.43	6.98	7.52	8.96
	4H	10.52	11.01	11.60	12.08	13.55	6.45	6.94	7.53	8.01	9.48
	6H	11.03	11.45	12.12	12.55	14.01	6.87	7.28	7.96	8.38	9.84
	8H	11.21	11.60	12.30	12.69	14.16	6.99	7.38	8.09	8.47	9.95
	12H	11.30	11.65	12.41	12.75	14.24	7.06	7.41	8.17	8.51	10.00
8H	4H	10.48	10.87	11.57	11.96	13.44	6.72	7.11	7.82	8.20	9.68
	6H	11.05	11.37	12.16	12.50	13.98	7.24	7.56	8.36	8.69	10.17
	8H	11.26	11.55	12.38	12.66	14.15	7.43	7.72	8.55	8.83	10.32
	12H	11.40	11.65	12.52	12.76	14.29	7.55	7.80	8.68	8.91	10.44
12H	4H	10.43	10.78	11.54	11.89	13.37	6.72	7.08	7.83	8.18	9.66
	6H	11.02	11.30	12.14	12.42	13.91	7.29	7.57	8.41	8.69	10.18
	8H	11.24	11.49	12.36	12.60	14.13	7.50	7.75	8.62	8.86	10.39