

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902938

Luminaire Tested: DFN2DIP-PN2F0-060D040US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902938
REPORT IS A COMBINATION OF REPORTS P899490 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-060D040US830-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8143.5 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 95.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902938

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902938

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		64
1	100	96	92	89	94	90	87	84	78	76	74		68	66	64		58
2	92	85	79	74	86	79	74	70	69	65	62		60	57	55		52
3	84	75	68	62	78	70	64	59	62	57	53		54	50	47		46
4	77	67	59	53	72	63	56	51	55	50	46		48	44	41		42
5	71	60	52	46	66	56	49	44	50	44	40		44	39	36		38
6	66	54	46	40	61	51	44	39	45	39	35		40	35	32		35
7	61	49	41	36	57	46	39	34	41	35	31		36	32	28		32
8	57	45	37	32	53	42	35	30	38	32	28		33	29	25		29
9	53	41	34	29	50	39	32	27	35	29	25		31	26	23		27
10	50	38	31	26	47	36	29	25	32	27	23		29	24	21		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5062	5062	5062
5°	5062	4971	5006
10°	5004	4863	4836
15°	4927	4692	4577
20°	4828	4460	4263
25°	4726	4203	3959
30°	4592	3939	3576
35°	4461	3658	3240
40°	4326	3367	2856
45°	4171	3046	2508
50°	4011	2723	2169
55°	3841	2380	1844
60°	3645	2022	1511
65°	3419	1661	1351
70°	3145	1322	1213
75°	2800	1145	1088
80°	2303	930	921
85°	1506	579	655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4171 cd/sqm

TEST NUMBER: P902938

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	2.7
10°-20°	601.3	7.4
20°-30°	844.3	10.4
30°-40°	920.3	11.3
40°-50°	845.9	10.4
50°-60°	664.3	8.2
60°-70°	432.4	5.3
70°-80°	222.6	2.7
80°-90°	60.2	0.7
90°-100°	73.8	0.9
100°-110°	234.4	2.9
110°-120°	401.2	4.9
120°-130°	527.6	6.5
130°-140°	592.2	7.3
140°-150°	580.8	7.1
150°-160°	487.2	6.0
160°-170°	323.1	4.0
170°-180°	112.9	1.4
0°-30°	1664.7	20.4
0°-40°	2585.0	31.7
0°-60°	4095.1	50.3
0°-90°	4810.3	59.1
90°-120°	709.4	8.7
90°-150°	2410.0	29.6
90°-180°	3333.0	40.9
0°-180°	8143.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	1	13	35	33	34	8
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	

TEST NUMBER: P902938

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9



TEST NUMBER: P902938

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3

TEST NUMBER: P902938

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.47	14.38	14.35	15.28	16.42	9.44	10.35	10.32	11.25	12.39
	3H	15.13	15.95	16.03	16.86	18.02	10.62	11.43	11.51	12.34	13.50
	4H	15.73	16.50	16.64	17.41	18.59	11.06	11.83	11.97	12.74	13.91
	6H	16.14	16.85	17.06	17.77	18.96	11.37	12.08	12.29	13.00	14.18
	8H	16.26	16.93	17.19	17.87	19.06	11.45	12.13	12.38	13.06	14.25
	12H	16.32	16.96	17.25	17.89	19.10	11.49	12.13	12.43	13.06	14.27
4H	2H	13.49	14.26	14.41	15.18	16.35	10.03	10.80	10.95	11.71	12.89
	3H	15.31	15.95	16.23	16.89	18.08	11.37	12.01	12.30	12.95	14.14
	4H	15.99	16.57	16.92	17.51	18.72	11.91	12.49	12.84	13.43	14.64
	6H	16.49	16.99	17.44	17.95	19.17	12.31	12.81	13.26	13.78	14.99
	8H	16.65	17.12	17.60	18.08	19.30	12.43	12.90	13.38	13.86	15.09
	12H	16.74	17.16	17.71	18.14	19.37	12.49	12.91	13.46	13.89	15.12
8H	4H	15.96	16.42	16.91	17.38	18.61	12.18	12.65	13.13	13.61	14.83
	6H	16.50	16.89	17.48	17.89	19.11	12.68	13.07	13.66	14.06	15.29
	8H	16.71	17.05	17.69	18.04	19.28	12.86	13.20	13.84	14.19	15.43
	12H	16.83	17.13	17.82	18.12	19.41	12.97	13.27	13.95	14.25	15.54
12H	4H	15.91	16.33	16.88	17.31	18.54	12.19	12.61	13.16	13.58	14.81
	6H	16.48	16.82	17.46	17.81	19.05	12.72	13.06	13.71	14.05	15.30
	8H	16.69	16.99	17.68	17.97	19.26	12.92	13.22	13.91	14.20	15.50