

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928424

Luminaire Tested: DFN2DIP-HX4F0-110D050US927-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928424
REPORT IS A COMBINATION OF REPORTS P900851 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D050US927-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12545.3 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 149.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928424
CATALOG NUMBER: DFN2DIP-HX4F0-110D050US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P928424

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.1	2.5
10°-20°	897.7	7.2
20°-30°	1319.3	10.5
30°-40°	1532.2	12.2
40°-50°	1530.4	12.2
50°-60°	1334.4	10.6
60°-70°	986.4	7.9
70°-80°	558.1	4.4
80°-90°	149.7	1.2
90°-100°	44.1	0.4
100°-110°	164.3	1.3
110°-120°	435.7	3.5
120°-130°	722.6	5.8
130°-140°	767.6	6.1
140°-150°	713.4	5.7
150°-160°	573.6	4.6
160°-170°	369.6	2.9
170°-180°	127.2	1.0
0°-30°	2536.0	20.2
0°-40°	4068.3	32.4
0°-60°	6933.0	55.3
0°-90°	8627.2	68.8
90°-120°	644.1	5.1
90°-150°	2847.7	22.7
90°-180°	3918.0	31.2
0°-180°	12545.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3390	3390	3390	3390	3390	
5°	3390	3377	3341	3367	3361	322
15°	3227	3208	3165	3178	3162	909
25°	2921	2895	2839	2846	2839	1344
35°	2520	2487	2435	2415	2399	1573
45°	2050	2028	1978	1943	1930	1582
55°	1552	1532	1493	1454	1438	1387
65°	1046	1027	994	965	949	1035
75°	547	541	525	505	512	584
85°	134	130	127	117	114	149
90°	1	12	19	24	26	12
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	572	597	149	79	547
125°	786	799	817	824	827	701
135°	973	988	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1251	1244	573
165°	1309	1304	1306	1313	1306	370
175°	1339	1332	1334	1341	1332	127
180°	1336	1336	1336	1336	1336	



TEST NUMBER: P928424

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3389.9	3389.9	3389.9	3389.9	3389.9
2.5°	3409.6	3393.3	3357.4	3389.9	3383.7
5°	3389.9	3377.1	3341.1	3367.0	3360.9
7.5°	3367.0	3347.7	3311.7	3338.0	3331.5
10°	3331.5	3308.6	3269.5	3295.4	3285.8
12.5°	3282.4	3263.0	3223.9	3240.2	3233.6
15°	3227.0	3207.6	3165.1	3178.2	3162.0
17.5°	3158.5	3139.2	3096.6	3112.9	3096.6
20°	3083.5	3064.1	3018.5	3028.1	3015.4
22.5°	3008.8	2979.3	2936.8	2936.8	2930.2
25°	2920.6	2894.7	2839.3	2845.6	2839.3
27.5°	2822.7	2799.9	2757.7	2748.0	2731.8
30°	2725.2	2698.9	2650.1	2640.4	2627.3
32.5°	2620.7	2601.4	2549.1	2529.4	2516.3
35°	2519.7	2487.3	2435.0	2415.3	2399.0
37.5°	2405.6	2376.2	2324.0	2301.2	2284.9
40°	2288.4	2262.1	2209.9	2180.9	2167.7
42.5°	2174.3	2148.0	2096.1	2063.2	2043.9
45°	2050.5	2027.6	1978.5	1942.9	1929.8
47.5°	1929.8	1907.0	1854.7	1818.7	1799.3
50°	1802.5	1786.3	1740.6	1695.0	1678.7
52.5°	1678.7	1655.8	1613.7	1577.7	1554.9
55°	1551.8	1532.0	1493.0	1453.9	1437.6
57.5°	1424.5	1408.3	1365.7	1326.6	1313.5
60°	1297.2	1284.5	1238.8	1202.8	1193.1
62.5°	1173.4	1150.6	1118.1	1085.6	1072.4
65°	1046.5	1026.7	994.3	964.9	948.7
67.5°	916.1	899.6	870.5	847.7	834.5
70°	795.4	782.3	752.9	730.1	717.2
72.5°	671.6	658.5	642.2	619.4	609.7
75°	547.4	541.3	524.6	505.3	511.9
77.5°	436.8	423.6	417.1	407.4	397.7
80°	326.1	322.7	316.1	306.4	299.9
82.5°	221.7	221.7	218.6	205.4	205.4
85°	133.5	130.4	127.3	117.2	114.1
87.5°	58.8	52.2	45.6	36.0	32.5
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.1
100°	171.2	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.6	70.6
105°	294.0	323.1	59.0	69.6	73.5
107.5°	362.7	386.7	61.0	71.5	75.5
110°	428.5	448.7	169.3	72.5	76.3



TEST NUMBER: P928424

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.3	507.7	491.3	74.4	77.4
115°	556.1	572.5	596.7	149.0	79.4
117.5°	613.1	632.4	649.0	510.5	257.2
120°	676.9	691.4	708.8	720.5	589.9
122.5°	731.0	746.5	765.9	771.7	772.8
125°	786.1	798.8	817.2	823.9	826.8
127.5°	836.4	850.0	864.6	874.2	875.2
130°	883.9	899.4	909.9	920.6	919.7
132.5°	932.3	944.9	955.4	964.2	963.2
135°	972.9	988.4	997.0	1006.8	1004.8
137.5°	1015.3	1027.0	1036.7	1046.4	1043.5
140°	1056.9	1064.8	1075.3	1084.0	1079.3
142.5°	1091.9	1098.7	1111.2	1118.9	1114.0
145°	1128.6	1127.6	1144.0	1150.8	1145.9
147.5°	1160.4	1157.5	1174.0	1178.8	1175.0
150°	1191.4	1184.7	1200.1	1205.9	1201.1
152.5°	1217.5	1209.8	1224.3	1230.1	1223.3
155°	1242.6	1234.0	1245.6	1251.4	1243.7
157.5°	1262.9	1255.2	1264.0	1270.8	1262.9
160°	1280.4	1274.6	1280.4	1286.1	1279.4
162.5°	1295.8	1290.1	1294.8	1301.7	1292.9
165°	1309.3	1303.6	1306.5	1313.2	1306.5
167.5°	1320.0	1314.2	1317.2	1323.9	1315.2
170°	1328.7	1322.9	1324.9	1331.6	1322.9
172.5°	1334.5	1328.7	1330.7	1337.5	1328.7
175°	1339.4	1332.5	1334.5	1341.3	1331.6
177.5°	1341.3	1334.5	1335.5	1342.3	1333.6
180°	1336.4	1336.4	1336.4	1336.4	1336.4



TEST NUMBER: P928424
 CATALOG NUMBER: DFN2DIP-HX4F0-110D050US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.06	13.12	12.84	13.92	14.89	11.63	12.69	12.40	13.49	14.46
	3H	13.74	14.69	14.53	15.50	16.50	13.26	14.21	14.05	15.02	16.03
	4H	14.33	15.23	15.14	16.05	17.07	13.86	14.76	14.67	15.58	16.59
	6H	14.74	15.57	15.56	16.40	17.43	14.27	15.10	15.09	15.92	16.95
	8H	14.85	15.64	15.68	16.49	17.52	14.38	15.17	15.21	16.01	17.04
	12H	14.91	15.66	15.75	16.50	17.56	14.43	15.18	15.26	16.02	17.08
4H	2H	12.55	13.44	13.36	14.26	15.28	12.20	13.10	13.01	13.92	14.93
	3H	14.43	15.18	15.25	16.03	17.06	14.04	14.79	14.86	15.64	16.67
	4H	15.15	15.84	15.99	16.69	17.75	14.75	15.43	15.59	16.28	17.34
	6H	15.68	16.27	16.53	17.15	18.21	15.27	15.86	16.12	16.74	17.80
	8H	15.84	16.39	16.69	17.26	18.33	15.42	15.98	16.28	16.85	17.92
	12H	15.92	16.42	16.80	17.31	18.39	15.50	15.99	16.37	16.88	17.97
8H	4H	15.37	15.92	16.22	16.79	17.87	15.01	15.56	15.86	16.43	17.50
	6H	16.01	16.47	16.89	17.38	18.45	15.64	16.10	16.53	17.01	18.09
	8H	16.23	16.64	17.13	17.54	18.64	15.86	16.27	16.76	17.17	18.27
	12H	16.37	16.73	17.27	17.63	18.77	15.99	16.35	16.89	17.24	18.39
12H	4H	15.36	15.86	16.24	16.75	17.83	15.01	15.51	15.89	16.40	17.48
	6H	16.04	16.45	16.94	17.35	18.45	15.69	16.09	16.58	17.00	18.09
	8H	16.29	16.65	17.19	17.55	18.69	15.93	16.29	16.83	17.19	18.34