

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902942

Luminaire Tested: DFN2DIP-PN2F0-060D050US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902942
REPORT IS A COMBINATION OF REPORTS P899500 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-060D050US830-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8977.7 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 105.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902942

CATALOG NUMBER: DFN2DIP-PN2F0-060D050US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902942

CATALOG NUMBER: DFN2DIP-PN2F0-060D050US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5062	5062	5062
5°	5062	4971	5006
10°	5004	4863	4836
15°	4927	4692	4577
20°	4828	4460	4263
25°	4726	4203	3959
30°	4592	3939	3576
35°	4461	3658	3240
40°	4326	3367	2856
45°	4171	3046	2508
50°	4011	2723	2169
55°	3841	2380	1844
60°	3645	2022	1511
65°	3419	1661	1351
70°	3145	1322	1213
75°	2800	1145	1088
80°	2303	930	921
85°	1506	579	655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4171 cd/sqm

TEST NUMBER: P902942

CATALOG NUMBER: DFN2DIP-PN2F0-060D050US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	2.4
10°-20°	601.3	6.7
20°-30°	844.3	9.4
30°-40°	920.3	10.3
40°-50°	845.9	9.4
50°-60°	664.3	7.4
60°-70°	432.4	4.8
70°-80°	222.6	2.5
80°-90°	61.1	0.7
90°-100°	92.2	1.0
100°-110°	293.0	3.3
110°-120°	501.5	5.6
120°-130°	659.5	7.3
130°-140°	740.3	8.2
140°-150°	725.9	8.1
150°-160°	609.0	6.8
160°-170°	403.9	4.5
170°-180°	141.2	1.6
0°-30°	1664.7	18.5
0°-40°	2585.0	28.8
0°-60°	4095.1	45.6
0°-90°	4811.2	53.6
90°-120°	886.7	9.9
90°-150°	3012.5	33.6
90°-180°	4167.0	46.4
0°-180°	8977.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	1	16	44	41	43	9
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P902942

CATALOG NUMBER: DFN2DIP-PN2F0-060D050US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3

TEST NUMBER: P902942

CATALOG NUMBER: DFN2DIP-PN2F0-060D050US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P902942

CATALOG NUMBER: DFN2DIP-PN2F0-060D050US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.99	13.85	13.93	14.80	16.02	8.96	9.82	9.89	10.77	11.99
	3H	14.65	15.42	15.60	16.38	17.62	10.14	10.90	11.08	11.86	13.10
	4H	15.25	15.98	16.21	16.93	18.19	10.57	11.30	11.53	12.26	13.52
	6H	15.66	16.32	16.63	17.29	18.56	10.88	11.55	11.85	12.52	13.78
	8H	15.77	16.41	16.75	17.39	18.66	10.97	11.60	11.94	12.58	13.85
	12H	15.83	16.43	16.81	17.41	18.70	11.00	11.61	11.98	12.58	13.87
4H	2H	13.01	13.74	13.98	14.70	15.95	9.55	10.28	10.51	11.24	12.49
	3H	14.82	15.42	15.79	16.41	17.68	10.88	11.49	11.86	12.48	13.74
	4H	15.50	16.05	16.48	17.03	18.32	11.42	11.97	12.40	12.95	14.24
	6H	15.99	16.47	16.99	17.47	18.77	11.82	12.29	12.81	13.30	14.59
	8H	16.16	16.60	17.15	17.60	18.91	11.94	12.38	12.94	13.38	14.69
	12H	16.24	16.64	17.26	17.66	18.97	12.00	12.39	13.01	13.41	14.72
8H	4H	15.46	15.91	16.46	16.90	18.21	11.69	12.13	12.68	13.13	14.43
	6H	16.01	16.37	17.03	17.41	18.72	12.18	12.55	13.20	13.59	14.89
	8H	16.21	16.53	17.24	17.56	18.88	12.36	12.68	13.39	13.71	15.03
	12H	16.34	16.62	17.37	17.64	19.01	12.47	12.75	13.50	13.77	15.14
12H	4H	15.41	15.81	16.43	16.83	18.14	11.69	12.09	12.70	13.10	14.41
	6H	15.98	16.30	17.01	17.33	18.65	12.23	12.55	13.26	13.58	14.90
	8H	16.19	16.47	17.22	17.49	18.86	12.42	12.71	13.46	13.73	15.10