

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905607

Luminaire Tested: DFN2DIP-PN2F0-030D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905607
REPORT IS A COMBINATION OF REPORTS P901004 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D040US835-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6509.9 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 58.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905607

CATALOG NUMBER: DFN2DIP-PN2F0-030D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905607

CATALOG NUMBER: DFN2DIP-PN2F0-030D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2685	2685	2685
5°	2685	2637	2656
10°	2655	2580	2566
15°	2614	2489	2428
20°	2561	2366	2261
25°	2507	2229	2100
30°	2436	2090	1897
35°	2366	1940	1719
40°	2295	1786	1515
45°	2213	1616	1331
50°	2127	1445	1151
55°	2038	1262	978
60°	1934	1073	802
65°	1814	881	717
70°	1668	702	643
75°	1485	608	577
80°	1222	493	489
85°	799	307	347

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2213 cd/sqm

TEST NUMBER: P905607

CATALOG NUMBER: DFN2DIP-PN2F0-030D040US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.8
10°-20°	319.0	4.9
20°-30°	447.9	6.9
30°-40°	488.2	7.5
40°-50°	448.7	6.9
50°-60°	352.4	5.4
60°-70°	229.4	3.5
70°-80°	118.1	1.8
80°-90°	32.5	0.5
90°-100°	44.5	0.7
100°-110°	165.9	2.5
110°-120°	440.1	6.8
120°-130°	729.9	11.2
130°-140°	775.4	11.9
140°-150°	720.6	11.1
150°-160°	579.4	8.9
160°-170°	373.3	5.7
170°-180°	128.5	2.0
0°-30°	883.1	13.6
0°-40°	1371.3	21.1
0°-60°	2172.4	33.4
0°-90°	2552.3	39.2
90°-120°	650.5	10.0
90°-150°	2876.4	44.2
90°-180°	3958.0	60.8
0°-180°	6509.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	1	12	20	24	26	6
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P905607

CATALOG NUMBER: DFN2DIP-PN2F0-030D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P905607

CATALOG NUMBER: DFN2DIP-PN2F0-030D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P905607

CATALOG NUMBER: DFN2DIP-PN2F0-030D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.36	10.11	10.41	11.16	12.58	5.33	6.08	6.38	7.13	8.55
	3H	11.01	11.68	12.08	12.74	14.18	6.50	7.17	7.56	8.23	9.67
	4H	11.61	12.24	12.68	13.30	14.75	6.93	7.57	8.00	8.63	10.07
	6H	12.01	12.59	13.09	13.66	15.11	7.23	7.82	8.31	8.88	10.34
	8H	12.12	12.68	13.21	13.76	15.21	7.31	7.87	8.40	8.95	10.40
	12H	12.17	12.70	13.26	13.77	15.25	7.35	7.87	8.44	8.95	10.42
4H	2H	9.37	10.00	10.45	11.06	12.51	5.91	6.54	6.98	7.60	9.05
	3H	11.17	11.69	12.25	12.78	14.24	7.23	7.76	8.31	8.85	10.30
	4H	11.84	12.32	12.93	13.40	14.88	7.76	8.24	8.85	9.32	10.80
	6H	12.33	12.74	13.43	13.85	15.32	8.16	8.57	9.25	9.67	11.15
	8H	12.49	12.88	13.59	13.97	15.46	8.27	8.66	9.37	9.76	11.24
	12H	12.57	12.92	13.69	14.03	15.52	8.32	8.67	9.44	9.78	11.28
8H	4H	11.80	12.18	12.90	13.28	14.77	8.02	8.41	9.12	9.50	10.99
	6H	12.34	12.66	13.46	13.79	15.28	8.51	8.83	9.63	9.97	11.46
	8H	12.54	12.82	13.67	13.94	15.44	8.69	8.97	9.82	10.09	11.59
	12H	12.66	12.91	13.79	14.02	15.56	8.79	9.04	9.92	10.15	11.70
12H	4H	11.74	12.09	12.86	13.20	14.70	8.02	8.37	9.13	9.48	10.97
	6H	12.31	12.59	13.44	13.71	15.21	8.56	8.84	9.68	9.96	11.46
	8H	12.51	12.76	13.64	13.87	15.42	8.75	8.99	9.88	10.11	11.65

END OF REPORT