

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905615

Luminaire Tested: DFN2DIP-PN2F0-030D060US835-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P905615  
REPORT IS A COMBINATION OF REPORTS P901024 AND P897905  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN2F0-030D060US835-RLONL  
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8490.0 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 80.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P905615  
CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P905615  
 CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	14	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2685	2685	2685
5°	2685	2637	2656
10°	2655	2580	2566
15°	2614	2489	2428
20°	2561	2366	2261
25°	2507	2229	2100
30°	2436	2090	1897
35°	2366	1940	1719
40°	2295	1786	1515
45°	2213	1616	1331
50°	2127	1445	1151
55°	2038	1262	978
60°	1934	1073	802
65°	1814	881	717
70°	1668	702	643
75°	1485	608	577
80°	1222	493	489
85°	799	307	347

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2213 cd/sqm



TEST NUMBER: P905615

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.2	1.4
10°-20°	319.0	3.8
20°-30°	447.9	5.3
30°-40°	488.2	5.8
40°-50°	448.7	5.3
50°-60°	352.4	4.2
60°-70°	229.4	2.7
70°-80°	118.1	1.4
80°-90°	33.7	0.4
90°-100°	66.8	0.8
100°-110°	248.9	2.9
110°-120°	660.2	7.8
120°-130°	1094.9	12.9
130°-140°	1163.0	13.7
140°-150°	1080.9	12.7
150°-160°	869.0	10.2
160°-170°	560.0	6.6
170°-180°	192.7	2.3
0°-30°	883.1	10.4
0°-40°	1371.3	16.2
0°-60°	2172.4	25.6
0°-90°	2553.5	30.1
90°-120°	975.8	11.5
90°-150°	4314.7	50.8
90°-180°	5936.0	69.9
0°-180°	8490.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	1	18	29	37	40	8
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	



TEST NUMBER: P905615

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7



TEST NUMBER: P905615

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9



TEST NUMBER: P905615  
 CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.24	8.93	9.36	10.04	11.57	4.21	4.90	5.33	6.01	7.54
	3H	9.89	10.50	11.01	11.62	13.17	5.37	5.99	6.49	7.10	8.65
	4H	10.48	11.06	11.61	12.18	13.73	5.80	6.39	6.94	7.50	9.06
	6H	10.87	11.41	12.02	12.53	14.10	6.10	6.64	7.24	7.76	9.32
	8H	10.99	11.50	12.13	12.63	14.19	6.18	6.69	7.32	7.83	9.38
	12H	11.04	11.52	12.18	12.65	14.23	6.21	6.70	7.36	7.82	9.40
4H	2H	8.24	8.82	9.38	9.94	11.49	4.78	5.36	5.92	6.48	8.03
	3H	10.03	10.52	11.18	11.66	13.23	6.09	6.58	7.24	7.72	9.29
	4H	10.70	11.15	11.85	12.28	13.87	6.62	7.07	7.77	8.20	9.79
	6H	11.19	11.57	12.34	12.73	14.30	7.01	7.40	8.17	8.55	10.13
	8H	11.35	11.71	12.50	12.85	14.45	7.13	7.49	8.29	8.63	10.23
	12H	11.43	11.75	12.60	12.91	14.51	7.18	7.50	8.35	8.66	10.26
8H	4H	10.65	11.01	11.81	12.16	13.75	6.88	7.24	8.03	8.38	9.97
	6H	11.19	11.49	12.37	12.68	14.27	7.37	7.66	8.54	8.85	10.44
	8H	11.40	11.65	12.58	12.82	14.43	7.55	7.80	8.73	8.97	10.58
	12H	11.51	11.74	12.70	12.90	14.55	7.65	7.87	8.83	9.04	10.68
12H	4H	10.60	10.92	11.77	12.08	13.68	6.87	7.20	8.04	8.36	9.95
	6H	11.17	11.42	12.35	12.59	14.20	7.41	7.67	8.59	8.84	10.45
	8H	11.37	11.59	12.55	12.76	14.40	7.60	7.83	8.79	8.99	10.63