

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928492

Luminaire Tested: DFN2DIP-HX4F0-040D040US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928492
REPORT IS A COMBINATION OF REPORTS P900819 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D040US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6454.8 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928492

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928492

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	943	943	943
5°	945	930	936
10°	937	918	924
15°	923	903	904
20°	905	882	884
25°	886	857	860
30°	863	834	831
35°	841	806	799
40°	814	778	769
45°	787	751	738
50°	758	721	703
55°	727	688	670
60°	693	648	633
65°	655	606	589
70°	606	556	541
75°	539	495	498
80°	459	418	414
85°	333	285	275

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 787 cd/sqm

TEST NUMBER: P928492

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	1.8
10°-20°	335.9	5.2
20°-30°	493.7	7.6
30°-40°	573.4	8.9
40°-50°	572.7	8.9
50°-60°	499.3	7.7
60°-70°	369.1	5.7
70°-80°	208.8	3.2
80°-90°	57.1	0.9
90°-100°	36.3	0.6
100°-110°	135.2	2.1
110°-120°	358.7	5.6
120°-130°	594.9	9.2
130°-140°	631.9	9.8
140°-150°	587.3	9.1
150°-160°	472.2	7.3
160°-170°	304.3	4.7
170°-180°	104.7	1.6
0°-30°	949.0	14.7
0°-40°	1522.3	23.6
0°-60°	2594.3	40.2
0°-90°	3229.3	50.0
90°-120°	530.2	8.2
90°-150°	2344.3	36.3
90°-180°	3225.0	50.0
0°-180°	6454.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1268	1268	1268	1268	1268	
5°	1268	1264	1250	1260	1258	120
15°	1208	1200	1184	1189	1183	340
25°	1093	1083	1062	1065	1062	503
35°	943	931	911	904	898	589
45°	767	759	740	727	722	592
55°	581	573	559	544	538	519
65°	392	384	372	361	355	387
75°	205	202	196	189	192	219
85°	50	49	48	44	43	56
90°	1	10	16	20	21	6
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	678	681	577
135°	801	814	821	829	827	619
145°	929	928	942	947	943	581
155°	1023	1016	1025	1030	1024	471
165°	1078	1073	1076	1081	1076	305
175°	1102	1097	1099	1104	1096	105
180°	1100	1100	1100	1100	1100	

TEST NUMBER: P928492

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.5	1268.5	1268.5	1268.5	1268.5
2.5°	1275.9	1269.8	1256.3	1268.5	1266.2
5°	1268.5	1263.7	1250.2	1259.9	1257.6
7.5°	1259.9	1252.7	1239.2	1249.1	1246.6
10°	1246.6	1238.1	1223.5	1233.2	1229.5
12.5°	1228.2	1221.0	1206.4	1212.5	1209.9
15°	1207.5	1200.3	1184.4	1189.2	1183.2
17.5°	1181.9	1174.7	1158.8	1164.8	1158.8
20°	1153.8	1146.5	1129.5	1133.1	1128.4
22.5°	1125.8	1114.8	1098.9	1098.9	1096.5
25°	1092.8	1083.1	1062.4	1064.8	1062.4
27.5°	1056.2	1047.7	1032.0	1028.3	1022.3
30°	1019.7	1009.9	991.7	988.0	983.1
32.5°	980.7	973.4	953.9	946.5	941.6
35°	942.9	930.7	911.2	903.8	897.7
37.5°	900.2	889.2	869.6	861.1	855.0
40°	856.3	846.5	826.9	816.1	811.2
42.5°	813.6	803.8	784.4	772.0	764.8
45°	767.2	758.8	740.3	727.1	722.1
47.5°	722.1	713.5	694.1	680.6	673.4
50°	674.5	668.4	651.3	634.2	628.1
52.5°	628.1	619.6	603.8	590.4	581.8
55°	580.7	573.3	558.7	544.0	538.0
57.5°	533.0	527.0	511.0	496.4	491.5
60°	485.4	480.6	463.6	450.1	446.5
62.5°	439.1	430.6	418.4	406.2	401.3
65°	391.6	384.2	372.0	361.0	355.0
67.5°	342.8	336.6	325.8	317.2	312.3
70°	297.6	292.7	281.7	273.2	268.4
72.5°	251.3	246.4	240.3	231.8	228.1
75°	204.9	202.5	196.3	189.1	191.5
77.5°	163.4	158.5	156.1	152.4	148.8
80°	122.0	120.7	118.3	114.7	112.2
82.5°	83.0	83.0	81.8	76.9	76.9
85°	50.0	48.8	47.6	43.8	42.7
87.5°	22.0	19.6	17.1	13.4	12.1
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.0	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	140.9	31.9	45.4	51.7	53.3
102.5°	193.4	191.9	46.9	55.7	58.1
105°	242.0	265.9	48.6	57.3	60.5
107.5°	298.5	318.4	50.2	58.9	62.1
110°	352.7	369.4	139.4	59.7	62.8

TEST NUMBER: P928492

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.7	417.9	404.4	61.3	63.7
115°	457.7	471.2	491.2	122.6	65.4
117.5°	504.7	520.6	534.2	420.3	211.7
120°	557.3	569.2	583.5	593.2	485.7
122.5°	601.8	614.6	630.6	635.3	636.1
125°	647.2	657.6	672.7	678.3	680.7
127.5°	688.6	699.8	711.7	719.7	720.5
130°	727.6	740.4	749.1	757.9	757.1
132.5°	767.4	777.8	786.6	793.7	793.0
135°	800.9	813.7	820.8	828.8	827.2
137.5°	835.9	845.4	853.5	861.4	859.0
140°	870.1	876.5	885.3	892.4	888.4
142.5°	898.9	904.4	914.8	921.0	917.1
145°	929.1	928.3	941.7	947.4	943.4
147.5°	955.3	952.9	966.4	970.4	967.3
150°	980.8	975.2	988.0	992.8	988.8
152.5°	1002.3	995.9	1007.8	1012.6	1007.1
155°	1023.0	1015.9	1025.4	1030.2	1023.8
157.5°	1039.7	1033.3	1040.6	1046.1	1039.7
160°	1054.0	1049.2	1054.0	1058.8	1053.2
162.5°	1066.8	1062.0	1066.0	1071.6	1064.4
165°	1077.9	1073.2	1075.6	1081.1	1075.6
167.5°	1086.7	1081.8	1084.4	1089.9	1082.7
170°	1093.9	1089.1	1090.6	1096.3	1089.1
172.5°	1098.6	1093.9	1095.5	1101.1	1093.9
175°	1102.5	1097.0	1098.6	1104.2	1096.3
177.5°	1104.2	1098.6	1099.4	1105.1	1097.9
180°	1100.2	1100.2	1100.2	1100.2	1100.2

TEST NUMBER: P928492

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.07	7.93	8.03	8.91	10.18	6.64	7.50	7.60	8.47	9.75
	3H	8.73	9.51	9.70	10.49	11.78	8.26	9.03	9.23	10.01	11.31
	4H	9.32	10.05	10.30	11.04	12.34	8.85	9.58	9.83	10.57	11.87
	6H	9.72	10.40	10.72	11.39	12.70	9.25	9.92	10.24	10.91	12.23
	8H	9.83	10.47	10.83	11.48	12.79	9.35	9.99	10.35	11.00	12.31
	12H	9.88	10.49	10.88	11.49	12.82	9.40	10.01	10.40	11.01	12.34
4H	2H	7.53	8.27	8.52	9.25	10.55	7.19	7.92	8.18	8.91	10.21
	3H	9.40	10.01	10.40	11.03	12.34	9.01	9.62	10.01	10.63	11.95
	4H	10.12	10.68	11.12	11.68	13.02	9.71	10.27	10.72	11.28	12.62
	6H	10.63	11.11	11.65	12.14	13.48	10.22	10.70	11.24	11.74	13.07
	8H	10.78	11.23	11.80	12.26	13.61	10.37	10.82	11.39	11.84	13.19
	12H	10.86	11.26	11.89	12.30	13.66	10.43	10.84	11.47	11.88	13.24
8H	4H	10.31	10.76	11.33	11.79	13.14	9.95	10.40	10.97	11.43	12.78
	6H	10.95	11.32	11.99	12.38	13.73	10.58	10.96	11.63	12.02	13.37
	8H	11.17	11.50	12.22	12.55	13.91	10.80	11.13	11.85	12.18	13.55
	12H	11.30	11.59	12.36	12.63	14.05	10.92	11.20	11.97	12.25	13.66
12H	4H	10.30	10.71	11.34	11.75	13.10	9.95	10.35	10.98	11.39	12.75
	6H	10.98	11.30	12.03	12.36	13.72	10.63	10.95	11.68	12.00	13.37
	8H	11.22	11.51	12.27	12.55	13.96	10.86	11.15	11.92	12.20	13.61