

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905631

Luminaire Tested: DFN2DIP-PN2F0-040D050US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905631
REPORT IS A COMBINATION OF REPORTS P901016 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D050US835-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8350.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 80.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905631

CATALOG NUMBER: DFN2DIP-PN2F0-040D050US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905631

CATALOG NUMBER: DFN2DIP-PN2F0-040D050US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3581	3581	3581
5°	3581	3516	3541
10°	3539	3439	3421
15°	3485	3318	3238
20°	3415	3155	3015
25°	3343	2972	2800
30°	3248	2786	2530
35°	3155	2587	2292
40°	3060	2382	2020
45°	2950	2155	1774
50°	2836	1926	1534
55°	2717	1683	1304
60°	2578	1430	1069
65°	2419	1174	956
70°	2224	936	857
75°	1980	810	770
80°	1629	658	652
85°	1065	409	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2950 cd/sqm

TEST NUMBER: P905631

CATALOG NUMBER: DFN2DIP-PN2F0-040D050US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	1.9
10°-20°	425.3	5.1
20°-30°	597.2	7.2
30°-40°	650.9	7.8
40°-50°	598.3	7.2
50°-60°	469.9	5.6
60°-70°	305.8	3.7
70°-80°	157.4	1.9
80°-90°	43.2	0.5
90°-100°	55.7	0.7
100°-110°	207.4	2.5
110°-120°	550.1	6.6
120°-130°	912.4	10.9
130°-140°	969.2	11.6
140°-150°	900.8	10.8
150°-160°	724.2	8.7
160°-170°	466.6	5.6
170°-180°	160.6	1.9
0°-30°	1177.4	14.1
0°-40°	1828.4	21.9
0°-60°	2896.5	34.7
0°-90°	3403.0	40.8
90°-120°	813.2	9.7
90°-150°	3595.6	43.1
90°-180°	4947.0	59.2
0°-180°	8350.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	1	15	24	31	33	8
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P905631

CATALOG NUMBER: DFN2DIP-PN2F0-040D050US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P905631

CATALOG NUMBER: DFN2DIP-PN2F0-040D050US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P905631

CATALOG NUMBER: DFN2DIP-PN2F0-040D050US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.53	11.29	11.57	12.33	13.73	6.50	7.26	7.54	8.30	9.70
	3H	12.19	12.86	13.23	13.91	15.33	7.67	8.35	8.72	9.40	10.82
	4H	12.78	13.42	13.84	14.47	15.90	8.10	8.75	9.16	9.80	11.22
	6H	13.18	13.77	14.25	14.83	16.26	8.41	9.00	9.48	10.05	11.49
	8H	13.29	13.86	14.37	14.93	16.36	8.49	9.05	9.56	10.12	11.55
	12H	13.34	13.88	14.42	14.94	16.40	8.52	9.05	9.60	10.12	11.58
4H	2H	10.54	11.18	11.61	12.23	13.66	7.08	7.72	8.14	8.77	10.20
	3H	12.34	12.87	13.41	13.95	15.39	8.40	8.94	9.47	10.02	11.45
	4H	13.01	13.50	14.09	14.57	16.03	8.93	9.42	10.01	10.49	11.95
	6H	13.50	13.92	14.59	15.02	16.47	9.33	9.75	10.42	10.84	12.30
	8H	13.67	14.06	14.75	15.14	16.61	9.45	9.84	10.53	10.92	12.39
	12H	13.75	14.10	14.85	15.20	16.67	9.50	9.85	10.60	10.95	12.43
8H	4H	12.97	13.36	14.06	14.45	15.92	9.19	9.59	10.28	10.67	12.14
	6H	13.51	13.83	14.62	14.96	16.43	9.69	10.01	10.80	11.14	12.61
	8H	13.71	14.00	14.83	15.11	16.59	9.86	10.15	10.98	11.26	12.74
	12H	13.84	14.08	14.96	15.19	16.72	9.97	10.22	11.09	11.32	12.85
12H	4H	12.92	13.27	14.02	14.37	15.85	9.19	9.55	10.30	10.65	12.12
	6H	13.48	13.77	14.60	14.88	16.36	9.73	10.01	10.85	11.12	12.61
	8H	13.69	13.94	14.81	15.04	16.57	9.92	10.17	11.04	11.28	12.80