

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928522

Luminaire Tested: DFN2DIP-HX4F0-040D110US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928522
REPORT IS A COMBINATION OF REPORTS P900946 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11646.3 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928522

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928522

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	20	19	18
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1002	1002	1002
5°	1004	986	992
10°	994	967	960
15°	980	935	910
20°	962	891	849
25°	944	842	790
30°	919	791	715
35°	895	737	649
40°	870	681	573
45°	841	618	505
50°	811	555	438
55°	781	488	374
60°	744	417	308
65°	703	346	277
70°	653	279	251
75°	590	246	228
80°	499	206	198
85°	349	138	149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1553 cd/sqm

TEST NUMBER: P928522

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.1
10°-20°	346.7	3.0
20°-30°	486.7	4.2
30°-40°	530.5	4.6
40°-50°	487.6	4.2
50°-60°	382.9	3.3
60°-70°	249.3	2.1
70°-80°	128.3	1.1
80°-90°	38.1	0.3
90°-100°	99.8	0.9
100°-110°	371.9	3.2
110°-120°	986.4	8.5
120°-130°	1636.0	14.0
130°-140°	1737.8	14.9
140°-150°	1615.1	13.9
150°-160°	1298.5	11.1
160°-170°	836.7	7.2
170°-180°	288.0	2.5
0°-30°	959.6	8.2
0°-40°	1490.1	12.8
0°-60°	2360.7	20.3
0°-90°	2776.3	23.8
90°-120°	1458.0	12.5
90°-150°	6446.8	55.4
90°-180°	8870.0	76.2
0°-180°	11646.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	2	26	44	55	59	11
95°	142	70	85	96	94	168
105°	666	731	134	158	166	711
115°	1259	1296	1351	337	180	1239
125°	1780	1808	1850	1865	1872	1587
135°	2202	2238	2257	2279	2275	1701
145°	2555	2553	2590	2605	2594	1598
155°	2813	2794	2820	2833	2816	1296
165°	2964	2951	2958	2973	2958	837
175°	3032	3017	3021	3036	3015	289
180°	3026	3026	3026	3026	3026	

TEST NUMBER: P928522

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	2.1	26.2	43.7	54.8	59.0
92.5°	54.8	46.0	52.5	57.0	59.0
95°	142.2	69.9	85.2	96.4	94.1
97.5°	256.1	76.7	111.5	118.3	120.4
100°	387.6	87.6	124.8	142.2	146.6
102.5°	531.9	527.7	129.2	153.1	159.9
105°	665.5	731.3	133.7	157.5	166.4
107.5°	821.0	875.6	138.1	161.9	170.8
110°	969.9	1015.7	383.2	164.3	172.9

TEST NUMBER: P928522

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1110.1	1149.3	1112.1	168.5	175.2
115°	1258.8	1295.9	1350.9	337.2	179.6
117.5°	1388.0	1431.7	1469.1	1155.8	582.3
120°	1532.5	1565.3	1604.8	1631.1	1335.5
122.5°	1655.0	1690.1	1734.0	1747.0	1749.4
125°	1779.8	1808.4	1850.0	1865.3	1871.8
127.5°	1893.7	1924.3	1957.3	1979.1	1981.3
130°	2001.0	2036.1	2060.0	2084.2	2082.2
132.5°	2110.4	2139.0	2163.0	2182.7	2180.7
135°	2202.5	2237.6	2257.1	2279.2	2274.7
137.5°	2298.7	2325.0	2347.0	2368.9	2362.4
140°	2392.8	2410.4	2434.4	2454.1	2443.2
142.5°	2471.8	2487.1	2515.5	2532.9	2522.0
145°	2555.0	2552.7	2589.8	2605.2	2594.3
147.5°	2627.1	2620.6	2657.7	2668.6	2660.1
150°	2697.2	2681.9	2717.0	2730.0	2719.1
152.5°	2756.2	2738.8	2771.6	2784.9	2769.5
155°	2813.2	2793.7	2819.9	2832.9	2815.5
157.5°	2859.2	2841.7	2861.5	2876.9	2859.2
160°	2898.7	2885.4	2898.7	2911.7	2896.3
162.5°	2933.5	2920.6	2931.5	2946.8	2927.1
165°	2964.2	2951.2	2957.7	2973.0	2957.7
167.5°	2988.4	2975.2	2981.9	2997.2	2977.5
170°	3008.2	2994.9	2999.3	3014.7	2994.9
172.5°	3021.1	3008.2	3012.6	3027.9	3008.2
175°	3032.0	3016.7	3021.1	3036.5	3014.7
177.5°	3036.5	3021.1	3023.5	3038.8	3019.1
180°	3025.6	3025.6	3025.6	3025.6	3025.6

TEST NUMBER: P928522

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.99	4.65	5.15	5.79	7.39	0.00	0.62	1.12	1.76	3.36
	3H	5.66	6.24	6.82	7.39	9.01	1.14	1.73	2.31	2.88	4.50
	4H	6.26	6.82	7.43	7.96	9.59	1.59	2.14	2.76	3.29	4.91
	6H	6.67	7.18	7.85	8.34	9.97	1.90	2.41	3.08	3.56	5.20
	8H	6.79	7.28	7.98	8.45	10.07	1.99	2.47	3.17	3.64	5.26
	12H	6.85	7.31	8.04	8.47	10.12	2.02	2.48	3.21	3.65	5.29
4H	2H	3.99	4.55	5.17	5.70	7.32	0.54	1.09	1.72	2.24	3.87
	3H	5.80	6.27	6.99	7.44	9.08	1.88	2.34	3.06	3.51	5.15
	4H	6.49	6.92	7.68	8.08	9.73	2.42	2.84	3.61	4.01	5.66
	6H	7.00	7.36	8.19	8.55	10.19	2.83	3.19	4.02	4.38	6.02
	8H	7.17	7.51	8.36	8.69	10.35	2.96	3.30	4.15	4.47	6.13
	12H	7.26	7.57	8.46	8.75	10.42	3.01	3.32	4.22	4.51	6.17
8H	4H	6.45	6.79	7.64	7.96	9.62	2.69	3.03	3.88	4.20	5.86
	6H	7.01	7.29	8.21	8.51	10.16	3.20	3.48	4.41	4.70	6.36
	8H	7.22	7.47	8.44	8.66	10.34	3.39	3.64	4.61	4.83	6.51
	12H	7.35	7.57	8.57	8.76	10.47	3.50	3.72	4.72	4.91	6.62
12H	4H	6.39	6.70	7.59	7.89	9.55	2.68	2.99	3.89	4.18	5.84
	6H	6.98	7.22	8.19	8.42	10.10	3.25	3.49	4.46	4.69	6.37
	8H	7.19	7.41	8.41	8.60	10.31	3.45	3.67	4.67	4.86	6.57