

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908310

Luminaire Tested: DFN2DIP-PN2F0-020D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908310
REPORT IS A COMBINATION OF REPORTS P899472 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D030US840-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4398.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 35.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908310
CATALOG NUMBER: DFN2DIP-PN2F0-020D030US840-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P908310

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US840-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1808	1775	1788
10°	1787	1737	1727
15°	1760	1675	1635
20°	1724	1593	1522
25°	1688	1501	1414
30°	1640	1407	1277
35°	1593	1306	1157
40°	1545	1203	1020
45°	1490	1088	896
50°	1432	973	775
55°	1372	850	658
60°	1302	722	540
65°	1221	593	483
70°	1123	472	433
75°	1000	409	389
80°	822	333	328
85°	537	206	233

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1490 cd/sqm



TEST NUMBER: P908310

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	1.8
10°-20°	214.8	4.9
20°-30°	301.5	6.9
30°-40°	328.7	7.5
40°-50°	302.1	6.9
50°-60°	237.3	5.4
60°-70°	154.4	3.5
70°-80°	79.5	1.8
80°-90°	23.0	0.5
90°-100°	59.3	1.3
100°-110°	188.4	4.3
110°-120°	322.4	7.3
120°-130°	424.0	9.6
130°-140°	475.9	10.8
140°-150°	466.7	10.6
150°-160°	391.5	8.9
160°-170°	259.6	5.9
170°-180°	90.7	2.1
0°-30°	594.5	13.5
0°-40°	923.2	21.0
0°-60°	1462.6	33.3
0°-90°	1719.5	39.1
90°-120°	570.1	13.0
90°-150°	1936.6	44.0
90°-180°	2678.0	60.9
0°-180°	4398.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	835	835	835	835	835	
5°	835	831	821	828	826	79
15°	794	786	760	746	738	224
25°	721	696	647	616	604	331
35°	621	582	516	468	452	389
45°	508	457	378	324	306	392
55°	386	327	246	200	186	345
65°	261	199	132	106	104	258
75°	139	86	60	55	54	147
85°	32	17	14	14	14	37
90°	1	10	28	27	28	4
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	



TEST NUMBER: P908310

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	834.8	834.8	834.8	834.8	834.8
2.5°	838.5	834.8	826.4	834.0	832.5
5°	834.8	831.0	821.1	828.0	825.7
7.5°	828.0	823.4	812.8	815.9	812.0
10°	818.9	813.5	798.5	796.2	791.7
12.5°	807.6	800.7	780.3	775.9	767.5
15°	794.0	785.6	759.9	745.6	738.1
17.5°	778.1	766.0	734.3	717.6	705.6
20°	759.9	744.8	707.1	688.2	671.6
22.5°	740.3	723.0	679.1	653.5	642.2
25°	720.7	696.5	646.6	615.7	604.3
27.5°	697.3	671.6	616.4	580.9	563.5
30°	672.4	643.6	583.2	544.7	524.2
32.5°	648.1	613.4	551.5	506.1	487.3
35°	621.0	582.5	516.0	468.4	451.7
37.5°	594.5	552.9	482.7	430.6	411.7
40°	566.5	521.3	448.0	394.4	374.7
42.5°	537.9	489.6	413.2	357.3	338.5
45°	507.7	457.0	377.8	324.1	305.9
47.5°	479.0	425.4	343.8	290.0	273.5
50°	447.3	393.6	310.5	258.3	242.6
52.5°	416.2	359.5	278.7	228.9	214.6
55°	386.0	327.1	245.5	200.3	185.8
57.5°	355.1	294.6	216.1	173.8	161.7
60°	323.4	262.9	185.1	146.6	134.5
62.5°	292.4	232.0	158.6	122.4	116.3
65°	260.6	199.4	131.5	105.8	103.5
67.5°	230.5	169.2	105.8	92.9	90.7
70°	198.6	139.8	87.6	80.1	77.1
72.5°	168.4	112.5	73.2	67.3	65.7
75°	139.0	86.0	60.4	55.1	54.4
77.5°	109.6	61.2	47.6	44.5	43.0
80°	82.3	43.8	36.3	33.2	33.2
82.5°	57.4	29.5	24.9	23.4	23.4
85°	32.4	16.6	14.3	14.3	14.3
87.5°	12.1	6.1	6.1	5.3	5.3
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P908310

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2



TEST NUMBER: P908310
 CATALOG NUMBER: DFN2DIP-PN2F0-020D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.97	8.72	9.03	9.77	11.20	3.94	4.69	5.00	5.74	7.17
	3H	9.63	10.29	10.69	11.36	12.80	5.11	5.78	6.17	6.84	8.28
	4H	10.22	10.85	11.29	11.91	13.36	5.54	6.18	6.62	7.24	8.69
	6H	10.62	11.20	11.70	12.27	13.73	5.85	6.43	6.93	7.49	8.95
	8H	10.73	11.29	11.82	12.37	13.82	5.93	6.48	7.01	7.56	9.01
	12H	10.78	11.31	11.87	12.39	13.86	5.96	6.48	7.05	7.56	9.04
4H	2H	7.98	8.61	9.06	9.68	11.12	4.52	5.15	5.60	6.22	7.66
	3H	9.78	10.30	10.86	11.39	12.85	5.84	6.37	6.93	7.46	8.92
	4H	10.45	10.93	11.54	12.01	13.49	6.37	6.85	7.46	7.93	9.42
	6H	10.94	11.36	12.04	12.46	13.93	6.77	7.18	7.87	8.28	9.76
	8H	11.10	11.49	12.20	12.59	14.08	6.88	7.27	7.98	8.37	9.86
	12H	11.18	11.53	12.30	12.64	14.14	6.93	7.28	8.05	8.39	9.89
8H	4H	10.41	10.79	11.51	11.89	13.38	6.63	7.02	7.73	8.12	9.60
	6H	10.95	11.27	12.07	12.40	13.89	7.12	7.44	8.24	8.58	10.07
	8H	11.15	11.43	12.28	12.55	14.06	7.30	7.58	8.43	8.70	10.21
	12H	11.27	11.52	12.40	12.63	14.18	7.40	7.65	8.53	8.76	10.31
12H	4H	10.35	10.70	11.47	11.81	13.31	6.63	6.98	7.75	8.09	9.58
	6H	10.92	11.20	12.05	12.32	13.83	7.17	7.45	8.29	8.57	10.07
	8H	11.12	11.37	12.25	12.48	14.03	7.36	7.60	8.49	8.72	10.26