

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928546

Luminaire Tested: DFN2DIP-HX4F0-050D080US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928546
REPORT IS A COMBINATION OF REPORTS P900894 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D080US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9918.6 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 102
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928546

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928546

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1252	1252	1252
5°	1254	1233	1240
10°	1242	1208	1200
15°	1225	1169	1138
20°	1203	1114	1061
25°	1179	1052	987
30°	1149	989	894
35°	1118	921	811
40°	1087	851	717
45°	1051	773	631
50°	1014	694	548
55°	976	610	467
60°	931	522	385
65°	879	432	346
70°	817	349	314
75°	738	307	285
80°	625	258	248
85°	437	173	186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1132 cd/sqm

TEST NUMBER: P928546

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.8	1.6
10°-20°	433.3	4.4
20°-30°	608.4	6.1
30°-40°	663.2	6.7
40°-50°	609.5	6.1
50°-60°	478.7	4.8
60°-70°	311.6	3.1
70°-80°	160.4	1.6
80°-90°	44.8	0.5
90°-100°	72.6	0.7
100°-110°	270.5	2.7
110°-120°	717.4	7.2
120°-130°	1189.8	12.0
130°-140°	1263.8	12.7
140°-150°	1174.6	11.8
150°-160°	944.4	9.5
160°-170°	608.5	6.1
170°-180°	209.4	2.1
0°-30°	1199.5	12.1
0°-40°	1862.7	18.8
0°-60°	2950.9	29.8
0°-90°	3467.6	35.0
90°-120°	1060.4	10.7
90°-150°	4688.7	47.3
90°-180°	6451.0	65.0
0°-180°	9918.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1684	1684	1684	1684	1684	
5°	1684	1677	1657	1670	1666	160
15°	1602	1585	1533	1504	1489	451
25°	1454	1405	1305	1242	1219	669
35°	1253	1175	1041	945	911	784
45°	1024	922	762	654	617	791
55°	779	660	495	404	375	696
65°	526	402	265	213	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	2	19	32	40	43	9
95°	103	51	62	70	68	122
105°	484	532	97	115	121	517
115°	916	942	982	245	131	901
125°	1294	1315	1345	1357	1361	1154
135°	1602	1627	1642	1658	1654	1237
145°	1858	1856	1884	1895	1887	1162
155°	2046	2032	2051	2060	2048	943
165°	2156	2146	2151	2162	2151	609
175°	2205	2194	2197	2208	2192	210
180°	2200	2200	2200	2200	2200	

TEST NUMBER: P928546

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.2	1684.2	1684.2	1684.2	1684.2
2.5°	1691.8	1684.2	1667.4	1682.7	1679.6
5°	1684.2	1676.6	1656.7	1670.4	1665.9
7.5°	1670.4	1661.4	1640.0	1646.1	1638.4
10°	1652.2	1641.5	1611.1	1606.4	1597.3
12.5°	1629.3	1615.7	1574.4	1565.4	1548.5
15°	1601.9	1585.1	1533.3	1504.4	1489.2
17.5°	1569.9	1545.5	1481.4	1447.9	1423.5
20°	1533.3	1502.8	1426.6	1388.6	1354.9
22.5°	1493.7	1458.6	1370.2	1318.4	1295.6
25°	1454.0	1405.2	1304.7	1242.2	1219.2
27.5°	1406.9	1354.9	1243.7	1172.1	1137.0
30°	1356.6	1298.5	1176.6	1098.9	1057.7
32.5°	1307.7	1237.6	1112.7	1021.2	983.1
35°	1252.9	1175.1	1041.1	945.0	911.4
37.5°	1199.5	1115.7	974.0	868.7	830.7
40°	1143.1	1051.8	903.8	795.6	756.0
42.5°	1085.3	987.7	833.7	720.9	682.9
45°	1024.3	922.1	762.1	653.8	617.2
47.5°	966.3	858.2	693.6	585.3	551.8
50°	902.4	794.1	626.5	521.2	489.3
52.5°	839.8	725.4	562.4	461.9	432.9
55°	778.8	659.9	495.3	403.9	375.0
57.5°	716.4	594.5	435.9	350.6	326.2
60°	652.3	530.4	373.4	295.8	271.3
62.5°	589.9	468.0	320.1	246.9	234.8
65°	525.8	402.4	265.2	213.4	208.8
67.5°	464.9	341.4	213.4	187.4	182.9
70°	400.9	282.0	176.8	161.5	155.4
72.5°	339.9	227.1	147.8	135.7	132.6
75°	280.4	173.7	121.9	111.2	109.8
77.5°	221.0	123.4	96.1	89.9	86.8
80°	166.1	88.4	73.1	67.1	67.1
82.5°	115.8	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.1	12.1	10.7	10.7
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.4	50.9	62.0	70.2	68.5
97.5°	186.2	55.7	81.1	86.1	87.5
100°	281.9	63.7	90.8	103.4	106.6
102.5°	386.9	383.8	94.0	111.3	116.3
105°	484.0	531.9	97.1	114.6	121.0
107.5°	597.1	636.8	100.4	117.8	124.2
110°	705.5	738.7	278.7	119.5	125.8

TEST NUMBER: P928546

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.3	835.9	808.9	122.5	127.5
115°	915.5	942.5	982.4	245.2	130.6
117.5°	1009.5	1041.2	1068.5	840.6	423.6
120°	1114.6	1138.4	1167.2	1186.2	971.2
122.5°	1203.6	1229.2	1261.1	1270.6	1272.3
125°	1294.4	1315.2	1345.4	1356.6	1361.3
127.5°	1377.2	1399.5	1423.6	1439.4	1440.9
130°	1455.3	1480.8	1498.2	1515.8	1514.3
132.5°	1534.9	1555.7	1573.1	1587.5	1585.9
135°	1601.8	1627.3	1641.5	1657.6	1654.4
137.5°	1671.8	1690.9	1706.9	1722.8	1718.1
140°	1740.2	1753.1	1770.5	1784.8	1776.9
142.5°	1797.7	1808.8	1829.4	1842.1	1834.2
145°	1858.2	1856.5	1883.5	1894.7	1886.7
147.5°	1910.6	1905.9	1932.9	1940.8	1934.6
150°	1961.6	1950.5	1976.0	1985.4	1977.5
152.5°	2004.6	1991.9	2015.7	2025.4	2014.2
155°	2046.0	2031.8	2050.9	2060.3	2047.7
157.5°	2079.4	2066.8	2081.1	2092.3	2079.4
160°	2108.2	2098.5	2108.2	2117.6	2106.4
162.5°	2133.5	2124.1	2132.0	2143.1	2128.8
165°	2155.8	2146.4	2151.1	2162.2	2151.1
167.5°	2173.4	2163.7	2168.6	2179.8	2165.5
170°	2187.8	2178.1	2181.3	2192.5	2178.1
172.5°	2197.2	2187.8	2191.0	2202.1	2187.8
175°	2205.1	2194.0	2197.2	2208.3	2192.5
177.5°	2208.3	2197.2	2198.9	2210.0	2195.7
180°	2200.4	2200.4	2200.4	2200.4	2200.4

TEST NUMBER: P928546

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.34	7.06	7.42	8.14	9.61	2.31	3.03	3.39	4.11	5.58
	3H	8.01	8.65	9.10	9.74	11.23	3.49	4.14	4.58	5.22	6.71
	4H	8.61	9.22	9.71	10.31	11.81	3.94	4.55	5.04	5.64	7.14
	6H	9.03	9.59	10.14	10.68	12.19	4.26	4.82	5.37	5.91	7.42
	8H	9.15	9.69	10.27	10.79	12.30	4.34	4.88	5.46	5.99	7.49
	12H	9.21	9.72	10.33	10.82	12.34	4.39	4.89	5.50	5.99	7.52
4H	2H	6.34	6.95	7.45	8.04	9.54	2.89	3.50	4.00	4.59	6.09
	3H	8.16	8.67	9.28	9.79	11.30	4.24	4.74	5.35	5.86	7.37
	4H	8.85	9.32	9.97	10.42	11.95	4.78	5.25	5.90	6.35	7.88
	6H	9.36	9.76	10.49	10.89	12.41	5.20	5.59	6.32	6.72	8.24
	8H	9.54	9.91	10.66	11.03	12.57	5.32	5.70	6.45	6.82	8.35
	12H	9.63	9.96	10.77	11.10	12.64	5.38	5.72	6.53	6.85	8.40
8H	4H	8.81	9.19	9.94	10.30	11.84	5.05	5.43	6.18	6.55	8.08
	6H	9.38	9.68	10.52	10.84	12.38	5.57	5.88	6.72	7.04	8.57
	8H	9.59	9.86	10.74	11.00	12.56	5.76	6.03	6.91	7.17	8.73
	12H	9.73	9.96	10.88	11.10	12.69	5.88	6.11	7.03	7.25	8.84
12H	4H	8.76	9.10	9.90	10.23	11.77	5.05	5.39	6.19	6.52	8.07
	6H	9.35	9.62	10.50	10.76	12.32	5.62	5.89	6.77	7.03	8.58
	8H	9.57	9.80	10.72	10.94	12.53	5.83	6.06	6.98	7.20	8.79

END OF REPORT