

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916355

Luminaire Tested: DFN2DIP-HX4F0-050D090US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916355
REPORT IS A COMBINATION OF REPORTS P899392 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D090US930-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9958.8 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 94.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916355

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916355

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	16	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1253	1253	1253
5°	1255	1233	1241
10°	1243	1209	1200
15°	1226	1169	1138
20°	1203	1114	1062
25°	1180	1052	988
30°	1149	989	894
35°	1119	921	812
40°	1088	851	717
45°	1052	773	631
50°	1015	694	548
55°	976	610	467
60°	931	522	385
65°	879	432	347
70°	817	349	314
75°	738	308	285
80°	625	258	248
85°	437	173	186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1748 cd/sqm

TEST NUMBER: P916355

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.6
10°-20°	433.5	4.4
20°-30°	608.6	6.1
30°-40°	663.4	6.7
40°-50°	609.7	6.1
50°-60°	478.8	4.8
60°-70°	311.7	3.1
70°-80°	160.4	1.6
80°-90°	47.5	0.5
90°-100°	143.6	1.4
100°-110°	456.3	4.6
110°-120°	780.8	7.8
120°-130°	1026.9	10.3
130°-140°	1152.6	11.6
140°-150°	1130.3	11.3
150°-160°	948.2	9.5
160°-170°	628.8	6.3
170°-180°	219.8	2.2
0°-30°	1200.0	12.0
0°-40°	1863.4	18.7
0°-60°	2951.9	29.6
0°-90°	3471.6	34.9
90°-120°	1380.7	13.9
90°-150°	4690.5	47.1
90°-180°	6487.0	65.1
0°-180°	9958.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	2	25	69	64	66	10
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	

TEST NUMBER: P916355

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1

TEST NUMBER: P916355

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7

TEST NUMBER: P916355

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.32	7.04	7.41	8.12	9.60	2.30	3.02	3.38	4.10	5.57
	3H	7.99	8.64	9.09	9.73	11.22	3.48	4.12	4.57	5.21	6.70
	4H	8.60	9.21	9.70	10.30	11.80	3.93	4.54	5.03	5.62	7.12
	6H	9.01	9.58	10.13	10.67	12.18	4.24	4.80	5.35	5.90	7.40
	8H	9.14	9.67	10.25	10.78	12.28	4.33	4.86	5.44	5.97	7.47
	12H	9.20	9.70	10.32	10.80	12.33	4.37	4.88	5.49	5.98	7.50
4H	2H	6.33	6.94	7.44	8.03	9.53	2.88	3.49	3.99	4.58	6.08
	3H	8.15	8.66	9.26	9.77	11.28	4.22	4.73	5.34	5.84	7.36
	4H	8.84	9.30	9.96	10.41	11.94	4.77	5.23	5.89	6.34	7.87
	6H	9.35	9.75	10.47	10.88	12.40	5.18	5.58	6.31	6.71	8.23
	8H	9.52	9.89	10.65	11.01	12.55	5.31	5.68	6.43	6.80	8.34
	12H	9.61	9.95	10.75	11.08	12.63	5.37	5.71	6.51	6.84	8.38
8H	4H	8.80	9.17	9.92	10.29	11.83	5.04	5.41	6.16	6.53	8.07
	6H	9.36	9.67	10.51	10.83	12.37	5.55	5.86	6.70	7.02	8.56
	8H	9.58	9.85	10.73	10.99	12.55	5.75	6.02	6.90	7.16	8.71
	12H	9.71	9.95	10.87	11.09	12.68	5.86	6.10	7.02	7.24	8.83
12H	4H	8.74	9.08	9.89	10.21	11.76	5.04	5.38	6.18	6.51	8.05
	6H	9.34	9.60	10.49	10.75	12.30	5.60	5.87	6.76	7.02	8.57
	8H	9.55	9.79	10.71	10.93	12.52	5.81	6.05	6.97	7.19	8.78

END OF REPORT