

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928584

Luminaire Tested: DFN2DIP-HX4F0-060D090US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928584
REPORT IS A COMBINATION OF REPORTS P900913 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D090US930-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12102.8 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928584
CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P928584

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1415	1415	1415
5°	1417	1395	1405
10°	1406	1377	1386
15°	1385	1354	1356
20°	1357	1323	1326
25°	1330	1285	1291
30°	1295	1250	1246
35°	1262	1209	1199
40°	1222	1167	1154
45°	1181	1126	1108
50°	1137	1082	1054
55°	1091	1031	1005
60°	1039	971	949
65°	982	909	883
70°	910	833	812
75°	809	743	747
80°	688	627	621
85°	499	427	413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1269 cd/sqm



TEST NUMBER: P928584

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	1.5
10°-20°	503.9	4.2
20°-30°	740.5	6.1
30°-40°	860.0	7.1
40°-50°	859.0	7.1
50°-60°	749.0	6.2
60°-70°	553.7	4.6
70°-80°	313.3	2.6
80°-90°	87.0	0.7
90°-100°	81.6	0.7
100°-110°	304.3	2.5
110°-120°	807.0	6.7
120°-130°	1338.5	11.1
130°-140°	1421.8	11.7
140°-150°	1321.4	10.9
150°-160°	1062.4	8.8
160°-170°	684.6	5.7
170°-180°	235.6	1.9
0°-30°	1423.5	11.8
0°-40°	2283.5	18.9
0°-60°	3891.5	32.2
0°-90°	4845.5	40.0
90°-120°	1193.0	9.9
90°-150°	5274.7	43.6
90°-180°	7257.0	60.0
0°-180°	12102.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	84
90°	2	22	36	45	48	11
95°	116	57	70	79	77	138
105°	544	598	109	129	136	582
115°	1030	1060	1105	276	147	1014
125°	1456	1480	1514	1526	1532	1299
135°	1802	1831	1847	1865	1861	1392
145°	2090	2088	2119	2132	2123	1307
155°	2302	2286	2307	2318	2304	1061
165°	2425	2415	2420	2432	2420	685
175°	2481	2468	2472	2484	2466	236
180°	2476	2476	2476	2476	2476	



TEST NUMBER: P928584

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	1.7	21.5	35.7	44.9	48.2
92.5°	44.9	37.7	43.0	46.6	48.2
95°	116.4	57.2	69.8	78.9	77.0
97.5°	209.5	62.8	91.3	96.7	98.5
100°	317.1	71.7	102.1	116.4	120.0
102.5°	435.2	431.8	105.7	125.3	130.8
105°	544.5	598.4	109.3	128.9	136.1
107.5°	671.7	716.4	113.0	132.5	139.8
110°	793.6	831.1	313.5	134.4	141.5



TEST NUMBER: P928584

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	908.2	940.3	909.9	137.8	143.4
115°	1029.9	1060.3	1105.2	275.9	146.9
117.5°	1135.6	1171.4	1202.0	945.7	476.4
120°	1253.9	1280.7	1313.0	1334.5	1092.7
122.5°	1354.1	1382.8	1418.8	1429.3	1431.3
125°	1456.2	1479.6	1513.6	1526.2	1531.5
127.5°	1549.3	1574.4	1601.5	1619.3	1621.0
130°	1637.2	1665.9	1685.5	1705.2	1703.6
132.5°	1726.7	1750.1	1769.7	1785.9	1784.2
135°	1802.0	1830.7	1846.7	1864.8	1861.2
137.5°	1880.8	1902.2	1920.3	1938.2	1932.9
140°	1957.7	1972.2	1991.8	2007.9	1999.0
142.5°	2022.4	2035.0	2058.1	2072.4	2063.5
145°	2090.5	2088.5	2119.0	2131.6	2122.6
147.5°	2149.4	2144.1	2174.5	2183.5	2176.4
150°	2206.9	2194.3	2223.0	2233.6	2224.7
152.5°	2255.1	2240.8	2267.7	2278.5	2265.9
155°	2301.7	2285.7	2307.2	2317.9	2303.6
157.5°	2339.4	2325.1	2341.3	2353.8	2339.4
160°	2371.6	2360.8	2371.6	2382.3	2369.8
162.5°	2400.2	2389.5	2398.5	2411.0	2394.9
165°	2425.3	2414.6	2420.0	2432.5	2420.0
167.5°	2445.1	2434.2	2439.7	2452.3	2436.1
170°	2461.2	2450.4	2454.0	2466.5	2450.4
172.5°	2471.9	2461.2	2464.8	2477.4	2461.2
175°	2480.8	2468.2	2471.9	2484.4	2466.5
177.5°	2484.4	2471.9	2473.8	2486.3	2470.2
180°	2475.5	2475.5	2475.5	2475.5	2475.5



TEST NUMBER: P928584
 CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.48	8.26	8.52	9.30	10.71	7.05	7.83	8.09	8.87	10.28
	3H	9.14	9.83	10.18	10.89	12.31	8.66	9.36	9.71	10.41	11.84
	4H	9.72	10.38	10.78	11.44	12.87	9.25	9.91	10.31	10.96	12.40
	6H	10.12	10.73	11.19	11.79	13.23	9.64	10.25	10.71	11.31	12.75
	8H	10.22	10.80	11.29	11.87	13.31	9.74	10.32	10.82	11.40	12.84
	12H	10.27	10.82	11.34	11.89	13.35	9.78	10.33	10.86	11.40	12.87
4H	2H	7.93	8.60	9.00	9.65	11.08	7.59	8.25	8.66	9.31	10.74
	3H	9.79	10.34	10.87	11.43	12.87	9.40	9.95	10.47	11.03	12.48
	4H	10.50	11.01	11.58	12.08	13.55	10.10	10.61	11.18	11.68	13.15
	6H	11.02	11.45	12.10	12.55	14.01	10.61	11.04	11.69	12.14	13.60
	8H	11.16	11.57	12.25	12.66	14.14	10.75	11.16	11.84	12.25	13.72
	12H	11.23	11.60	12.34	12.70	14.19	10.81	11.18	11.92	12.28	13.76
8H	4H	10.70	11.10	11.78	12.19	13.67	10.33	10.74	11.42	11.83	13.31
	6H	11.32	11.66	12.44	12.79	14.26	10.96	11.30	12.07	12.43	13.90
	8H	11.55	11.84	12.66	12.95	14.45	11.18	11.47	12.29	12.58	14.08
	12H	11.67	11.93	12.80	13.04	14.57	11.29	11.55	12.41	12.66	14.19
12H	4H	10.68	11.04	11.78	12.15	13.63	10.32	10.69	11.43	11.79	13.28
	6H	11.35	11.65	12.47	12.76	14.25	11.00	11.30	12.12	12.41	13.90
	8H	11.59	11.85	12.71	12.96	14.49	11.24	11.49	12.36	12.60	14.13