

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908327

Luminaire Tested: DFN2DIP-PN2F0-030D020US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908327
REPORT IS A COMBINATION OF REPORTS P900984 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D020US840-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4574.6 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 43.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908327

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908327

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2712	2712	2712
5°	2712	2663	2682
10°	2681	2605	2591
15°	2639	2513	2452
20°	2586	2389	2283
25°	2532	2251	2121
30°	2460	2110	1916
35°	2390	1959	1736
40°	2318	1804	1530
45°	2235	1632	1344
50°	2149	1459	1162
55°	2058	1275	988
60°	1953	1083	810
65°	1831	889	724
70°	1685	709	649
75°	1499	614	583
80°	1234	498	494
85°	807	310	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2235 cd/sqm

TEST NUMBER: P908327

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.6
10°-20°	322.1	7.0
20°-30°	452.3	9.9
30°-40°	493.0	10.8
40°-50°	453.1	9.9
50°-60°	355.9	7.8
60°-70°	231.6	5.1
70°-80°	119.2	2.6
80°-90°	31.6	0.7
90°-100°	22.5	0.5
100°-110°	83.8	1.8
110°-120°	222.2	4.9
120°-130°	368.6	8.1
130°-140°	391.5	8.6
140°-150°	363.9	8.0
150°-160°	292.5	6.4
160°-170°	188.5	4.1
170°-180°	64.9	1.4
0°-30°	891.8	19.5
0°-40°	1384.8	30.3
0°-60°	2193.8	48.0
0°-90°	2576.3	56.3
90°-120°	328.5	7.2
90°-150°	1452.4	31.7
90°-180°	1998.0	43.7
0°-180°	4574.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	0	6	10	12	13	4
95°	32	16	19	22	21	38
105°	150	165	30	35	38	160
115°	284	292	304	76	40	279
125°	401	407	417	420	422	358
135°	496	504	508	514	512	383
145°	576	575	584	587	584	360
155°	634	629	635	638	634	292
165°	668	665	666	670	666	189
175°	683	680	681	684	679	65
180°	682	682	682	682	682	

TEST NUMBER: P908327

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.5	6.0	9.8	12.3	13.3
92.5°	12.3	10.4	11.8	12.8	13.3
95°	32.0	15.8	19.2	21.7	21.2
97.5°	57.7	17.3	25.1	26.7	27.2
100°	87.4	19.7	28.1	32.0	33.0
102.5°	119.9	118.9	29.1	34.5	36.1
105°	150.0	164.7	30.1	35.4	37.5
107.5°	185.0	197.2	31.1	36.5	38.5
110°	218.5	228.8	86.3	37.1	39.0

TEST NUMBER: P908327

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	250.0	258.9	250.5	38.0	39.5
115°	283.6	292.0	304.4	75.9	40.5
117.5°	312.7	322.6	330.9	260.4	131.2
120°	345.3	352.6	361.5	367.5	300.8
122.5°	372.8	380.7	390.6	393.5	394.2
125°	401.0	407.4	416.8	420.2	421.7
127.5°	426.7	433.5	441.0	445.9	446.4
130°	450.8	458.7	464.1	469.6	469.1
132.5°	475.4	481.9	487.3	491.7	491.3
135°	496.2	504.1	508.5	513.5	512.5
137.5°	517.9	523.8	528.8	533.7	532.2
140°	539.1	543.1	548.5	552.9	550.5
142.5°	556.8	560.4	566.7	570.7	568.2
145°	575.6	575.1	583.5	586.9	584.5
147.5°	591.9	590.4	598.7	601.2	599.3
150°	607.6	604.2	612.1	615.0	612.6
152.5°	621.0	617.0	624.4	627.4	623.9
155°	633.8	629.3	635.3	638.2	634.3
157.5°	644.2	640.3	644.7	648.1	644.2
160°	653.1	650.1	653.1	656.0	652.6
162.5°	660.9	657.9	660.5	663.9	659.4
165°	667.8	664.9	666.3	669.8	666.3
167.5°	673.3	670.2	671.8	675.3	670.8
170°	677.7	674.7	675.7	679.1	674.7
172.5°	680.6	677.7	678.7	682.2	677.7
175°	683.1	679.6	680.6	684.1	679.1
177.5°	684.1	680.6	681.2	684.6	680.1
180°	681.7	681.7	681.7	681.7	681.7

TEST NUMBER: P908327

CATALOG NUMBER: DFN2DIP-PN2F0-030D020US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.07	11.95	11.98	12.87	14.05	7.03	7.92	7.94	8.84	10.02
	3H	12.73	13.52	13.65	14.45	15.66	8.21	9.00	9.13	9.93	11.14
	4H	13.33	14.07	14.26	15.01	16.22	8.65	9.40	9.59	10.33	11.55
	6H	13.73	14.42	14.68	15.36	16.59	8.96	9.65	9.91	10.59	11.82
	8H	13.85	14.51	14.81	15.47	16.69	9.04	9.70	10.00	10.66	11.88
	12H	13.91	14.53	14.87	15.48	16.73	9.08	9.70	10.04	10.66	11.91
4H	2H	11.09	11.83	12.03	12.77	13.99	7.63	8.37	8.57	9.31	10.52
	3H	12.90	13.52	13.85	14.49	15.72	8.96	9.58	9.91	10.55	11.78
	4H	13.58	14.14	14.54	15.10	16.36	9.50	10.06	10.46	11.02	12.28
	6H	14.08	14.56	15.05	15.55	16.80	9.90	10.39	10.87	11.37	12.63
	8H	14.24	14.69	15.21	15.67	16.94	10.02	10.48	11.00	11.45	12.72
	12H	14.33	14.74	15.32	15.73	17.00	10.08	10.49	11.07	11.48	12.76
8H	4H	13.54	14.00	14.52	14.98	16.24	9.77	10.22	10.74	11.20	12.47
	6H	14.09	14.47	15.09	15.49	16.75	10.27	10.64	11.27	11.66	12.93
	8H	14.29	14.62	15.30	15.63	16.92	10.44	10.77	11.45	11.78	13.07
	12H	14.42	14.71	15.43	15.71	17.04	10.55	10.84	11.56	11.84	13.18
12H	4H	13.50	13.91	14.49	14.90	16.18	9.77	10.18	10.77	11.18	12.45
	6H	14.06	14.39	15.07	15.40	16.69	10.31	10.64	11.32	11.65	12.93
	8H	14.27	14.56	15.28	15.57	16.90	10.51	10.80	11.52	11.80	13.13