

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908329

Luminaire Tested: DFN2DIP-PN2F0-030D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908329
REPORT IS A COMBINATION OF REPORTS P900993 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D030US840-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5998.7 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908329

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908329

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2553	2553	2553
5°	2553	2512	2531
10°	2528	2473	2493
15°	2487	2427	2435
20°	2433	2365	2377
25°	2379	2292	2310
30°	2312	2223	2226
35°	2248	2144	2137
40°	2170	2063	2052
45°	2093	1982	1965
50°	2007	1896	1865
55°	1918	1798	1772
60°	1816	1681	1665
65°	1705	1560	1539
70°	1564	1412	1402
75°	1370	1235	1271
80°	1133	1008	1032
85°	770	637	647

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2093 cd/sqm

TEST NUMBER: P908329

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.8
10°-20°	312.2	5.2
20°-30°	458.8	7.6
30°-40°	532.8	8.9
40°-50°	532.2	8.9
50°-60°	464.1	7.7
60°-70°	343.1	5.7
70°-80°	194.1	3.2
80°-90°	53.0	0.9
90°-100°	33.7	0.6
100°-110°	125.7	2.1
110°-120°	333.3	5.6
120°-130°	552.9	9.2
130°-140°	587.3	9.8
140°-150°	545.8	9.1
150°-160°	438.8	7.3
160°-170°	282.8	4.7
170°-180°	97.3	1.6
0°-30°	881.9	14.7
0°-40°	1414.7	23.6
0°-60°	2411.0	40.2
0°-90°	3001.1	50.0
90°-120°	492.7	8.2
90°-150°	2178.7	36.3
90°-180°	2998.0	50.0
0°-180°	5998.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	1	9	15	19	20	6
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P908329

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5

TEST NUMBER: P908329

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P908329

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.41	11.28	11.37	12.25	13.52	9.98	10.84	10.93	11.81	13.08
	3H	12.06	12.83	13.02	13.81	15.10	11.57	12.35	12.54	13.33	14.62
	4H	12.63	13.36	13.61	14.35	15.65	12.15	12.88	13.13	13.86	15.17
	6H	13.01	13.69	14.01	14.68	15.99	12.53	13.20	13.52	14.19	15.51
	8H	13.11	13.75	14.11	14.76	16.07	12.62	13.27	13.62	14.27	15.58
	12H	13.15	13.76	14.16	14.76	16.10	12.66	13.27	13.66	14.27	15.61
4H	2H	10.87	11.60	11.85	12.58	13.88	10.52	11.25	11.50	12.23	13.53
	3H	12.71	13.32	13.71	14.33	15.65	12.31	12.92	13.31	13.93	15.25
	4H	13.41	13.96	14.41	14.97	16.31	12.99	13.55	14.00	14.56	15.90
	6H	13.90	14.38	14.92	15.41	16.75	13.48	13.96	14.50	14.99	16.33
	8H	14.04	14.49	15.06	15.52	16.87	13.62	14.07	14.64	15.09	16.44
	12H	14.11	14.51	15.14	15.55	16.91	13.67	14.08	14.71	15.12	16.47
8H	4H	13.59	14.04	14.61	15.07	16.42	13.22	13.67	14.24	14.70	16.05
	6H	14.20	14.57	15.24	15.64	16.98	13.83	14.20	14.87	15.26	16.61
	8H	14.41	14.73	15.46	15.78	17.15	14.03	14.35	15.08	15.40	16.77
	12H	14.52	14.81	15.58	15.86	17.27	14.13	14.42	15.18	15.46	16.87
12H	4H	13.58	13.98	14.61	15.02	16.38	13.21	13.62	14.25	14.66	16.02
	6H	14.22	14.55	15.27	15.60	16.97	13.86	14.19	14.91	15.24	16.61
	8H	14.45	14.74	15.50	15.78	17.19	14.08	14.37	15.13	15.41	16.83

END OF REPORT