

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928590

Luminaire Tested: DFN2DIP-HX4F0-060D100US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928590
REPORT IS A COMBINATION OF REPORTS P900932 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D100US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12225.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 130.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928590

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928590

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	30	28	26
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1505	1479	1488
10°	1491	1450	1440
15°	1470	1402	1365
20°	1443	1336	1273
25°	1415	1263	1185
30°	1378	1187	1072
35°	1342	1105	973
40°	1305	1021	860
45°	1262	927	757
50°	1217	833	657
55°	1171	732	561
60°	1117	626	462
65°	1055	519	416
70°	980	418	376
75°	886	369	343
80°	749	310	297
85°	524	208	224

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1411 cd/sqm

TEST NUMBER: P928590

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.4	1.5
10°-20°	520.0	4.3
20°-30°	730.0	6.0
30°-40°	795.8	6.5
40°-50°	731.4	6.0
50°-60°	574.4	4.7
60°-70°	373.9	3.1
70°-80°	192.5	1.6
80°-90°	54.0	0.4
90°-100°	90.7	0.7
100°-110°	338.1	2.8
110°-120°	896.7	7.3
120°-130°	1487.3	12.2
130°-140°	1579.8	12.9
140°-150°	1468.3	12.0
150°-160°	1180.4	9.7
160°-170°	760.6	6.2
170°-180°	261.8	2.1
0°-30°	1439.4	11.8
0°-40°	2235.2	18.3
0°-60°	3541.0	29.0
0°-90°	4161.3	34.0
90°-120°	1325.5	10.8
90°-150°	5860.8	47.9
90°-180°	8064.0	66.0
0°-180°	12225.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2021	2021	2021	2021	2021	
5°	2021	2012	1988	2005	1999	192
15°	1922	1902	1840	1805	1787	542
25°	1745	1686	1566	1491	1463	802
35°	1504	1410	1249	1134	1094	941
45°	1229	1106	915	784	741	949
55°	935	792	594	485	450	835
65°	631	483	318	256	250	626
75°	336	208	146	134	132	356
85°	79	40	35	35	35	90
90°	2	24	40	50	54	11
95°	129	64	78	88	86	153
105°	605	665	122	143	151	646
115°	1144	1178	1228	306	163	1127
125°	1618	1644	1682	1696	1702	1443
135°	2002	2034	2052	2072	2068	1547
145°	2323	2321	2354	2368	2358	1453
155°	2558	2540	2564	2575	2560	1178
165°	2695	2683	2689	2703	2689	761
175°	2756	2742	2746	2760	2741	262
180°	2750	2750	2750	2750	2750	

TEST NUMBER: P928590

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.0	2021.0	2021.0	2021.0	2021.0
2.5°	2030.2	2021.0	2000.8	2019.2	2015.6
5°	2021.0	2011.9	1988.0	2004.6	1999.1
7.5°	2004.6	1993.7	1968.1	1975.2	1966.1
10°	1982.6	1969.8	1933.3	1927.7	1916.8
12.5°	1955.3	1938.7	1889.3	1878.4	1858.2
15°	1922.3	1902.0	1839.9	1805.2	1787.0
17.5°	1883.9	1854.5	1777.7	1737.5	1708.2
20°	1839.9	1803.3	1711.9	1666.3	1625.9
22.5°	1792.4	1750.3	1644.2	1582.1	1554.7
25°	1744.9	1686.3	1565.6	1490.7	1463.2
27.5°	1688.3	1625.9	1492.4	1406.4	1364.4
30°	1627.9	1558.2	1411.9	1318.8	1269.3
32.5°	1569.3	1485.1	1335.3	1225.4	1179.6
35°	1503.5	1410.2	1249.3	1134.0	1093.6
37.5°	1439.5	1338.7	1168.8	1042.5	996.8
40°	1371.7	1262.1	1084.5	954.7	907.2
42.5°	1302.3	1185.3	1000.5	865.0	819.5
45°	1229.1	1106.4	914.6	784.5	740.7
47.5°	1159.7	1029.8	832.3	702.3	662.1
50°	1082.8	953.0	751.8	625.4	587.2
52.5°	1007.7	870.5	674.9	554.2	519.5
55°	934.6	791.9	594.4	484.8	450.0
57.5°	859.7	713.3	523.1	420.7	391.4
60°	782.8	636.5	448.1	354.9	325.6
62.5°	707.9	561.6	384.0	296.3	281.7
65°	631.1	482.8	318.3	256.2	250.5
67.5°	557.9	409.6	256.2	224.9	219.5
70°	481.0	338.4	212.1	193.9	186.5
72.5°	407.9	272.5	177.3	162.8	159.1
75°	336.5	208.4	146.3	133.5	131.8
77.5°	265.3	148.1	115.2	107.9	104.2
80°	199.3	106.1	87.7	80.5	80.5
82.5°	139.0	71.4	60.3	56.6	56.6
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.3	14.6	14.6	12.8	12.8
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.4	79.6	113.4	129.3	133.3
102.5°	483.5	479.8	117.4	139.2	145.3
105°	605.1	664.8	121.5	143.2	151.3
107.5°	746.4	796.0	125.5	147.3	155.3
110°	881.7	923.4	348.3	149.4	157.1

TEST NUMBER: P928590

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.1	1044.8	1011.1	153.1	159.3
115°	1144.3	1178.2	1228.0	306.5	163.3
117.5°	1261.8	1301.6	1335.5	1050.8	529.4
120°	1393.2	1423.0	1458.9	1482.8	1214.1
122.5°	1504.6	1536.4	1576.4	1588.2	1590.3
125°	1618.0	1644.0	1681.8	1695.8	1701.6
127.5°	1721.5	1749.4	1779.4	1799.3	1801.2
130°	1819.1	1851.0	1872.8	1894.7	1892.8
132.5°	1918.6	1944.6	1966.4	1984.3	1982.4
135°	2002.3	2034.2	2051.9	2072.0	2068.0
137.5°	2089.7	2113.6	2133.7	2153.6	2147.6
140°	2175.2	2191.4	2213.1	2231.1	2221.1
142.5°	2247.1	2261.1	2286.8	2302.6	2292.8
145°	2322.8	2320.6	2354.5	2368.4	2358.4
147.5°	2388.2	2382.3	2416.1	2426.0	2418.3
150°	2452.0	2438.1	2470.0	2481.8	2471.9
152.5°	2505.6	2489.8	2519.7	2531.6	2517.7
155°	2557.5	2539.7	2563.6	2575.4	2559.6
157.5°	2599.3	2583.5	2601.4	2615.3	2599.3
160°	2635.2	2623.2	2635.2	2647.0	2633.1
162.5°	2666.8	2655.0	2665.0	2678.9	2661.0
165°	2694.7	2682.9	2688.8	2702.8	2688.8
167.5°	2716.7	2704.7	2710.9	2724.8	2706.8
170°	2734.7	2722.7	2726.7	2740.6	2722.7
172.5°	2746.5	2734.7	2738.7	2752.7	2734.7
175°	2756.4	2742.5	2746.5	2760.5	2740.6
177.5°	2760.5	2746.5	2748.7	2762.6	2744.6
180°	2750.5	2750.5	2750.5	2750.5	2750.5

TEST NUMBER: P928590

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.86	7.57	7.95	8.66	10.14	2.83	3.55	3.92	4.63	6.11
	3H	8.53	9.17	9.62	10.26	11.76	4.01	4.65	5.11	5.74	7.25
	4H	9.13	9.74	10.24	10.83	12.34	4.46	5.07	5.57	6.16	7.67
	6H	9.55	10.11	10.66	11.20	12.72	4.78	5.33	5.89	6.43	7.95
	8H	9.67	10.20	10.79	11.31	12.83	4.86	5.39	5.98	6.51	8.02
	12H	9.73	10.23	10.85	11.34	12.87	4.90	5.41	6.03	6.51	8.05
4H	2H	6.86	7.47	7.98	8.56	10.07	3.41	4.02	4.53	5.11	6.62
	3H	8.68	9.19	9.80	10.31	11.83	4.75	5.26	5.88	6.38	7.90
	4H	9.37	9.83	10.50	10.94	12.48	5.30	5.76	6.42	6.87	8.41
	6H	9.88	10.28	11.01	11.41	12.94	5.71	6.11	6.85	7.24	8.78
	8H	10.05	10.42	11.19	11.55	13.10	5.84	6.21	6.97	7.34	8.88
	12H	10.14	10.48	11.29	11.62	13.17	5.90	6.24	7.05	7.37	8.93
8H	4H	9.33	9.70	10.46	10.82	12.37	5.57	5.94	6.70	7.07	8.61
	6H	9.89	10.20	11.05	11.37	12.91	6.09	6.39	7.24	7.56	9.10
	8H	10.11	10.38	11.27	11.52	13.09	6.28	6.55	7.44	7.69	9.26
	12H	10.24	10.48	11.41	11.62	13.22	6.39	6.63	7.56	7.77	9.37
12H	4H	9.28	9.61	10.42	10.75	12.30	5.57	5.91	6.72	7.04	8.60
	6H	9.87	10.14	11.03	11.28	12.85	6.14	6.40	7.29	7.55	9.12
	8H	10.08	10.32	11.25	11.46	13.06	6.34	6.58	7.50	7.72	9.32

END OF REPORT