

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928594

Luminaire Tested: DFN2DIP-HX4F0-060D110US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928594
REPORT IS A COMBINATION OF REPORTS P900950 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D110US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13031.8 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 141.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928594

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928594

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	31	30	29
3	78	70	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	44	37	32	51	41	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1505	1479	1488
10°	1491	1450	1440
15°	1470	1402	1365
20°	1443	1336	1273
25°	1415	1263	1185
30°	1378	1187	1072
35°	1342	1105	973
40°	1305	1021	860
45°	1262	927	757
50°	1217	833	657
55°	1171	732	561
60°	1117	626	462
65°	1055	519	416
70°	980	418	376
75°	886	369	343
80°	749	310	297
85°	524	208	224

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1553 cd/sqm

TEST NUMBER: P928594

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.4	1.5
10°-20°	520.0	4.0
20°-30°	730.0	5.6
30°-40°	795.8	6.1
40°-50°	731.4	5.6
50°-60°	574.4	4.4
60°-70°	373.9	2.9
70°-80°	192.5	1.5
80°-90°	54.4	0.4
90°-100°	99.8	0.8
100°-110°	371.9	2.9
110°-120°	986.4	7.6
120°-130°	1636.0	12.6
130°-140°	1737.8	13.3
140°-150°	1615.1	12.4
150°-160°	1298.5	10.0
160°-170°	836.7	6.4
170°-180°	288.0	2.2
0°-30°	1439.4	11.0
0°-40°	2235.2	17.2
0°-60°	3541.0	27.2
0°-90°	4161.8	31.9
90°-120°	1458.0	11.2
90°-150°	6446.8	49.5
90°-180°	8870.0	68.1
0°-180°	13031.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2021	2021	2021	2021	2021	
5°	2021	2012	1988	2005	1999	192
15°	1922	1902	1840	1805	1787	542
25°	1745	1686	1566	1491	1463	802
35°	1504	1410	1249	1134	1094	941
45°	1229	1106	915	784	741	949
55°	935	792	594	485	450	835
65°	631	483	318	256	250	626
75°	336	208	146	134	132	356
85°	79	40	35	35	35	90
90°	2	26	44	55	59	12
95°	142	70	85	96	94	168
105°	666	731	134	158	166	711
115°	1259	1296	1351	337	180	1239
125°	1780	1808	1850	1865	1872	1587
135°	2202	2238	2257	2279	2275	1701
145°	2555	2553	2590	2605	2594	1598
155°	2813	2794	2820	2833	2816	1296
165°	2964	2951	2958	2973	2958	837
175°	3032	3017	3021	3036	3015	289
180°	3026	3026	3026	3026	3026	

TEST NUMBER: P928594

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.0	2021.0	2021.0	2021.0	2021.0
2.5°	2030.2	2021.0	2000.8	2019.2	2015.6
5°	2021.0	2011.9	1988.0	2004.6	1999.1
7.5°	2004.6	1993.7	1968.1	1975.2	1966.1
10°	1982.6	1969.8	1933.3	1927.7	1916.8
12.5°	1955.3	1938.7	1889.3	1878.4	1858.2
15°	1922.3	1902.0	1839.9	1805.2	1787.0
17.5°	1883.9	1854.5	1777.7	1737.5	1708.2
20°	1839.9	1803.3	1711.9	1666.3	1625.9
22.5°	1792.4	1750.3	1644.2	1582.1	1554.7
25°	1744.9	1686.3	1565.6	1490.7	1463.2
27.5°	1688.3	1625.9	1492.4	1406.4	1364.4
30°	1627.9	1558.2	1411.9	1318.8	1269.3
32.5°	1569.3	1485.1	1335.3	1225.4	1179.6
35°	1503.5	1410.2	1249.3	1134.0	1093.6
37.5°	1439.5	1338.7	1168.8	1042.5	996.8
40°	1371.7	1262.1	1084.5	954.7	907.2
42.5°	1302.3	1185.3	1000.5	865.0	819.5
45°	1229.1	1106.4	914.6	784.5	740.7
47.5°	1159.7	1029.8	832.3	702.3	662.1
50°	1082.8	953.0	751.8	625.4	587.2
52.5°	1007.7	870.5	674.9	554.2	519.5
55°	934.6	791.9	594.4	484.8	450.0
57.5°	859.7	713.3	523.1	420.7	391.4
60°	782.8	636.5	448.1	354.9	325.6
62.5°	707.9	561.6	384.0	296.3	281.7
65°	631.1	482.8	318.3	256.2	250.5
67.5°	557.9	409.6	256.2	224.9	219.5
70°	481.0	338.4	212.1	193.9	186.5
72.5°	407.9	272.5	177.3	162.8	159.1
75°	336.5	208.4	146.3	133.5	131.8
77.5°	265.3	148.1	115.2	107.9	104.2
80°	199.3	106.1	87.7	80.5	80.5
82.5°	139.0	71.4	60.3	56.6	56.6
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.3	14.6	14.6	12.8	12.8
90°	2.1	26.2	43.7	54.8	59.0
92.5°	54.8	46.0	52.5	57.0	59.0
95°	142.2	69.9	85.2	96.4	94.1
97.5°	256.1	76.7	111.5	118.3	120.4
100°	387.6	87.6	124.8	142.2	146.6
102.5°	531.9	527.7	129.2	153.1	159.9
105°	665.5	731.3	133.7	157.5	166.4
107.5°	821.0	875.6	138.1	161.9	170.8
110°	969.9	1015.7	383.2	164.3	172.9

TEST NUMBER: P928594

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1110.1	1149.3	1112.1	168.5	175.2
115°	1258.8	1295.9	1350.9	337.2	179.6
117.5°	1388.0	1431.7	1469.1	1155.8	582.3
120°	1532.5	1565.3	1604.8	1631.1	1335.5
122.5°	1655.0	1690.1	1734.0	1747.0	1749.4
125°	1779.8	1808.4	1850.0	1865.3	1871.8
127.5°	1893.7	1924.3	1957.3	1979.1	1981.3
130°	2001.0	2036.1	2060.0	2084.2	2082.2
132.5°	2110.4	2139.0	2163.0	2182.7	2180.7
135°	2202.5	2237.6	2257.1	2279.2	2274.7
137.5°	2298.7	2325.0	2347.0	2368.9	2362.4
140°	2392.8	2410.4	2434.4	2454.1	2443.2
142.5°	2471.8	2487.1	2515.5	2532.9	2522.0
145°	2555.0	2552.7	2589.8	2605.2	2594.3
147.5°	2627.1	2620.6	2657.7	2668.6	2660.1
150°	2697.2	2681.9	2717.0	2730.0	2719.1
152.5°	2756.2	2738.8	2771.6	2784.9	2769.5
155°	2813.2	2793.7	2819.9	2832.9	2815.5
157.5°	2859.2	2841.7	2861.5	2876.9	2859.2
160°	2898.7	2885.4	2898.7	2911.7	2896.3
162.5°	2933.5	2920.6	2931.5	2946.8	2927.1
165°	2964.2	2951.2	2957.7	2973.0	2957.7
167.5°	2988.4	2975.2	2981.9	2997.2	2977.5
170°	3008.2	2994.9	2999.3	3014.7	2994.9
172.5°	3021.1	3008.2	3012.6	3027.9	3008.2
175°	3032.0	3016.7	3021.1	3036.5	3014.7
177.5°	3036.5	3021.1	3023.5	3038.8	3019.1
180°	3025.6	3025.6	3025.6	3025.6	3025.6

TEST NUMBER: P928594

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.59	7.29	7.69	8.39	9.90	2.56	3.27	3.67	4.36	5.87
	3H	8.26	8.89	9.37	9.99	11.52	3.74	4.37	4.86	5.48	7.00
	4H	8.86	9.46	9.98	10.56	12.10	4.19	4.78	5.31	5.89	7.42
	6H	9.28	9.83	10.41	10.93	12.48	4.51	5.05	5.64	6.16	7.71
	8H	9.40	9.92	10.53	11.05	12.58	4.59	5.11	5.73	6.24	7.77
	12H	9.46	9.95	10.60	11.07	12.63	4.63	5.13	5.77	6.24	7.80
4H	2H	6.59	7.19	7.72	8.29	9.83	3.14	3.74	4.27	4.84	6.38
	3H	8.41	8.91	9.55	10.04	11.58	4.48	4.98	5.62	6.11	7.66
	4H	9.10	9.55	10.24	10.68	12.24	5.03	5.48	6.17	6.60	8.17
	6H	9.61	10.00	10.75	11.14	12.70	5.44	5.83	6.59	6.98	8.53
	8H	9.78	10.15	10.93	11.28	12.85	5.57	5.93	6.71	7.07	8.64
	12H	9.87	10.20	11.03	11.35	12.93	5.63	5.96	6.79	7.11	8.68
8H	4H	9.06	9.42	10.20	10.56	12.13	5.30	5.66	6.44	6.80	8.37
	6H	9.62	9.92	10.78	11.10	12.67	5.82	6.11	6.98	7.29	8.86
	8H	9.84	10.10	11.01	11.26	12.85	6.01	6.27	7.18	7.43	9.02
	12H	9.97	10.20	11.14	11.36	12.98	6.12	6.35	7.29	7.51	9.13
12H	4H	9.00	9.33	10.16	10.48	12.06	5.30	5.63	6.46	6.78	8.35
	6H	9.60	9.86	10.77	11.01	12.60	5.86	6.13	7.03	7.28	8.87
	8H	9.81	10.04	10.98	11.20	12.82	6.07	6.30	7.24	7.45	9.08

END OF REPORT