

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908343

Luminaire Tested: DFN2DIP-PN2F0-030D060US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908343
REPORT IS A COMBINATION OF REPORTS P901024 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D060US840-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8573.7 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 80.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908343

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908343

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2712	2712	2712
5°	2712	2663	2682
10°	2681	2605	2591
15°	2639	2513	2452
20°	2586	2389	2283
25°	2532	2251	2121
30°	2460	2110	1916
35°	2390	1959	1736
40°	2318	1804	1530
45°	2235	1632	1344
50°	2149	1459	1162
55°	2058	1275	988
60°	1953	1083	810
65°	1831	889	724
70°	1685	709	649
75°	1499	614	583
80°	1234	498	494
85°	807	310	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2235 cd/sqm

TEST NUMBER: P908343

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	1.4
10°-20°	322.1	3.8
20°-30°	452.3	5.3
30°-40°	493.0	5.8
40°-50°	453.1	5.3
50°-60°	355.9	4.2
60°-70°	231.6	2.7
70°-80°	119.2	1.4
80°-90°	34.0	0.4
90°-100°	67.4	0.8
100°-110°	251.4	2.9
110°-120°	666.7	7.8
120°-130°	1105.7	12.9
130°-140°	1174.5	13.7
140°-150°	1091.6	12.7
150°-160°	877.6	10.2
160°-170°	565.5	6.6
170°-180°	194.6	2.3
0°-30°	891.8	10.4
0°-40°	1384.8	16.2
0°-60°	2193.8	25.6
0°-90°	2578.7	30.1
90°-120°	985.5	11.5
90°-150°	4357.2	50.8
90°-180°	5995.0	69.9
0°-180°	8573.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	18	30	37	40	8
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P908343

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P908343

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9

TEST NUMBER: P908343

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.28	8.97	9.39	10.07	11.60	4.24	4.93	5.36	6.04	7.57
	3H	9.92	10.54	11.05	11.65	13.20	5.40	6.02	6.53	7.14	8.68
	4H	10.51	11.10	11.64	12.21	13.77	5.84	6.42	6.97	7.54	9.09
	6H	10.91	11.45	12.05	12.56	14.13	6.13	6.67	7.28	7.79	9.36
	8H	11.02	11.53	12.17	12.67	14.22	6.21	6.72	7.36	7.86	9.42
	12H	11.07	11.56	12.22	12.68	14.26	6.24	6.73	7.39	7.86	9.44
4H	2H	8.27	8.86	9.41	9.97	11.53	4.81	5.39	5.95	6.51	8.06
	3H	10.06	10.55	11.21	11.69	13.26	6.13	6.61	7.27	7.76	9.32
	4H	10.74	11.18	11.88	12.31	13.90	6.65	7.10	7.80	8.23	9.82
	6H	11.22	11.61	12.38	12.76	14.34	7.05	7.43	8.20	8.59	10.16
	8H	11.38	11.74	12.54	12.89	14.48	7.16	7.52	8.32	8.67	10.26
	12H	11.46	11.79	12.63	12.94	14.54	7.21	7.54	8.38	8.69	10.29
8H	4H	10.69	11.05	11.84	12.19	13.78	6.91	7.27	8.07	8.42	10.01
	6H	11.23	11.52	12.40	12.71	14.30	7.40	7.70	8.58	8.89	10.48
	8H	11.43	11.69	12.61	12.85	14.46	7.58	7.84	8.76	9.00	10.61
	12H	11.55	11.77	12.73	12.94	14.58	7.68	7.91	8.86	9.07	10.71
12H	4H	10.63	10.96	11.80	12.11	13.71	6.91	7.23	8.08	8.39	9.99
	6H	11.20	11.46	12.38	12.62	14.23	7.45	7.70	8.63	8.87	10.48
	8H	11.40	11.63	12.58	12.79	14.43	7.64	7.86	8.82	9.02	10.67