

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928614

Luminaire Tested: DFN2DIP-HX4F0-070D070US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928614
REPORT IS A COMBINATION OF REPORTS P900880 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D070US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10497.2 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928614

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928614

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1753	1753	1753
5°	1756	1726	1737
10°	1739	1692	1680
15°	1715	1636	1593
20°	1684	1559	1486
25°	1651	1473	1382
30°	1608	1384	1251
35°	1565	1289	1136
40°	1522	1191	1004
45°	1472	1082	884
50°	1420	971	767
55°	1366	853	654
60°	1303	730	539
65°	1231	605	485
70°	1143	488	439
75°	1034	431	399
80°	874	362	347
85°	611	242	261

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1472 cd/sqm

TEST NUMBER: P928614

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	2.1
10°-20°	606.6	5.8
20°-30°	851.7	8.1
30°-40°	928.4	8.8
40°-50°	853.3	8.1
50°-60°	670.1	6.4
60°-70°	436.2	4.2
70°-80°	224.5	2.1
80°-90°	60.7	0.6
90°-100°	63.5	0.6
100°-110°	236.7	2.3
110°-120°	627.7	6.0
120°-130°	1041.1	9.9
130°-140°	1105.9	10.5
140°-150°	1027.8	9.8
150°-160°	826.3	7.9
160°-170°	532.4	5.1
170°-180°	183.3	1.7
0°-30°	1679.3	16.0
0°-40°	2607.7	24.8
0°-60°	4131.2	39.4
0°-90°	4852.6	46.2
90°-120°	927.9	8.8
90°-150°	4102.6	39.1
90°-180°	5645.0	53.8
0°-180°	10497.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2358	2358	2358	2358	2358	
5°	2358	2347	2319	2339	2332	224
15°	2243	2219	2147	2106	2085	632
25°	2036	1967	1826	1739	1707	936
35°	1754	1645	1458	1323	1276	1098
45°	1434	1291	1067	915	864	1107
55°	1090	924	693	566	525	974
65°	736	563	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	1	17	28	35	38	10
95°	90	44	54	61	60	107
105°	424	465	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1177	1187	1191	1010
135°	1402	1424	1436	1450	1448	1083
145°	1626	1624	1648	1658	1651	1017
155°	1790	1778	1794	1803	1792	825
165°	1886	1878	1882	1892	1882	533
175°	1930	1920	1923	1932	1918	184
180°	1925	1925	1925	1925	1925	

TEST NUMBER: P928614

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2357.9	2357.9	2357.9	2357.9	2357.9
2.5°	2368.5	2357.9	2334.3	2355.8	2351.5
5°	2357.9	2347.2	2319.4	2338.6	2332.3
7.5°	2338.6	2325.9	2296.1	2304.4	2293.8
10°	2313.1	2298.1	2255.5	2249.0	2236.3
12.5°	2281.1	2261.9	2204.2	2191.5	2167.9
15°	2242.6	2219.1	2146.6	2106.1	2084.9
17.5°	2197.8	2163.7	2074.0	2027.1	1992.9
20°	2146.6	2103.8	1997.2	1944.0	1896.9
22.5°	2091.2	2042.1	1918.2	1845.7	1813.9
25°	2035.7	1967.3	1826.5	1739.1	1707.0
27.5°	1969.6	1896.9	1741.2	1640.9	1591.8
30°	1899.2	1817.9	1647.2	1538.6	1480.9
32.5°	1830.8	1732.6	1557.8	1429.7	1376.2
35°	1754.0	1645.2	1457.5	1323.1	1276.0
37.5°	1679.4	1561.9	1363.6	1216.1	1163.0
40°	1600.3	1472.5	1265.3	1113.9	1058.4
42.5°	1519.3	1382.8	1167.2	1009.2	956.1
45°	1434.0	1290.9	1067.0	915.3	864.1
47.5°	1352.9	1201.5	971.0	819.3	772.5
50°	1263.2	1111.8	877.0	729.7	685.1
52.5°	1175.6	1015.6	787.4	646.5	606.0
55°	1090.3	923.9	693.4	565.5	525.0
57.5°	1002.9	832.2	610.4	490.8	456.6
60°	913.3	742.5	522.7	414.1	379.9
62.5°	825.8	655.2	448.0	345.7	328.7
65°	736.2	563.2	371.3	298.9	292.3
67.5°	650.9	477.9	298.9	262.3	256.1
70°	561.2	394.8	247.4	226.2	217.5
72.5°	475.9	317.8	206.9	190.0	185.7
75°	392.6	243.1	170.7	155.7	153.7
77.5°	309.5	172.7	134.5	125.8	121.6
80°	232.5	123.8	102.4	94.0	94.0
82.5°	162.1	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.1	17.0	17.0	14.9	14.9
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	162.9	48.8	71.0	75.3	76.6
100°	246.7	55.7	79.4	90.5	93.3
102.5°	338.5	335.9	82.2	97.5	101.7
105°	423.6	465.4	85.0	100.2	105.9
107.5°	522.4	557.2	87.9	103.1	108.7
110°	617.3	646.4	243.8	104.6	110.0



TEST NUMBER: P928614

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.4	731.4	707.7	107.2	111.5
115°	801.1	824.7	859.6	214.6	114.3
117.5°	883.3	911.1	934.9	735.5	370.6
120°	975.2	996.1	1021.3	1038.0	849.9
122.5°	1053.1	1075.5	1103.5	1111.7	1113.2
125°	1132.6	1150.8	1177.3	1187.0	1191.1
127.5°	1205.1	1224.5	1245.6	1259.5	1260.8
130°	1273.4	1295.7	1310.9	1326.3	1325.0
132.5°	1343.0	1361.2	1376.5	1389.0	1387.7
135°	1401.6	1423.9	1436.4	1450.4	1447.6
137.5°	1462.8	1479.6	1493.6	1507.5	1503.3
140°	1522.7	1533.9	1549.2	1561.7	1554.8
142.5°	1572.9	1582.7	1600.7	1611.8	1604.9
145°	1625.9	1624.5	1648.1	1657.9	1650.9
147.5°	1671.7	1667.7	1691.3	1698.2	1692.8
150°	1716.4	1706.7	1729.0	1737.3	1730.3
152.5°	1754.0	1742.9	1763.7	1772.1	1762.4
155°	1790.2	1777.8	1794.5	1802.8	1791.7
157.5°	1819.5	1808.4	1821.0	1830.7	1819.5
160°	1844.7	1836.2	1844.7	1852.9	1843.1
162.5°	1866.8	1858.5	1865.5	1875.2	1862.7
165°	1886.3	1878.1	1882.2	1891.9	1882.2
167.5°	1901.7	1893.2	1897.6	1907.3	1894.8
170°	1914.3	1905.9	1908.6	1918.4	1905.9
172.5°	1922.6	1914.3	1917.1	1926.8	1914.3
175°	1929.5	1919.7	1922.6	1932.3	1918.4
177.5°	1932.3	1922.6	1924.1	1933.8	1921.2
180°	1925.4	1925.4	1925.4	1925.4	1925.4

TEST NUMBER: P928614

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.74	9.54	9.73	10.54	11.86	4.71	5.51	5.70	6.51	7.84
	3H	10.41	11.13	11.42	12.14	13.49	5.90	6.61	6.90	7.62	8.97
	4H	11.02	11.70	12.04	12.71	14.07	6.35	7.02	7.37	8.04	9.39
	6H	11.44	12.06	12.47	13.08	14.45	6.67	7.29	7.70	8.31	9.68
	8H	11.57	12.16	12.60	13.19	14.56	6.76	7.35	7.79	8.39	9.75
	12H	11.63	12.19	12.67	13.22	14.61	6.80	7.37	7.84	8.39	9.78
4H	2H	8.75	9.43	9.78	10.44	11.80	5.30	5.98	6.33	6.99	8.35
	3H	10.58	11.14	11.61	12.18	13.55	6.65	7.21	7.68	8.26	9.62
	4H	11.27	11.78	12.31	12.82	14.21	7.20	7.71	8.24	8.75	10.14
	6H	11.78	12.23	12.83	13.28	14.67	7.62	8.06	8.67	9.12	10.51
	8H	11.96	12.37	13.01	13.42	14.83	7.75	8.16	8.80	9.21	10.61
	12H	12.05	12.43	13.12	13.49	14.90	7.81	8.18	8.88	9.25	10.66
8H	4H	11.24	11.65	12.29	12.70	14.10	7.48	7.89	8.53	8.94	10.34
	6H	11.80	12.14	12.88	13.24	14.63	8.00	8.34	9.07	9.43	10.83
	8H	12.02	12.32	13.10	13.39	14.81	8.19	8.49	9.27	9.56	10.98
	12H	12.16	12.42	13.24	13.49	14.95	8.31	8.57	9.39	9.64	11.10
12H	4H	11.19	11.56	12.25	12.62	14.03	7.48	7.85	8.55	8.92	10.33
	6H	11.78	12.08	12.86	13.15	14.57	8.05	8.35	9.13	9.42	10.84
	8H	12.00	12.26	13.08	13.33	14.79	8.26	8.52	9.34	9.59	11.05