

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928616

Luminaire Tested: DFN2DIP-HX4F0-070D080US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928616
REPORT IS A COMBINATION OF REPORTS P900897 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D080US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12102.8 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928616

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928616

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47		
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45	39		
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38	33		
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28		
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24		
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	27	24	21		
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16		
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17	15		
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13		
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1651	1651	1651
5°	1653	1628	1639
10°	1640	1606	1617
15°	1616	1580	1582
20°	1584	1543	1547
25°	1551	1499	1506
30°	1511	1459	1454
35°	1473	1411	1398
40°	1425	1362	1346
45°	1378	1313	1292
50°	1327	1262	1230
55°	1273	1203	1173
60°	1212	1133	1108
65°	1146	1061	1031
70°	1061	972	948
75°	944	866	871
80°	803	732	725
85°	583	499	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1378 cd/sqm

TEST NUMBER: P928616

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.9	1.7
10°-20°	587.9	4.9
20°-30°	863.9	7.1
30°-40°	1003.4	8.3
40°-50°	1002.1	8.3
50°-60°	873.8	7.2
60°-70°	646.0	5.3
70°-80°	365.5	3.0
80°-90°	100.4	0.8
90°-100°	72.6	0.6
100°-110°	270.5	2.2
110°-120°	717.4	5.9
120°-130°	1189.8	9.8
130°-140°	1263.8	10.4
140°-150°	1174.6	9.7
150°-160°	944.4	7.8
160°-170°	608.5	5.0
170°-180°	209.4	1.7
0°-30°	1660.7	13.7
0°-40°	2664.1	22.0
0°-60°	4540.1	37.5
0°-90°	5651.9	46.7
90°-120°	1060.4	8.8
90°-150°	4688.7	38.7
90°-180°	6451.0	53.3
0°-180°	12102.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2220	2220	2220	2220	2220	
5°	2220	2212	2188	2205	2201	211
15°	2113	2100	2073	2081	2071	595
25°	1913	1896	1859	1863	1859	880
35°	1650	1629	1594	1582	1571	1030
45°	1343	1328	1296	1272	1264	1036
55°	1016	1003	978	952	941	908
65°	685	672	651	632	621	678
75°	358	354	344	331	335	383
85°	87	85	83	77	75	98
90°	2	19	32	40	43	11
95°	103	51	62	70	68	122
105°	484	532	97	115	121	517
115°	916	942	982	245	131	901
125°	1294	1315	1345	1357	1361	1154
135°	1602	1627	1642	1658	1654	1237
145°	1858	1856	1884	1895	1887	1162
155°	2046	2032	2051	2060	2048	943
165°	2156	2146	2151	2162	2151	609
175°	2205	2194	2197	2208	2192	210
180°	2200	2200	2200	2200	2200	

TEST NUMBER: P928616

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2219.8	2219.8	2219.8	2219.8	2219.8
2.5°	2232.8	2222.1	2198.5	2219.8	2215.7
5°	2219.8	2211.5	2187.9	2204.9	2200.8
7.5°	2204.9	2192.2	2168.6	2185.9	2181.6
10°	2181.6	2166.6	2141.0	2158.0	2151.7
12.5°	2149.4	2136.8	2111.2	2121.8	2117.5
15°	2113.2	2100.5	2072.6	2081.3	2070.6
17.5°	2068.3	2055.7	2027.8	2038.5	2027.8
20°	2019.2	2006.5	1976.6	1983.0	1974.6
22.5°	1970.3	1951.0	1923.2	1923.2	1918.8
25°	1912.6	1895.5	1859.3	1863.4	1859.3
27.5°	1848.4	1833.5	1805.9	1799.5	1788.8
30°	1784.6	1767.3	1735.5	1729.1	1720.5
32.5°	1716.1	1703.5	1669.3	1656.4	1647.8
35°	1650.0	1628.8	1594.5	1581.7	1571.0
37.5°	1575.3	1556.1	1521.8	1506.9	1496.3
40°	1498.5	1481.3	1447.1	1428.1	1419.5
42.5°	1423.8	1406.6	1372.6	1351.1	1338.4
45°	1342.7	1327.8	1295.6	1272.3	1263.7
47.5°	1263.7	1248.7	1214.5	1191.0	1178.3
50°	1180.4	1169.7	1139.8	1109.9	1099.3
52.5°	1099.3	1084.4	1056.7	1033.2	1018.2
55°	1016.1	1003.3	977.7	952.1	941.4
57.5°	932.8	922.2	894.3	868.7	860.2
60°	849.5	841.1	811.3	787.7	781.3
62.5°	768.4	753.5	732.2	710.9	702.3
65°	685.3	672.4	651.1	631.9	621.2
67.5°	599.9	589.1	570.0	555.1	546.5
70°	520.9	512.3	493.0	478.1	469.7
72.5°	439.8	431.2	420.5	405.6	399.3
75°	358.5	354.4	343.5	330.9	335.2
77.5°	286.1	277.4	273.1	266.7	260.5
80°	213.5	211.3	207.0	200.7	196.3
82.5°	145.2	145.2	143.1	134.6	134.6
85°	87.4	85.4	83.4	76.8	74.7
87.5°	38.5	34.2	29.9	23.6	21.3
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.4	50.9	62.0	70.2	68.5
97.5°	186.2	55.7	81.1	86.1	87.5
100°	281.9	63.7	90.8	103.4	106.6
102.5°	386.9	383.8	94.0	111.3	116.3
105°	484.0	531.9	97.1	114.6	121.0
107.5°	597.1	636.8	100.4	117.8	124.2
110°	705.5	738.7	278.7	119.5	125.8

TEST NUMBER: P928616

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.3	835.9	808.9	122.5	127.5
115°	915.5	942.5	982.4	245.2	130.6
117.5°	1009.5	1041.2	1068.5	840.6	423.6
120°	1114.6	1138.4	1167.2	1186.2	971.2
122.5°	1203.6	1229.2	1261.1	1270.6	1272.3
125°	1294.4	1315.2	1345.4	1356.6	1361.3
127.5°	1377.2	1399.5	1423.6	1439.4	1440.9
130°	1455.3	1480.8	1498.2	1515.8	1514.3
132.5°	1534.9	1555.7	1573.1	1587.5	1585.9
135°	1601.8	1627.3	1641.5	1657.6	1654.4
137.5°	1671.8	1690.9	1706.9	1722.8	1718.1
140°	1740.2	1753.1	1770.5	1784.8	1776.9
142.5°	1797.7	1808.8	1829.4	1842.1	1834.2
145°	1858.2	1856.5	1883.5	1894.7	1886.7
147.5°	1910.6	1905.9	1932.9	1940.8	1934.6
150°	1961.6	1950.5	1976.0	1985.4	1977.5
152.5°	2004.6	1991.9	2015.7	2025.4	2014.2
155°	2046.0	2031.8	2050.9	2060.3	2047.7
157.5°	2079.4	2066.8	2081.1	2092.3	2079.4
160°	2108.2	2098.5	2108.2	2117.6	2106.4
162.5°	2133.5	2124.1	2132.0	2143.1	2128.8
165°	2155.8	2146.4	2151.1	2162.2	2151.1
167.5°	2173.4	2163.7	2168.6	2179.8	2165.5
170°	2187.8	2178.1	2181.3	2192.5	2178.1
172.5°	2197.2	2187.8	2191.0	2202.1	2187.8
175°	2205.1	2194.0	2197.2	2208.3	2192.5
177.5°	2208.3	2197.2	2198.9	2210.0	2195.7
180°	2200.4	2200.4	2200.4	2200.4	2200.4

TEST NUMBER: P928616

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.70	9.53	9.69	10.53	11.85	8.27	9.10	9.25	10.10	11.42
	3H	10.36	11.11	11.36	12.11	13.45	9.89	10.63	10.88	11.64	12.98
	4H	10.95	11.65	11.96	12.66	14.01	10.47	11.18	11.48	12.19	13.54
	6H	11.35	12.00	12.37	13.01	14.37	10.87	11.52	11.89	12.54	13.89
	8H	11.45	12.07	12.48	13.10	14.46	10.97	11.59	12.00	12.63	13.98
	12H	11.50	12.09	12.53	13.11	14.49	11.02	11.61	12.05	12.63	14.01
4H	2H	9.16	9.87	10.17	10.88	12.22	8.81	9.52	9.83	10.53	11.88
	3H	11.02	11.61	12.05	12.65	14.01	10.63	11.22	11.65	12.26	13.62
	4H	11.74	12.28	12.77	13.31	14.69	11.33	11.87	12.36	12.90	14.29
	6H	12.25	12.72	13.29	13.77	15.15	11.84	12.31	12.88	13.36	14.74
	8H	12.40	12.84	13.44	13.88	15.28	11.99	12.42	13.03	13.47	14.86
	12H	12.47	12.87	13.53	13.93	15.33	12.05	12.44	13.11	13.51	14.91
8H	4H	11.93	12.37	12.98	13.41	14.81	11.57	12.01	12.61	13.05	14.45
	6H	12.56	12.92	13.63	14.01	15.40	12.20	12.56	13.27	13.65	15.04
	8H	12.79	13.10	13.86	14.17	15.58	12.42	12.73	13.49	13.80	15.22
	12H	12.92	13.19	13.99	14.26	15.71	12.53	12.81	13.61	13.88	15.33
12H	4H	11.92	12.31	12.98	13.37	14.77	11.56	11.96	12.63	13.02	14.42
	6H	12.59	12.91	13.67	13.98	15.39	12.24	12.56	13.32	13.63	15.04
	8H	12.84	13.11	13.91	14.18	15.63	12.48	12.76	13.56	13.82	15.28