

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916400

Luminaire Tested: DFN2DIP-HX4F0-080D050US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916400
REPORT IS A COMBINATION OF REPORTS P899325 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D050US930-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10064.9 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 105.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916400

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916400

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	111	111	111	111		104	104	104	104		91	91	91		80	80	80		69	69	69
1	101	97	93	89		95	91	87	84		80	77	75		70	68	66		61	60	58
2	92	84	78	73		86	79	74	69		70	66	62		62	58	56		54	51	49
3	84	74	67	61		79	70	63	58		62	57	52		55	50	47		48	45	42
4	77	66	58	51		72	62	55	49		55	49	45		49	44	40		43	39	36
5	71	59	50	44		66	55	48	42		49	43	39		44	39	35		38	35	32
6	65	53	44	38		61	50	42	37		45	38	34		40	35	31		35	31	28
7	60	48	40	34		56	45	38	32		40	34	30		36	31	27		32	28	25
8	56	43	35	30		53	41	34	29		37	31	27		33	28	24		29	25	22
9	52	40	32	27		49	38	31	26		34	28	24		30	26	22		27	23	20
10	49	37	29	24		46	35	28	23		31	26	22		28	23	20		25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1887	1887	1887
5°	1890	1861	1873
10°	1875	1836	1848
15°	1848	1806	1809
20°	1811	1764	1768
25°	1774	1714	1721
30°	1727	1668	1662
35°	1683	1613	1599
40°	1630	1557	1539
45°	1576	1502	1478
50°	1517	1443	1407
55°	1455	1376	1341
60°	1386	1296	1266
65°	1310	1213	1178
70°	1213	1112	1083
75°	1079	991	996
80°	918	837	829
85°	667	570	551

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1576 cd/sqm

TEST NUMBER: P916400

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.9	2.4
10°-20°	672.1	6.7
20°-30°	987.7	9.8
30°-40°	1147.1	11.4
40°-50°	1145.7	11.4
50°-60°	999.0	9.9
60°-70°	738.5	7.3
70°-80°	417.8	4.2
80°-90°	114.0	1.1
90°-100°	79.8	0.8
100°-110°	253.5	2.5
110°-120°	433.8	4.3
120°-130°	570.5	5.7
130°-140°	640.4	6.4
140°-150°	627.9	6.2
150°-160°	526.8	5.2
160°-170°	349.3	3.5
170°-180°	122.1	1.2
0°-30°	1898.6	18.9
0°-40°	3045.8	30.3
0°-60°	5190.5	51.6
0°-90°	6460.8	64.2
90°-120°	767.0	7.6
90°-150°	2605.8	25.9
90°-180°	3604.0	35.8
0°-180°	10064.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2538	2538	2538	2538	2538	
5°	2538	2528	2501	2521	2516	241
15°	2416	2402	2370	2379	2367	680
25°	2186	2167	2126	2130	2126	1006
35°	1886	1862	1823	1808	1796	1178
45°	1535	1518	1481	1455	1445	1185
55°	1162	1147	1118	1088	1076	1039
65°	784	769	744	722	710	775
75°	410	405	393	378	383	438
85°	100	98	95	88	85	112
90°	1	14	38	36	37	10
95°	57	68	70	70	68	63
105°	234	237	240	241	241	247
115°	435	442	440	438	435	431
125°	633	643	640	636	635	566
135°	819	831	833	832	829	633
145°	994	1002	1008	1009	1005	621
155°	1137	1140	1144	1149	1145	523
165°	1237	1236	1236	1243	1238	349
175°	1287	1284	1282	1289	1283	122
180°	1289	1289	1289	1289	1289	

TEST NUMBER: P916400

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2537.9	2537.9	2537.9	2537.9	2537.9
2.5°	2552.6	2540.5	2513.6	2537.9	2533.2
5°	2537.9	2528.3	2501.4	2520.8	2516.2
7.5°	2520.8	2506.3	2479.4	2499.1	2494.2
10°	2494.2	2477.0	2447.8	2467.2	2460.0
12.5°	2457.4	2442.9	2413.6	2425.8	2420.9
15°	2416.0	2401.5	2369.6	2379.4	2367.3
17.5°	2364.7	2350.2	2318.3	2330.5	2318.3
20°	2308.5	2294.0	2259.8	2267.1	2257.5
22.5°	2252.6	2230.6	2198.7	2198.7	2193.8
25°	2186.5	2167.1	2125.7	2130.4	2125.7
27.5°	2113.3	2096.2	2064.6	2057.3	2045.2
30°	2040.3	2020.6	1984.1	1976.9	1967.0
32.5°	1962.1	1947.6	1908.5	1893.7	1883.9
35°	1886.4	1862.1	1823.0	1808.2	1796.1
37.5°	1801.0	1779.0	1739.9	1722.8	1710.7
40°	1713.3	1693.5	1654.5	1632.7	1622.9
42.5°	1627.8	1608.1	1569.3	1544.7	1530.2
45°	1535.1	1518.0	1481.2	1454.6	1444.8
47.5°	1444.8	1427.7	1388.5	1361.6	1347.1
50°	1349.5	1337.3	1303.1	1268.9	1256.8
52.5°	1256.8	1239.7	1208.1	1181.2	1164.1
55°	1161.7	1147.0	1117.8	1088.5	1076.3
57.5°	1066.5	1054.3	1022.5	993.2	983.3
60°	971.2	961.6	927.4	900.5	893.2
62.5°	878.5	861.4	837.1	812.8	802.9
65°	783.5	768.7	744.4	722.4	710.2
67.5°	685.8	673.4	651.7	634.6	624.8
70°	595.5	585.6	563.7	546.6	537.0
72.5°	502.8	493.0	480.8	463.7	456.5
75°	409.9	405.2	392.8	378.3	383.2
77.5°	327.0	317.2	312.3	305.0	297.7
80°	244.2	241.6	236.7	229.4	224.5
82.5°	166.0	166.0	163.6	153.8	153.8
85°	100.0	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.2	26.9	24.4
90°	1.1	14.0	38.1	35.8	36.9
92.5°	24.1	32.6	33.8	35.0	35.0
95°	56.7	67.7	69.5	69.5	67.7
97.5°	94.4	104.5	108.8	108.8	108.8
100°	137.9	146.9	150.0	150.0	148.9
102.5°	183.8	190.5	194.7	195.9	194.7
105°	234.0	237.1	239.5	241.3	241.3
107.5°	283.7	288.4	288.4	289.2	283.7
110°	331.9	338.2	338.2	338.2	335.0

TEST NUMBER: P916400

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	390.6	389.5	386.4	384.0
115°	435.3	441.6	439.6	438.5	435.3
117.5°	486.2	494.8	489.3	486.2	483.1
120°	537.5	546.1	537.5	537.5	534.0
122.5°	584.2	595.1	589.6	586.5	584.2
125°	633.2	642.9	639.8	636.3	635.1
127.5°	680.9	693.0	688.8	684.0	680.9
130°	725.7	739.6	737.7	735.4	731.1
132.5°	775.8	786.7	787.5	782.0	778.9
135°	819.0	831.0	833.3	832.2	829.1
137.5°	867.2	876.9	878.8	878.0	873.3
140°	909.5	919.2	924.6	924.6	920.4
142.5°	953.0	962.8	965.9	967.0	962.8
145°	994.3	1002.0	1008.2	1009.4	1005.1
147.5°	1031.2	1040.9	1045.5	1047.5	1043.2
150°	1069.3	1075.9	1080.1	1083.6	1080.1
152.5°	1103.1	1109.7	1115.1	1119.4	1115.1
155°	1136.9	1140.0	1143.5	1148.9	1145.4
157.5°	1166.0	1168.3	1170.3	1178.1	1172.6
160°	1192.0	1194.4	1195.6	1202.2	1197.5
162.5°	1216.2	1216.2	1217.3	1224.7	1219.3
165°	1236.8	1235.6	1235.6	1243.4	1237.9
167.5°	1255.4	1251.9	1251.9	1259.7	1254.3
170°	1269.4	1266.3	1265.2	1272.9	1266.3
172.5°	1279.1	1276.0	1274.9	1282.6	1276.0
175°	1286.9	1283.8	1281.5	1289.2	1282.6
177.5°	1291.2	1288.1	1285.7	1292.3	1285.7
180°	1289.2	1289.2	1289.2	1289.2	1289.2

TEST NUMBER: P916400

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.69	11.70	11.52	12.55	13.60	10.26	11.27	11.09	12.11	13.17
	3H	12.37	13.27	13.20	14.13	15.21	11.89	12.80	12.73	13.65	14.73
	4H	12.96	13.81	13.81	14.68	15.77	12.49	13.34	13.34	14.20	15.29
	6H	13.37	14.16	14.23	15.03	16.13	12.89	13.68	13.76	14.55	15.66
	8H	13.48	14.23	14.35	15.12	16.22	13.00	13.75	13.88	14.64	15.75
	12H	13.53	14.25	14.41	15.13	16.26	13.05	13.76	13.93	14.65	15.78
4H	2H	11.17	12.03	12.03	12.89	13.98	10.83	11.68	11.69	12.55	13.64
	3H	13.05	13.77	13.92	14.66	15.77	12.66	13.37	13.53	14.27	15.38
	4H	13.77	14.42	14.66	15.32	16.45	13.37	14.02	14.25	14.91	16.04
	6H	14.30	14.86	15.20	15.78	16.91	13.89	14.45	14.79	15.37	16.50
	8H	14.45	14.98	15.35	15.89	17.04	14.04	14.56	14.94	15.48	16.62
	12H	14.53	15.01	15.45	15.94	17.09	14.11	14.58	15.03	15.51	16.67
8H	4H	13.98	14.51	14.88	15.42	16.57	13.62	14.15	14.52	15.06	16.21
	6H	14.62	15.06	15.55	16.01	17.16	14.26	14.69	15.19	15.65	16.79
	8H	14.84	15.23	15.78	16.17	17.34	14.48	14.86	15.41	15.81	16.97
	12H	14.98	15.32	15.92	16.26	17.48	14.60	14.94	15.54	15.88	17.09
12H	4H	13.98	14.45	14.90	15.38	16.53	13.62	14.10	14.54	15.03	16.18
	6H	14.65	15.04	15.59	15.98	17.15	14.30	14.69	15.24	15.63	16.80
	8H	14.90	15.24	15.84	16.18	17.40	14.55	14.88	15.49	15.82	17.04