

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911045

Luminaire Tested: DFN2DIP-PN2F0-020D050US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911045
REPORT IS A COMBINATION OF REPORTS P901011 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D050US850-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7685.4 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911045

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911045

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1869	1869	1869
5°	1869	1839	1853
10°	1851	1810	1825
15°	1821	1777	1783
20°	1781	1731	1740
25°	1742	1678	1691
30°	1692	1628	1629
35°	1646	1569	1564
40°	1589	1510	1502
45°	1532	1451	1439
50°	1470	1388	1365
55°	1404	1316	1297
60°	1330	1231	1219
65°	1248	1142	1127
70°	1145	1033	1027
75°	1003	903	931
80°	830	738	755
85°	562	467	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1719 cd/sqm

TEST NUMBER: P911045

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.1
10°-20°	228.6	3.0
20°-30°	335.9	4.4
30°-40°	390.1	5.1
40°-50°	389.6	5.1
50°-60°	339.7	4.4
60°-70°	251.1	3.3
70°-80°	142.1	1.8
80°-90°	40.8	0.5
90°-100°	61.7	0.8
100°-110°	230.0	3.0
110°-120°	610.1	7.9
120°-130°	1011.9	13.2
130°-140°	1074.8	14.0
140°-150°	999.0	13.0
150°-160°	803.1	10.5
160°-170°	517.5	6.7
170°-180°	178.1	2.3
0°-30°	645.7	8.4
0°-40°	1035.8	13.5
0°-60°	1765.1	23.0
0°-90°	2199.1	28.6
90°-120°	901.9	11.7
90°-150°	3987.5	51.9
90°-180°	5486.0	71.4
0°-180°	7685.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	1	16	27	34	36	7
95°	88	43	53	60	58	104
105°	412	452	83	98	103	440
115°	779	802	836	209	111	767
125°	1101	1118	1144	1154	1158	982
135°	1362	1384	1396	1410	1407	1052
145°	1580	1579	1602	1611	1605	988
155°	1740	1728	1744	1752	1742	802
165°	1833	1825	1829	1839	1829	518
175°	1875	1866	1869	1878	1865	178
180°	1871	1871	1871	1871	1871	

TEST NUMBER: P911045

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.3	16.2	27.1	33.9	36.5
92.5°	33.9	28.5	32.5	35.3	36.5
95°	87.9	43.3	52.8	59.7	58.2
97.5°	158.4	47.5	69.0	73.2	74.4
100°	239.8	54.2	77.2	87.9	90.7
102.5°	329.0	326.4	80.0	94.7	98.9
105°	411.7	452.4	82.6	97.5	102.9
107.5°	507.8	541.5	85.4	100.1	105.7
110°	600.0	628.2	237.0	101.6	106.9

TEST NUMBER: P911045

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	686.6	710.9	687.9	104.2	108.3
115°	778.6	801.6	835.5	208.6	111.1
117.5°	858.5	885.5	908.7	714.9	360.2
120°	947.9	968.2	992.6	1008.9	826.0
122.5°	1023.6	1045.3	1072.5	1080.6	1082.1
125°	1100.8	1118.5	1144.3	1153.7	1157.8
127.5°	1171.2	1190.2	1210.7	1224.1	1225.4
130°	1237.6	1259.4	1274.1	1289.1	1287.9
132.5°	1305.4	1323.0	1337.8	1350.1	1348.8
135°	1362.3	1384.0	1396.0	1409.8	1407.0
137.5°	1421.7	1438.0	1451.7	1465.2	1461.2
140°	1480.0	1490.9	1505.7	1517.9	1511.2
142.5°	1528.9	1538.4	1555.9	1566.7	1559.9
145°	1580.3	1578.9	1601.8	1611.4	1604.6
147.5°	1624.9	1620.8	1643.9	1650.6	1645.3
150°	1668.3	1658.8	1680.5	1688.6	1681.8
152.5°	1704.8	1694.0	1714.3	1722.5	1713.0
155°	1740.0	1727.9	1744.1	1752.2	1741.5
157.5°	1768.4	1757.7	1769.9	1779.4	1768.4
160°	1792.9	1784.7	1792.9	1800.9	1791.5
162.5°	1814.4	1806.5	1813.1	1822.6	1810.4
165°	1833.4	1825.4	1829.4	1838.8	1829.4
167.5°	1848.4	1840.2	1844.4	1853.8	1841.6
170°	1860.6	1852.4	1855.1	1864.6	1852.4
172.5°	1868.7	1860.6	1863.3	1872.8	1860.6
175°	1875.4	1865.9	1868.7	1878.1	1864.6
177.5°	1878.1	1868.7	1870.1	1879.5	1867.3
180°	1871.3	1871.3	1871.3	1871.3	1871.3

TEST NUMBER: P911045

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.92	7.62	8.04	8.73	10.28	6.49	7.18	7.61	8.30	9.84
	3H	8.55	9.17	9.68	10.30	11.86	8.07	8.69	9.20	9.82	11.38
	4H	9.12	9.71	10.25	10.83	12.40	8.63	9.23	9.77	10.35	11.92
	6H	9.49	10.04	10.64	11.16	12.74	9.01	9.55	10.15	10.68	12.26
	8H	9.58	10.10	10.73	11.24	12.82	9.10	9.62	10.25	10.76	12.33
	12H	9.62	10.11	10.77	11.25	12.84	9.13	9.62	10.28	10.75	12.35
4H	2H	7.35	7.95	8.50	9.07	10.64	7.00	7.60	8.15	8.72	10.29
	3H	9.18	9.67	10.33	10.82	12.40	8.78	9.28	9.93	10.43	12.01
	4H	9.87	10.33	11.03	11.46	13.06	9.46	9.91	10.61	11.05	12.65
	6H	10.36	10.75	11.52	11.91	13.50	9.94	10.33	11.10	11.49	13.08
	8H	10.49	10.86	11.65	12.01	13.62	10.07	10.43	11.23	11.59	13.19
	12H	10.55	10.88	11.73	12.04	13.66	10.12	10.45	11.29	11.61	13.22
8H	4H	10.04	10.41	11.20	11.56	13.17	9.67	10.04	10.83	11.19	12.80
	6H	10.64	10.94	11.82	12.14	13.74	10.27	10.57	11.45	11.77	13.37
	8H	10.85	11.11	12.03	12.28	13.91	10.47	10.73	11.65	11.90	13.53
	12H	10.96	11.19	12.15	12.36	14.02	10.56	10.79	11.75	11.96	13.62
12H	4H	10.02	10.35	11.19	11.51	13.12	9.66	9.99	10.83	11.15	12.76
	6H	10.67	10.93	11.85	12.10	13.73	10.30	10.57	11.49	11.74	13.36
	8H	10.89	11.12	12.07	12.29	13.94	10.52	10.75	11.71	11.92	13.57

END OF REPORT