

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911049

Luminaire Tested: DFN2DIP-PN2F0-020D060US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911049
REPORT IS A COMBINATION OF REPORTS P901021 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D060US850-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8783.3 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911049

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911049

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1869	1869	1869
5°	1869	1839	1853
10°	1851	1810	1825
15°	1821	1777	1783
20°	1781	1731	1740
25°	1742	1678	1691
30°	1692	1628	1629
35°	1646	1569	1564
40°	1589	1510	1502
45°	1532	1451	1439
50°	1470	1388	1365
55°	1404	1316	1297
60°	1330	1231	1219
65°	1248	1142	1127
70°	1145	1033	1027
75°	1003	903	931
80°	830	738	755
85°	562	467	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2063 cd/sqm

TEST NUMBER: P911049

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	0.9
10°-20°	228.6	2.6
20°-30°	335.9	3.8
30°-40°	390.1	4.4
40°-50°	389.6	4.4
50°-60°	339.7	3.9
60°-70°	251.1	2.9
70°-80°	142.1	1.6
80°-90°	41.5	0.5
90°-100°	74.1	0.8
100°-110°	276.0	3.1
110°-120°	732.1	8.3
120°-130°	1214.2	13.8
130°-140°	1289.8	14.7
140°-150°	1198.7	13.6
150°-160°	963.8	11.0
160°-170°	621.0	7.1
170°-180°	213.7	2.4
0°-30°	645.7	7.4
0°-40°	1035.8	11.8
0°-60°	1765.1	20.1
0°-90°	2199.8	25.0
90°-120°	1082.2	12.3
90°-150°	4785.0	54.5
90°-180°	6583.0	74.9
0°-180°	8783.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	2	20	32	41	44	8
95°	106	52	63	72	70	125
105°	494	543	99	117	124	528
115°	934	962	1003	250	133	920
125°	1321	1342	1373	1384	1389	1178
135°	1635	1661	1675	1692	1688	1263
145°	1896	1895	1922	1934	1926	1186
155°	2088	2074	2093	2103	2090	962
165°	2200	2190	2195	2207	2195	622
175°	2250	2239	2242	2254	2238	214
180°	2246	2246	2246	2246	2246	

TEST NUMBER: P911049

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.6	19.5	32.4	40.7	43.8
92.5°	40.7	34.2	38.9	42.3	43.8
95°	105.6	51.9	63.3	71.6	69.9
97.5°	190.1	56.9	82.7	87.8	89.4
100°	287.7	65.0	92.6	105.6	108.8
102.5°	394.8	391.7	95.9	113.7	118.7
105°	493.9	542.7	99.1	116.9	123.5
107.5°	609.4	649.9	102.5	120.2	126.8
110°	720.0	753.9	284.5	122.0	128.3

TEST NUMBER: P911049

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	823.9	853.0	825.4	125.0	130.1
115°	934.3	961.9	1002.6	250.3	133.3
117.5°	1030.2	1062.6	1090.4	857.9	432.2
120°	1137.5	1161.8	1191.2	1210.6	991.2
122.5°	1228.3	1254.4	1287.0	1296.6	1298.4
125°	1321.0	1342.2	1373.1	1384.5	1389.2
127.5°	1405.5	1428.3	1452.8	1469.0	1470.5
130°	1485.2	1511.2	1529.0	1546.9	1545.4
132.5°	1566.5	1587.6	1605.4	1620.0	1618.5
135°	1634.8	1660.8	1675.3	1691.7	1688.3
137.5°	1706.1	1725.6	1742.0	1758.2	1753.4
140°	1776.0	1789.1	1806.9	1821.5	1813.4
142.5°	1834.6	1846.0	1867.1	1880.0	1871.9
145°	1896.4	1894.6	1922.2	1933.7	1925.6
147.5°	1949.8	1945.0	1972.6	1980.7	1974.4
150°	2002.0	1990.5	2016.6	2026.3	2018.2
152.5°	2045.8	2032.8	2057.1	2067.0	2055.5
155°	2088.0	2073.5	2093.0	2102.7	2089.7
157.5°	2122.2	2109.2	2123.8	2135.3	2122.2
160°	2151.5	2141.6	2151.5	2161.1	2149.8
162.5°	2177.3	2167.7	2175.7	2187.2	2172.5
165°	2200.1	2190.5	2195.3	2206.7	2195.3
167.5°	2218.0	2208.2	2213.2	2224.7	2209.9
170°	2232.7	2222.9	2226.2	2237.5	2222.9
172.5°	2242.4	2232.7	2236.0	2247.4	2232.7
175°	2250.5	2239.1	2242.4	2253.7	2237.5
177.5°	2253.7	2242.4	2244.1	2255.5	2240.8
180°	2245.6	2245.6	2245.6	2245.6	2245.6

TEST NUMBER: P911049

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.39	7.06	7.53	8.19	9.78	5.95	6.62	7.10	7.76	9.35
	3H	8.01	8.62	9.16	9.76	11.36	7.53	8.14	8.69	9.28	10.88
	4H	8.58	9.15	9.74	10.29	11.90	8.10	8.67	9.26	9.81	11.42
	6H	8.95	9.48	10.12	10.62	12.24	8.47	8.99	9.64	10.14	11.76
	8H	9.04	9.55	10.22	10.71	12.32	8.56	9.06	9.73	10.22	11.83
	12H	9.08	9.55	10.25	10.71	12.34	8.59	9.06	9.76	10.22	11.85
4H	2H	6.81	7.39	7.98	8.53	10.14	6.47	7.04	7.64	8.18	9.79
	3H	8.64	9.12	9.81	10.29	11.91	8.24	8.72	9.41	9.89	11.51
	4H	9.33	9.77	10.51	10.93	12.57	8.92	9.36	10.09	10.51	12.15
	6H	9.81	10.19	11.00	11.37	13.00	9.40	9.77	10.58	10.95	12.58
	8H	9.95	10.30	11.13	11.47	13.12	9.53	9.88	10.71	11.05	12.69
	12H	10.00	10.32	11.20	11.51	13.16	9.57	9.89	10.77	11.07	12.72
8H	4H	9.50	9.85	10.68	11.02	12.67	9.13	9.48	10.31	10.65	12.30
	6H	10.10	10.39	11.30	11.60	13.24	9.73	10.02	10.92	11.23	12.87
	8H	10.30	10.56	11.51	11.75	13.41	9.92	10.18	11.13	11.37	13.03
	12H	10.41	10.64	11.62	11.82	13.52	10.02	10.24	11.23	11.43	13.12
12H	4H	9.47	9.79	10.67	10.97	12.63	9.11	9.43	10.31	10.61	12.26
	6H	10.12	10.38	11.33	11.57	13.23	9.76	10.01	10.96	11.20	12.87
	8H	10.34	10.56	11.55	11.75	13.44	9.97	10.19	11.18	11.38	13.07

END OF REPORT