

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911056

Luminaire Tested: DFN2DIP-PN2F0-030D030US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911056
REPORT IS A COMBINATION OF REPORTS P899473 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D030US850-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6238.1 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911056

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911056

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US850-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2804	2804	2804
5°	2804	2759	2779
10°	2777	2716	2737
15°	2731	2665	2675
20°	2671	2597	2610
25°	2612	2517	2537
30°	2539	2442	2444
35°	2469	2354	2347
40°	2383	2265	2254
45°	2298	2176	2158
50°	2205	2082	2048
55°	2106	1974	1946
60°	1995	1846	1828
65°	1873	1713	1690
70°	1717	1551	1540
75°	1503	1356	1396
80°	1244	1107	1134
85°	845	700	710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2298 cd/sqm

TEST NUMBER: P911056

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	2.0
10°-20°	342.8	5.5
20°-30°	503.8	8.1
30°-40°	585.2	9.4
40°-50°	584.4	9.4
50°-60°	509.6	8.2
60°-70°	376.7	6.0
70°-80°	213.1	3.4
80°-90°	59.2	0.9
90°-100°	65.1	1.0
100°-110°	206.9	3.3
110°-120°	354.0	5.7
120°-130°	465.6	7.5
130°-140°	522.6	8.4
140°-150°	512.5	8.2
150°-160°	429.9	6.9
160°-170°	285.1	4.6
170°-180°	99.7	1.6
0°-30°	968.5	15.5
0°-40°	1553.6	24.9
0°-60°	2647.7	42.4
0°-90°	3296.7	52.8
90°-120°	626.0	10.0
90°-150°	2126.7	34.1
90°-180°	2941.0	47.1
0°-180°	6238.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	57
90°	1	11	31	29	30	6
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	

TEST NUMBER: P911056

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5

TEST NUMBER: P911056

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2

TEST NUMBER: P911056

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.00	11.88	11.93	12.83	14.06	10.56	11.45	11.49	12.40	13.63
	3H	12.64	13.43	13.58	14.39	15.65	12.16	12.95	13.10	13.91	15.17
	4H	13.21	13.97	14.17	14.93	16.19	12.73	13.48	13.69	14.45	15.71
	6H	13.60	14.29	14.57	15.26	16.54	13.11	13.81	14.08	14.78	16.05
	8H	13.70	14.36	14.67	15.34	16.62	13.21	13.87	14.19	14.86	16.13
	12H	13.74	14.37	14.72	15.35	16.64	13.25	13.87	14.23	14.85	16.15
4H	2H	11.45	12.20	12.41	13.17	14.43	11.10	11.85	12.06	12.82	14.08
	3H	13.29	13.92	14.27	14.92	16.19	12.89	13.52	13.87	14.52	15.79
	4H	13.99	14.57	14.98	15.56	16.86	13.58	14.15	14.56	15.14	16.44
	6H	14.49	14.99	15.49	16.00	17.30	14.07	14.57	15.07	15.58	16.88
	8H	14.63	15.09	15.63	16.10	17.41	14.21	14.67	15.20	15.67	16.99
	12H	14.70	15.11	15.71	16.13	17.45	14.26	14.68	15.28	15.70	17.02
8H	4H	14.18	14.64	15.18	15.65	16.96	13.81	14.28	14.81	15.28	16.59
	6H	14.79	15.17	15.81	16.22	17.53	14.42	14.80	15.44	15.84	17.16
	8H	15.00	15.33	16.03	16.37	17.70	14.62	14.95	15.65	15.99	17.32
	12H	15.12	15.41	16.15	16.44	17.81	14.72	15.02	15.75	16.04	17.42
12H	4H	14.17	14.58	15.18	15.60	16.92	13.81	14.22	14.82	15.24	16.56
	6H	14.81	15.15	15.84	16.18	17.51	14.45	14.79	15.48	15.82	17.15
	8H	15.04	15.34	16.08	16.37	17.74	14.67	14.97	15.71	16.00	17.37