

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928672

Luminaire Tested: DFN2DIP-HX4F0-090D040US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928672
REPORT IS A COMBINATION OF REPORTS P900829 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D040US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10489.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 118.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928672

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928672

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	94	90	96	92	89	86	83	80	77	74	72	70	65	64	62
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	53
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2122	2122	2122
5°	2126	2093	2107
10°	2109	2065	2078
15°	2078	2031	2034
20°	2036	1984	1988
25°	1995	1928	1936
30°	1943	1875	1869
35°	1893	1814	1798
40°	1833	1751	1731
45°	1772	1689	1662
50°	1706	1623	1582
55°	1637	1547	1508
60°	1558	1457	1424
65°	1473	1364	1325
70°	1364	1250	1218
75°	1214	1114	1120
80°	1033	941	932
85°	749	641	620

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1772 cd/sqm

TEST NUMBER: P928672

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	2.6
10°-20°	755.8	7.2
20°-30°	1110.7	10.6
30°-40°	1290.1	12.3
40°-50°	1288.5	12.3
50°-60°	1123.5	10.7
60°-70°	830.5	7.9
70°-80°	469.9	4.5
80°-90°	125.9	1.2
90°-100°	36.3	0.3
100°-110°	135.2	1.3
110°-120°	358.7	3.4
120°-130°	594.9	5.7
130°-140°	631.9	6.0
140°-150°	587.3	5.6
150°-160°	472.2	4.5
160°-170°	304.3	2.9
170°-180°	104.7	1.0
0°-30°	2135.2	20.4
0°-40°	3425.3	32.7
0°-60°	5837.3	55.7
0°-90°	7263.6	69.2
90°-120°	530.2	5.1
90°-150°	2344.3	22.4
90°-180°	3225.0	30.7
0°-180°	10489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2854	2854	2854	2854	2854	
5°	2854	2843	2813	2835	2830	271
15°	2717	2701	2665	2676	2662	765
25°	2459	2437	2391	2396	2391	1131
35°	2122	2094	2050	2034	2020	1325
45°	1726	1707	1666	1636	1625	1332
55°	1306	1290	1257	1224	1210	1168
65°	881	864	837	812	799	871
75°	461	456	442	425	431	492
85°	112	110	107	99	96	125
90°	1	10	16	20	21	10
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	678	681	577
135°	801	814	821	829	827	619
145°	929	928	942	947	943	581
155°	1023	1016	1025	1030	1024	471
165°	1078	1073	1076	1081	1076	305
175°	1102	1097	1099	1104	1096	105
180°	1100	1100	1100	1100	1100	



TEST NUMBER: P928672

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2854.0	2854.0	2854.0	2854.0	2854.0
2.5°	2870.7	2857.0	2826.7	2854.0	2848.8
5°	2854.0	2843.3	2813.1	2834.9	2829.6
7.5°	2834.9	2818.6	2788.3	2810.4	2804.9
10°	2804.9	2785.7	2752.7	2774.6	2766.4
12.5°	2763.5	2747.2	2714.4	2728.0	2722.5
15°	2717.0	2700.7	2664.8	2675.9	2662.2
17.5°	2659.3	2643.0	2607.2	2620.9	2607.2
20°	2596.1	2579.8	2541.3	2549.5	2538.7
22.5°	2533.2	2508.5	2472.6	2472.6	2467.1
25°	2458.9	2437.1	2390.6	2395.8	2390.6
27.5°	2376.5	2357.3	2321.9	2313.7	2300.0
30°	2294.5	2272.3	2231.2	2223.1	2212.1
32.5°	2206.5	2190.2	2146.2	2129.7	2118.6
35°	2121.5	2094.1	2050.1	2033.6	2019.9
37.5°	2025.4	2000.7	1956.7	1937.5	1923.8
40°	1926.7	1904.6	1860.6	1836.1	1825.1
42.5°	1830.6	1808.5	1764.8	1737.2	1720.9
45°	1726.3	1707.2	1665.8	1635.8	1624.8
47.5°	1624.8	1605.6	1561.5	1531.3	1515.0
50°	1517.6	1503.9	1465.5	1427.1	1413.4
52.5°	1413.4	1394.1	1358.6	1328.4	1309.1
55°	1306.5	1289.9	1257.0	1224.1	1210.4
57.5°	1199.4	1185.7	1149.9	1117.0	1105.9
60°	1092.2	1081.4	1043.0	1012.7	1004.6
62.5°	987.9	968.7	941.3	914.0	902.9
65°	881.1	864.5	837.1	812.4	798.7
67.5°	771.3	757.4	732.8	713.7	702.6
70°	669.7	658.6	633.9	614.7	603.9
72.5°	565.4	554.4	540.7	521.5	513.4
75°	461.0	455.7	441.7	425.4	431.0
77.5°	367.7	356.7	351.2	343.0	334.9
80°	274.6	271.6	266.1	257.9	252.5
82.5°	186.6	186.6	184.0	172.9	172.9
85°	112.4	109.8	107.2	98.7	96.1
87.5°	49.5	43.9	38.5	30.3	27.4
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.0	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	140.9	31.9	45.4	51.7	53.3
102.5°	193.4	191.9	46.9	55.7	58.1
105°	242.0	265.9	48.6	57.3	60.5
107.5°	298.5	318.4	50.2	58.9	62.1
110°	352.7	369.4	139.4	59.7	62.8

TEST NUMBER: P928672

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.7	417.9	404.4	61.3	63.7
115°	457.7	471.2	491.2	122.6	65.4
117.5°	504.7	520.6	534.2	420.3	211.7
120°	557.3	569.2	583.5	593.2	485.7
122.5°	601.8	614.6	630.6	635.3	636.1
125°	647.2	657.6	672.7	678.3	680.7
127.5°	688.6	699.8	711.7	719.7	720.5
130°	727.6	740.4	749.1	757.9	757.1
132.5°	767.4	777.8	786.6	793.7	793.0
135°	800.9	813.7	820.8	828.8	827.2
137.5°	835.9	845.4	853.5	861.4	859.0
140°	870.1	876.5	885.3	892.4	888.4
142.5°	898.9	904.4	914.8	921.0	917.1
145°	929.1	928.3	941.7	947.4	943.4
147.5°	955.3	952.9	966.4	970.4	967.3
150°	980.8	975.2	988.0	992.8	988.8
152.5°	1002.3	995.9	1007.8	1012.6	1007.1
155°	1023.0	1015.9	1025.4	1030.2	1023.8
157.5°	1039.7	1033.3	1040.6	1046.1	1039.7
160°	1054.0	1049.2	1054.0	1058.8	1053.2
162.5°	1066.8	1062.0	1066.0	1071.6	1064.4
165°	1077.9	1073.2	1075.6	1081.1	1075.6
167.5°	1086.7	1081.8	1084.4	1089.9	1082.7
170°	1093.9	1089.1	1090.6	1096.3	1089.1
172.5°	1098.6	1093.9	1095.5	1101.1	1093.9
175°	1102.5	1097.0	1098.6	1104.2	1096.3
177.5°	1104.2	1098.6	1099.4	1105.1	1097.9
180°	1100.2	1100.2	1100.2	1100.2	1100.2

TEST NUMBER: P928672

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.50	12.56	12.27	13.36	14.33	11.07	12.13	11.84	12.93	13.89
	3H	13.18	14.13	13.96	14.94	15.93	12.70	13.66	13.49	14.46	15.46
	4H	13.77	14.68	14.58	15.49	16.50	13.30	14.20	14.10	15.02	16.02
	6H	14.18	15.02	15.00	15.84	16.86	13.71	14.54	14.52	15.36	16.39
	8H	14.29	15.09	15.12	15.93	16.95	13.82	14.61	14.64	15.45	16.48
	12H	14.35	15.11	15.18	15.94	16.99	13.87	14.63	14.70	15.46	16.51
4H	2H	11.99	12.89	12.79	13.70	14.71	11.64	12.54	12.45	13.36	14.37
	3H	13.87	14.63	14.69	15.47	16.50	13.48	14.23	14.30	15.08	16.10
	4H	14.59	15.28	15.43	16.13	17.18	14.19	14.88	15.02	15.72	16.77
	6H	15.12	15.72	15.97	16.59	17.64	14.71	15.31	15.56	16.18	17.23
	8H	15.28	15.83	16.13	16.70	17.77	14.86	15.42	15.72	16.28	17.35
	12H	15.36	15.86	16.23	16.75	17.82	14.94	15.44	15.81	16.32	17.40
8H	4H	14.81	15.36	15.66	16.23	17.30	14.45	15.00	15.30	15.87	16.94
	6H	15.45	15.91	16.33	16.82	17.89	15.09	15.55	15.97	16.45	17.52
	8H	15.67	16.08	16.56	16.98	18.07	15.30	15.71	16.19	16.61	17.70
	12H	15.81	16.17	16.71	17.07	18.21	15.43	15.79	16.32	16.68	17.82
12H	4H	14.80	15.30	15.68	16.19	17.26	14.45	14.95	15.32	15.84	16.91
	6H	15.48	15.89	16.37	16.79	17.88	15.13	15.54	16.02	16.44	17.53
	8H	15.73	16.09	16.63	16.99	18.13	15.38	15.74	16.27	16.63	17.77