

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911066

Luminaire Tested: DFN2DIP-PN2F0-030D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911066
REPORT IS A COMBINATION OF REPORTS P899494 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D050US850-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7735.3 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911066

CATALOG NUMBER: DFN2DIP-PN2F0-030D050US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911066

CATALOG NUMBER: DFN2DIP-PN2F0-030D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	38	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	16	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2978	2978	2978
5°	2978	2925	2945
10°	2944	2861	2845
15°	2898	2760	2693
20°	2840	2624	2508
25°	2780	2472	2329
30°	2702	2317	2104
35°	2624	2152	1906
40°	2545	1981	1680
45°	2454	1792	1476
50°	2359	1602	1276
55°	2260	1400	1085
60°	2144	1190	889
65°	2011	977	795
70°	1850	778	713
75°	1647	674	640
80°	1355	548	542
85°	886	340	384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2454 cd/sqm

TEST NUMBER: P911066

CATALOG NUMBER: DFN2DIP-PN2F0-030D050US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	1.7
10°-20°	353.8	4.6
20°-30°	496.7	6.4
30°-40°	541.4	7.0
40°-50°	497.6	6.4
50°-60°	390.8	5.1
60°-70°	254.4	3.3
70°-80°	130.9	1.7
80°-90°	38.4	0.5
90°-100°	108.5	1.4
100°-110°	344.8	4.5
110°-120°	590.1	7.6
120°-130°	776.0	10.0
130°-140°	871.0	11.3
140°-150°	854.2	11.0
150°-160°	716.5	9.3
160°-170°	475.2	6.1
170°-180°	166.1	2.1
0°-30°	979.3	12.7
0°-40°	1520.7	19.7
0°-60°	2409.2	31.1
0°-90°	2832.9	36.6
90°-120°	1043.4	13.5
90°-150°	3544.6	45.8
90°-180°	4902.0	63.4
0°-180°	7735.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	2	19	52	49	50	8
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	

TEST NUMBER: P911066

CATALOG NUMBER: DFN2DIP-PN2F0-030D050US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7

TEST NUMBER: P911066

CATALOG NUMBER: DFN2DIP-PN2F0-030D050US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7

TEST NUMBER: P911066

CATALOG NUMBER: DFN2DIP-PN2F0-030D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.43	10.16	10.50	11.23	12.68	5.39	6.13	6.46	7.19	8.65
	3H	11.08	11.73	12.15	12.81	14.28	6.56	7.21	7.64	8.29	9.76
	4H	11.67	12.29	12.76	13.36	14.84	6.99	7.61	8.08	8.69	10.17
	6H	12.07	12.64	13.16	13.72	15.21	7.29	7.86	8.39	8.94	10.43
	8H	12.18	12.72	13.28	13.82	15.30	7.37	7.91	8.47	9.01	10.49
	12H	12.23	12.75	13.34	13.84	15.34	7.40	7.92	8.51	9.01	10.52
4H	2H	9.43	10.05	10.52	11.13	12.60	5.97	6.59	7.06	7.66	9.14
	3H	11.22	11.74	12.33	12.84	14.33	7.29	7.80	8.39	8.91	10.40
	4H	11.90	12.37	13.00	13.46	14.98	7.82	8.29	8.92	9.38	10.89
	6H	12.39	12.79	13.50	13.91	15.41	8.21	8.62	9.33	9.74	11.24
	8H	12.55	12.93	13.66	14.04	15.56	8.33	8.71	9.44	9.82	11.34
	12H	12.63	12.97	13.76	14.09	15.62	8.38	8.72	9.51	9.85	11.37
8H	4H	11.85	12.23	12.97	13.34	14.86	8.08	8.46	9.19	9.57	11.08
	6H	12.39	12.70	13.53	13.86	15.37	8.57	8.88	9.71	10.03	11.55
	8H	12.60	12.87	13.74	14.00	15.54	8.75	9.02	9.89	10.15	11.69
	12H	12.72	12.96	13.86	14.08	15.66	8.85	9.09	9.99	10.22	11.79
12H	4H	11.80	12.14	12.93	13.26	14.79	8.07	8.42	9.21	9.54	11.06
	6H	12.37	12.64	13.51	13.77	15.31	8.61	8.89	9.75	10.02	11.55
	8H	12.57	12.81	13.71	13.94	15.51	8.80	9.04	9.95	10.17	11.74