

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928674

Luminaire Tested: DFN2DIP-HX4F0-090D040US930-RLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928674
REPORT IS A COMBINATION OF REPORTS P900830 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D040US930-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9462.1 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 118.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928674
CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928674

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			
1	102	98	94	91	96	92	89	86	82	79	77	72	71	69	64	62	61	57			
2	93	86	80	75	88	81	76	72	73	68	65	64	61	59	57	54	52	49			
3	86	76	69	63	80	72	66	61	65	60	55	57	54	50	51	48	45	42			
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40	37			
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32			
6	67	55	47	41	63	52	45	40	47	41	37	43	38	34	38	34	31	29			
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28	26			
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25	23			
9	54	42	35	29	51	40	33	29	37	31	27	33	28	25	30	26	23	21			
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2254	2254	2254
5°	2258	2219	2233
10°	2236	2175	2160
15°	2205	2104	2048
20°	2165	2005	1910
25°	2123	1894	1777
30°	2067	1780	1608
35°	2013	1658	1460
40°	1957	1531	1290
45°	1892	1391	1136
50°	1826	1249	986
55°	1756	1097	841
60°	1675	939	692
65°	1582	778	623
70°	1470	628	564
75°	1329	554	514
80°	1124	465	446
85°	785	312	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1892 cd/sqm



TEST NUMBER: P928674

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.1	3.0
10°-20°	780.0	8.2
20°-30°	1095.0	11.6
30°-40°	1193.7	12.6
40°-50°	1097.1	11.6
50°-60°	861.6	9.1
60°-70°	560.8	5.9
70°-80°	288.7	3.1
80°-90°	75.6	0.8
90°-100°	36.3	0.4
100°-110°	135.2	1.4
110°-120°	358.7	3.8
120°-130°	594.9	6.3
130°-140°	631.9	6.7
140°-150°	587.3	6.2
150°-160°	472.2	5.0
160°-170°	304.3	3.2
170°-180°	104.7	1.1
0°-30°	2159.1	22.8
0°-40°	3352.8	35.4
0°-60°	5311.5	56.1
0°-90°	6236.7	65.9
90°-120°	530.2	5.6
90°-150°	2344.3	24.8
90°-180°	3225.0	34.1
0°-180°	9462.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3032	3032	3032	3032	3032	
5°	3032	3018	2982	3007	2999	287
15°	2883	2853	2760	2708	2680	813
25°	2617	2529	2348	2236	2195	1204
35°	2255	2115	1874	1701	1640	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	946	724	477	384	376	938
75°	505	313	220	200	198	534
85°	118	60	52	52	52	135
90°	1	10	16	20	21	9
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	678	681	577
135°	801	814	821	829	827	619
145°	929	928	942	947	943	581
155°	1023	1016	1025	1030	1024	471
165°	1078	1073	1076	1081	1076	305
175°	1102	1097	1099	1104	1096	105
180°	1100	1100	1100	1100	1100	



TEST NUMBER: P928674

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3031.6	3031.6	3031.6	3031.6	3031.6
2.5°	3045.2	3031.6	3001.2	3028.9	3023.4
5°	3031.6	3017.9	2982.1	3006.8	2998.6
7.5°	3006.8	2990.5	2952.1	2962.9	2949.2
10°	2973.9	2954.7	2900.0	2891.5	2875.2
12.5°	2932.9	2908.2	2833.9	2817.6	2787.3
15°	2883.4	2853.2	2760.0	2707.8	2680.5
17.5°	2825.8	2781.8	2666.5	2606.3	2562.4
20°	2760.0	2705.0	2567.8	2499.4	2438.9
22.5°	2688.7	2625.5	2466.3	2373.1	2332.1
25°	2617.4	2529.4	2348.4	2236.0	2194.7
27.5°	2532.4	2438.9	2238.6	2109.7	2046.5
30°	2441.8	2337.3	2117.9	1978.2	1903.9
32.5°	2353.9	2227.6	2002.9	1838.2	1769.4
35°	2255.3	2115.3	1873.9	1701.1	1640.5
37.5°	2159.2	2008.2	1753.1	1563.7	1495.3
40°	2057.6	1893.2	1626.8	1432.1	1360.8
42.5°	1953.4	1777.9	1500.7	1297.6	1229.2
45°	1843.7	1659.7	1371.8	1176.8	1111.0
47.5°	1739.5	1544.8	1248.4	1053.4	993.2
50°	1624.2	1429.4	1127.6	938.1	880.8
52.5°	1511.6	1305.8	1012.4	831.3	779.2
55°	1401.8	1187.9	891.5	727.1	675.0
57.5°	1289.5	1070.0	784.8	631.1	587.1
60°	1174.2	954.7	672.1	532.4	488.4
62.5°	1061.9	842.4	576.0	444.5	422.7
65°	946.5	724.2	477.3	384.2	375.8
67.5°	836.8	614.4	384.2	337.3	329.2
70°	721.6	507.7	318.2	290.8	279.7
72.5°	611.8	408.6	266.0	244.2	238.7
75°	504.7	312.6	219.5	200.2	197.6
77.5°	397.9	222.1	172.9	161.9	156.3
80°	298.9	159.3	131.5	120.8	120.8
82.5°	208.4	107.1	90.5	85.0	85.0
85°	117.8	60.2	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.0	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	140.9	31.9	45.4	51.7	53.3
102.5°	193.4	191.9	46.9	55.7	58.1
105°	242.0	265.9	48.6	57.3	60.5
107.5°	298.5	318.4	50.2	58.9	62.1
110°	352.7	369.4	139.4	59.7	62.8



TEST NUMBER: P928674

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.7	417.9	404.4	61.3	63.7
115°	457.7	471.2	491.2	122.6	65.4
117.5°	504.7	520.6	534.2	420.3	211.7
120°	557.3	569.2	583.5	593.2	485.7
122.5°	601.8	614.6	630.6	635.3	636.1
125°	647.2	657.6	672.7	678.3	680.7
127.5°	688.6	699.8	711.7	719.7	720.5
130°	727.6	740.4	749.1	757.9	757.1
132.5°	767.4	777.8	786.6	793.7	793.0
135°	800.9	813.7	820.8	828.8	827.2
137.5°	835.9	845.4	853.5	861.4	859.0
140°	870.1	876.5	885.3	892.4	888.4
142.5°	898.9	904.4	914.8	921.0	917.1
145°	929.1	928.3	941.7	947.4	943.4
147.5°	955.3	952.9	966.4	970.4	967.3
150°	980.8	975.2	988.0	992.8	988.8
152.5°	1002.3	995.9	1007.8	1012.6	1007.1
155°	1023.0	1015.9	1025.4	1030.2	1023.8
157.5°	1039.7	1033.3	1040.6	1046.1	1039.7
160°	1054.0	1049.2	1054.0	1058.8	1053.2
162.5°	1066.8	1062.0	1066.0	1071.6	1064.4
165°	1077.9	1073.2	1075.6	1081.1	1075.6
167.5°	1086.7	1081.8	1084.4	1089.9	1082.7
170°	1093.9	1089.1	1090.6	1096.3	1089.1
172.5°	1098.6	1093.9	1095.5	1101.1	1093.9
175°	1102.5	1097.0	1098.6	1104.2	1096.3
177.5°	1104.2	1098.6	1099.4	1105.1	1097.9
180°	1100.2	1100.2	1100.2	1100.2	1100.2



TEST NUMBER: P928674
 CATALOG NUMBER: DFN2DIP-HX4F0-090D040US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.34	12.32	12.16	13.15	14.18	7.32	8.30	8.13	9.13	10.15
	3H	13.03	13.91	13.86	14.75	15.81	8.52	9.39	9.34	10.23	11.29
	4H	13.65	14.47	14.49	15.32	16.39	8.98	9.80	9.82	10.65	11.72
	6H	14.08	14.84	14.93	15.70	16.77	9.31	10.07	10.16	10.92	12.00
	8H	14.21	14.93	15.07	15.81	16.89	9.40	10.12	10.27	11.00	12.08
	12H	14.28	14.96	15.15	15.83	16.94	9.45	10.14	10.32	11.01	12.11
4H	2H	11.38	12.20	12.23	13.05	14.12	7.93	8.76	8.78	9.60	10.67
	3H	13.22	13.91	14.08	14.79	15.87	9.29	9.98	10.16	10.86	11.94
	4H	13.92	14.54	14.79	15.42	16.53	9.85	10.47	10.72	11.35	12.46
	6H	14.45	14.98	15.33	15.89	17.00	10.28	10.82	11.17	11.72	12.83
	8H	14.62	15.13	15.52	16.02	17.15	10.41	10.91	11.30	11.81	12.94
	12H	14.73	15.18	15.64	16.09	17.22	10.49	10.94	11.40	11.85	12.98
8H	4H	13.90	14.40	14.79	15.30	16.42	10.14	10.64	11.03	11.54	12.67
	6H	14.47	14.89	15.39	15.83	16.95	10.67	11.08	11.59	12.02	13.15
	8H	14.69	15.06	15.62	15.99	17.13	10.86	11.23	11.79	12.16	13.30
	12H	14.84	15.16	15.77	16.08	17.28	10.99	11.31	11.92	12.24	13.43
12H	4H	13.86	14.31	14.77	15.23	16.36	10.15	10.60	11.06	11.52	12.65
	6H	14.45	14.82	15.38	15.75	16.89	10.72	11.09	11.65	12.02	13.16
	8H	14.68	15.00	15.61	15.92	17.12	10.94	11.26	11.87	12.18	13.38