

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928732

Luminaire Tested: DFN2DIP-HX4F0-100D100US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928732
REPORT IS A COMBINATION OF REPORTS P900939 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D100US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16137.1 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 175.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928732

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928732

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2358	2358	2358
5°	2362	2325	2341
10°	2343	2294	2309
15°	2309	2257	2260
20°	2262	2204	2209
25°	2216	2142	2151
30°	2158	2084	2076
35°	2104	2015	1998
40°	2036	1946	1923
45°	1969	1876	1846
50°	1895	1803	1757
55°	1818	1719	1676
60°	1731	1619	1582
65°	1637	1516	1472
70°	1516	1389	1354
75°	1348	1238	1244
80°	1147	1045	1035
85°	833	713	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1969 cd/sqm

TEST NUMBER: P928732

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.5	1.8
10°-20°	839.8	5.2
20°-30°	1234.2	7.6
30°-40°	1433.4	8.9
40°-50°	1431.6	8.9
50°-60°	1248.3	7.7
60°-70°	922.8	5.7
70°-80°	522.1	3.2
80°-90°	142.7	0.9
90°-100°	90.7	0.6
100°-110°	338.1	2.1
110°-120°	896.7	5.6
120°-130°	1487.3	9.2
130°-140°	1579.8	9.8
140°-150°	1468.3	9.1
150°-160°	1180.4	7.3
160°-170°	760.6	4.7
170°-180°	261.8	1.6
0°-30°	2372.4	14.7
0°-40°	3805.8	23.6
0°-60°	6485.8	40.2
0°-90°	8073.4	50.0
90°-120°	1325.5	8.2
90°-150°	5860.8	36.3
90°-180°	8064.0	50.0
0°-180°	16137.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3171	3171	3171	3171	3171	
5°	3171	3159	3126	3150	3144	301
15°	3019	3001	2961	2973	2958	850
25°	2732	2708	2656	2662	2656	1257
35°	2357	2327	2278	2260	2244	1472
45°	1918	1897	1851	1818	1805	1480
55°	1452	1433	1397	1360	1345	1298
65°	979	961	930	903	888	968
75°	512	506	491	473	479	547
85°	125	122	119	110	107	139
90°	2	24	40	50	54	15
95°	129	64	78	88	86	153
105°	605	665	122	143	151	646
115°	1144	1178	1228	306	163	1127
125°	1618	1644	1682	1696	1702	1443
135°	2002	2034	2052	2072	2068	1547
145°	2323	2321	2354	2368	2358	1453
155°	2558	2540	2564	2575	2560	1178
165°	2695	2683	2689	2703	2689	761
175°	2756	2742	2746	2760	2741	262
180°	2750	2750	2750	2750	2750	

TEST NUMBER: P928732

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3171.2	3171.2	3171.2	3171.2	3171.2
2.5°	3189.7	3174.4	3140.8	3171.2	3165.4
5°	3171.2	3159.3	3125.6	3149.9	3144.0
7.5°	3149.9	3131.7	3098.1	3122.7	3116.6
10°	3116.6	3095.2	3058.6	3082.9	3073.9
12.5°	3070.6	3052.5	3015.9	3031.1	3025.0
15°	3018.8	3000.7	2960.9	2973.2	2958.0
17.5°	2954.8	2936.7	2896.8	2912.1	2896.8
20°	2884.5	2866.4	2823.7	2832.8	2820.8
22.5°	2814.7	2787.2	2747.4	2747.4	2741.3
25°	2732.2	2707.9	2656.2	2662.0	2656.2
27.5°	2640.6	2619.2	2579.8	2570.8	2555.5
30°	2549.4	2524.8	2479.1	2470.1	2457.8
32.5°	2451.7	2433.6	2384.7	2366.3	2354.0
35°	2357.2	2326.8	2277.9	2259.5	2244.3
37.5°	2250.5	2222.9	2174.1	2152.7	2137.5
40°	2140.8	2116.1	2067.3	2040.2	2027.9
42.5°	2034.0	2009.4	1960.9	1930.2	1912.1
45°	1918.2	1896.8	1850.9	1817.5	1805.3
47.5°	1805.3	1784.0	1735.1	1701.4	1683.3
50°	1686.2	1671.0	1628.3	1585.6	1570.4
52.5°	1570.4	1549.1	1509.5	1476.0	1454.6
55°	1451.7	1433.3	1396.7	1360.1	1344.9
57.5°	1332.6	1317.4	1277.6	1241.1	1228.8
60°	1213.5	1201.6	1158.8	1125.2	1116.1
62.5°	1097.7	1076.4	1046.0	1015.6	1003.3
65°	979.0	960.6	930.2	902.6	887.5
67.5°	857.1	841.5	814.3	793.0	780.7
70°	744.1	731.8	704.3	683.0	671.0
72.5°	628.3	616.0	600.8	579.5	570.3
75°	512.1	506.4	490.8	472.7	478.8
77.5°	408.6	396.3	390.1	381.1	372.0
80°	305.1	301.9	295.7	286.6	280.5
82.5°	207.4	207.4	204.5	192.2	192.2
85°	124.9	122.0	119.1	109.7	106.8
87.5°	55.0	48.8	42.7	33.7	30.4
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.4	79.6	113.4	129.3	133.3
102.5°	483.5	479.8	117.4	139.2	145.3
105°	605.1	664.8	121.5	143.2	151.3
107.5°	746.4	796.0	125.5	147.3	155.3
110°	881.7	923.4	348.3	149.4	157.1

TEST NUMBER: P928732

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.1	1044.8	1011.1	153.1	159.3
115°	1144.3	1178.2	1228.0	306.5	163.3
117.5°	1261.8	1301.6	1335.5	1050.8	529.4
120°	1393.2	1423.0	1458.9	1482.8	1214.1
122.5°	1504.6	1536.4	1576.4	1588.2	1590.3
125°	1618.0	1644.0	1681.8	1695.8	1701.6
127.5°	1721.5	1749.4	1779.4	1799.3	1801.2
130°	1819.1	1851.0	1872.8	1894.7	1892.8
132.5°	1918.6	1944.6	1966.4	1984.3	1982.4
135°	2002.3	2034.2	2051.9	2072.0	2068.0
137.5°	2089.7	2113.6	2133.7	2153.6	2147.6
140°	2175.2	2191.4	2213.1	2231.1	2221.1
142.5°	2247.1	2261.1	2286.8	2302.6	2292.8
145°	2322.8	2320.6	2354.5	2368.4	2358.4
147.5°	2388.2	2382.3	2416.1	2426.0	2418.3
150°	2452.0	2438.1	2470.0	2481.8	2471.9
152.5°	2505.6	2489.8	2519.7	2531.6	2517.7
155°	2557.5	2539.7	2563.6	2575.4	2559.6
157.5°	2599.3	2583.5	2601.4	2615.3	2599.3
160°	2635.2	2623.2	2635.2	2647.0	2633.1
162.5°	2666.8	2655.0	2665.0	2678.9	2661.0
165°	2694.7	2682.9	2688.8	2702.8	2688.8
167.5°	2716.7	2704.7	2710.9	2724.8	2706.8
170°	2734.7	2722.7	2726.7	2740.6	2722.7
172.5°	2746.5	2734.7	2738.7	2752.7	2734.7
175°	2756.4	2742.5	2746.5	2760.5	2740.6
177.5°	2760.5	2746.5	2748.7	2762.6	2744.6
180°	2750.5	2750.5	2750.5	2750.5	2750.5

TEST NUMBER: P928732

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.26	11.12	11.21	12.09	13.36	9.82	10.69	10.78	11.66	12.93
	3H	11.92	12.69	12.89	13.67	14.96	11.44	12.22	12.41	13.20	14.49
	4H	12.51	13.24	13.49	14.22	15.52	12.03	12.76	13.01	13.75	15.05
	6H	12.91	13.58	13.90	14.57	15.88	12.43	13.10	13.42	14.09	15.41
	8H	13.01	13.65	14.01	14.66	15.97	12.54	13.18	13.54	14.19	15.50
	12H	13.06	13.67	14.06	14.67	16.01	12.58	13.19	13.58	14.19	15.53
4H	2H	10.72	11.45	11.71	12.44	13.74	10.37	11.11	11.36	12.09	13.39
	3H	12.59	13.20	13.58	14.21	15.53	12.19	12.80	13.19	13.82	15.13
	4H	13.30	13.86	14.31	14.87	16.21	12.90	13.45	13.90	14.46	15.80
	6H	13.82	14.30	14.83	15.33	16.66	13.41	13.89	14.42	14.92	16.25
	8H	13.97	14.42	14.99	15.44	16.79	13.55	14.00	14.57	15.03	16.38
	12H	14.04	14.45	15.08	15.49	16.84	13.62	14.02	14.66	15.06	16.42
8H	4H	13.50	13.95	14.52	14.97	16.32	13.14	13.59	14.16	14.61	15.96
	6H	14.13	14.50	15.17	15.57	16.92	13.77	14.14	14.81	15.20	16.55
	8H	14.35	14.68	15.40	15.73	17.10	13.98	14.31	15.03	15.36	16.73
	12H	14.48	14.77	15.54	15.82	17.23	14.10	14.39	15.15	15.43	16.84
12H	4H	13.48	13.89	14.52	14.93	16.29	13.13	13.54	14.17	14.58	15.93
	6H	14.16	14.49	15.21	15.54	16.91	13.81	14.14	14.86	15.19	16.55
	8H	14.40	14.69	15.46	15.74	17.15	14.05	14.33	15.10	15.38	16.79

END OF REPORT