

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911122

Luminaire Tested: DFN2DIP-PN2F0-060D040US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911122
REPORT IS A COMBINATION OF REPORTS P899490 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-060D040US850-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9581.7 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 95.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911122

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911122

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5956	5956	5956
5°	5956	5849	5891
10°	5888	5722	5690
15°	5797	5520	5386
20°	5680	5248	5016
25°	5561	4945	4658
30°	5403	4635	4208
35°	5249	4304	3812
40°	5091	3961	3360
45°	4908	3584	2951
50°	4719	3204	2552
55°	4520	2800	2170
60°	4289	2380	1777
65°	4023	1954	1590
70°	3700	1556	1426
75°	3294	1347	1281
80°	2710	1094	1084
85°	1771	680	769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4908 cd/sqm

TEST NUMBER: P911122

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	2.7
10°-20°	707.6	7.4
20°-30°	993.4	10.4
30°-40°	1082.8	11.3
40°-50°	995.2	10.4
50°-60°	781.6	8.2
60°-70°	508.8	5.3
70°-80°	261.9	2.7
80°-90°	70.8	0.7
90°-100°	86.8	0.9
100°-110°	275.8	2.9
110°-120°	472.0	4.9
120°-130°	620.8	6.5
130°-140°	696.8	7.3
140°-150°	683.3	7.1
150°-160°	573.2	6.0
160°-170°	380.1	4.0
170°-180°	132.9	1.4
0°-30°	1958.7	20.4
0°-40°	3041.5	31.7
0°-60°	4818.4	50.3
0°-90°	5659.9	59.1
90°-120°	834.7	8.7
90°-150°	2835.6	29.6
90°-180°	3922.0	40.9
0°-180°	9581.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	1	15	42	39	40	9
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P911122

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P911122

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P911122

CATALOG NUMBER: DFN2DIP-PN2F0-060D040US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.04	14.95	14.92	15.84	16.98	10.00	10.91	10.89	11.81	12.95
	3H	15.70	16.51	16.59	17.42	18.58	11.18	12.00	12.08	12.90	14.07
	4H	16.30	17.07	17.21	17.98	19.15	11.62	12.39	12.53	13.31	14.48
	6H	16.71	17.41	17.63	18.33	19.52	11.93	12.64	12.86	13.56	14.75
	8H	16.83	17.50	17.76	18.44	19.62	12.02	12.69	12.95	13.63	14.81
	12H	16.88	17.52	17.82	18.45	19.66	12.06	12.70	12.99	13.63	14.84
4H	2H	14.06	14.83	14.98	15.74	16.92	10.60	11.37	11.51	12.28	13.45
	3H	15.87	16.51	16.80	17.46	18.64	11.94	12.57	12.86	13.52	14.71
	4H	16.55	17.13	17.49	18.07	19.29	12.47	13.05	13.41	13.99	15.21
	6H	17.05	17.55	18.00	18.52	19.73	12.88	13.38	13.83	14.34	15.56
	8H	17.22	17.69	18.17	18.64	19.87	13.00	13.47	13.95	14.42	15.65
	12H	17.30	17.73	18.28	18.70	19.93	13.06	13.48	14.03	14.45	15.69
8H	4H	16.52	16.99	17.47	17.95	19.17	12.75	13.21	13.70	14.17	15.40
	6H	17.07	17.45	18.05	18.45	19.68	13.24	13.63	14.22	14.63	15.86
	8H	17.27	17.61	18.26	18.60	19.85	13.42	13.76	14.41	14.75	16.00
	12H	17.40	17.70	18.39	18.68	19.97	13.53	13.83	14.52	14.81	16.11
12H	4H	16.48	16.90	17.45	17.87	19.10	12.75	13.17	13.72	14.15	15.38
	6H	17.04	17.38	18.03	18.37	19.62	13.29	13.63	14.27	14.62	15.86
	8H	17.25	17.55	18.24	18.53	19.83	13.49	13.79	14.48	14.77	16.06

END OF REPORT