

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928760

Luminaire Tested: DFN2DIP-HX4F0-110D080US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928760
REPORT IS A COMBINATION OF REPORTS P900905 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D080US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15330.2 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 170.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928760

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928760

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	54	50	51	47	44	44	41	38
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	50	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2594	2594	2594
5°	2598	2558	2575
10°	2577	2524	2540
15°	2540	2482	2486
20°	2489	2425	2430
25°	2438	2356	2366
30°	2374	2292	2284
35°	2314	2217	2197
40°	2240	2140	2115
45°	2166	2064	2031
50°	2085	1984	1933
55°	2000	1891	1843
60°	1904	1781	1741
65°	1800	1667	1619
70°	1667	1528	1489
75°	1483	1362	1369
80°	1262	1150	1139
85°	916	784	757

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2166 cd/sqm

TEST NUMBER: P928760

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.3	2.1
10°-20°	923.8	6.0
20°-30°	1357.6	8.9
30°-40°	1576.7	10.3
40°-50°	1574.8	10.3
50°-60°	1373.2	9.0
60°-70°	1015.1	6.6
70°-80°	574.3	3.7
80°-90°	155.4	1.0
90°-100°	72.6	0.5
100°-110°	270.5	1.8
110°-120°	717.4	4.7
120°-130°	1189.8	7.8
130°-140°	1263.8	8.2
140°-150°	1174.6	7.7
150°-160°	944.4	6.2
160°-170°	608.5	4.0
170°-180°	209.4	1.4
0°-30°	2609.7	17.0
0°-40°	4186.4	27.3
0°-60°	7134.4	46.5
0°-90°	8879.2	57.9
90°-120°	1060.4	6.9
90°-150°	4688.7	30.6
90°-180°	6451.0	42.1
0°-180°	15330.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3488	3488	3488	3488	3488	
5°	3488	3475	3438	3465	3458	331
15°	3321	3301	3257	3270	3254	935
25°	3005	2979	2922	2928	2922	1383
35°	2593	2560	2506	2485	2469	1619
45°	2110	2086	2036	1999	1986	1628
55°	1597	1576	1536	1496	1479	1428
65°	1077	1057	1023	993	976	1065
75°	563	557	540	520	527	601
85°	137	134	131	121	117	153
90°	2	19	32	40	43	14
95°	103	51	62	70	68	122
105°	484	532	97	115	121	517
115°	916	942	982	245	131	901
125°	1294	1315	1345	1357	1361	1154
135°	1602	1627	1642	1658	1654	1237
145°	1858	1856	1884	1895	1887	1162
155°	2046	2032	2051	2060	2048	943
165°	2156	2146	2151	2162	2151	609
175°	2205	2194	2197	2208	2192	210
180°	2200	2200	2200	2200	2200	

TEST NUMBER: P928760

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3488.4	3488.4	3488.4	3488.4	3488.4
2.5°	3508.6	3491.9	3454.9	3488.4	3481.9
5°	3488.4	3475.2	3438.2	3464.8	3458.5
7.5°	3464.8	3444.9	3407.9	3435.0	3428.2
10°	3428.2	3404.7	3364.5	3391.1	3381.2
12.5°	3377.7	3357.7	3317.5	3334.2	3327.5
15°	3320.7	3300.8	3257.0	3270.5	3253.8
17.5°	3250.2	3230.3	3186.6	3203.3	3186.6
20°	3173.0	3153.1	3106.1	3116.1	3102.9
22.5°	3096.2	3065.9	3022.1	3022.1	3015.3
25°	3005.4	2978.7	2921.8	2928.2	2921.8
27.5°	2904.7	2881.2	2837.7	2827.8	2811.1
30°	2804.3	2777.3	2727.1	2717.1	2703.6
32.5°	2696.8	2676.9	2623.2	2602.9	2589.3
35°	2592.9	2559.5	2505.7	2485.4	2468.7
37.5°	2475.5	2445.2	2391.5	2368.0	2351.3
40°	2354.9	2327.8	2274.1	2244.2	2230.7
42.5°	2237.4	2210.4	2157.0	2123.2	2103.3
45°	2110.0	2086.5	2036.0	1999.4	1985.8
47.5°	1985.8	1962.4	1908.6	1871.6	1851.6
50°	1854.9	1838.2	1791.1	1744.2	1727.5
52.5°	1727.5	1703.9	1660.6	1623.5	1600.0
55°	1596.8	1576.5	1536.4	1496.1	1479.4
57.5°	1465.9	1449.2	1405.4	1365.1	1351.6
60°	1334.9	1321.8	1274.7	1237.7	1227.8
62.5°	1207.5	1184.0	1150.5	1117.1	1103.6
65°	1076.9	1056.6	1023.2	992.9	976.2
67.5°	942.7	925.7	895.8	872.3	858.8
70°	818.5	805.0	774.7	751.3	738.1
72.5°	691.1	677.6	660.9	637.4	627.4
75°	563.3	557.0	539.9	520.0	526.7
77.5°	449.5	435.9	429.2	419.2	409.3
80°	335.6	332.0	325.3	315.3	308.6
82.5°	228.1	228.1	224.9	211.4	211.4
85°	137.4	134.1	131.0	120.6	117.4
87.5°	60.5	53.7	46.9	37.0	33.4
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.4	50.9	62.0	70.2	68.5
97.5°	186.2	55.7	81.1	86.1	87.5
100°	281.9	63.7	90.8	103.4	106.6
102.5°	386.9	383.8	94.0	111.3	116.3
105°	484.0	531.9	97.1	114.6	121.0
107.5°	597.1	636.8	100.4	117.8	124.2
110°	705.5	738.7	278.7	119.5	125.8

TEST NUMBER: P928760

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.3	835.9	808.9	122.5	127.5
115°	915.5	942.5	982.4	245.2	130.6
117.5°	1009.5	1041.2	1068.5	840.6	423.6
120°	1114.6	1138.4	1167.2	1186.2	971.2
122.5°	1203.6	1229.2	1261.1	1270.6	1272.3
125°	1294.4	1315.2	1345.4	1356.6	1361.3
127.5°	1377.2	1399.5	1423.6	1439.4	1440.9
130°	1455.3	1480.8	1498.2	1515.8	1514.3
132.5°	1534.9	1555.7	1573.1	1587.5	1585.9
135°	1601.8	1627.3	1641.5	1657.6	1654.4
137.5°	1671.8	1690.9	1706.9	1722.8	1718.1
140°	1740.2	1753.1	1770.5	1784.8	1776.9
142.5°	1797.7	1808.8	1829.4	1842.1	1834.2
145°	1858.2	1856.5	1883.5	1894.7	1886.7
147.5°	1910.6	1905.9	1932.9	1940.8	1934.6
150°	1961.6	1950.5	1976.0	1985.4	1977.5
152.5°	2004.6	1991.9	2015.7	2025.4	2014.2
155°	2046.0	2031.8	2050.9	2060.3	2047.7
157.5°	2079.4	2066.8	2081.1	2092.3	2079.4
160°	2108.2	2098.5	2108.2	2117.6	2106.4
162.5°	2133.5	2124.1	2132.0	2143.1	2128.8
165°	2155.8	2146.4	2151.1	2162.2	2151.1
167.5°	2173.4	2163.7	2168.6	2179.8	2165.5
170°	2187.8	2178.1	2181.3	2192.5	2178.1
172.5°	2197.2	2187.8	2191.0	2202.1	2187.8
175°	2205.1	2194.0	2197.2	2208.3	2192.5
177.5°	2208.3	2197.2	2198.9	2210.0	2195.7
180°	2200.4	2200.4	2200.4	2200.4	2200.4

TEST NUMBER: P928760

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.29	12.22	12.17	13.13	14.28	10.85	11.79	11.74	12.70	13.85
	3H	12.95	13.79	13.85	14.71	15.89	12.48	13.32	13.38	14.24	15.41
	4H	13.54	14.34	14.46	15.26	16.45	13.07	13.87	13.98	14.79	15.97
	6H	13.95	14.68	14.87	15.61	16.81	13.47	14.21	14.40	15.13	16.33
	8H	14.06	14.75	14.99	15.70	16.90	13.58	14.28	14.51	15.22	16.42
	12H	14.11	14.77	15.05	15.71	16.94	13.63	14.29	14.56	15.23	16.45
4H	2H	11.76	12.55	12.68	13.47	14.66	11.41	12.21	12.33	13.13	14.32
	3H	13.63	14.29	14.56	15.25	16.45	13.24	13.90	14.17	14.85	16.06
	4H	14.35	14.95	15.29	15.90	17.13	13.94	14.55	14.88	15.50	16.72
	6H	14.87	15.39	15.82	16.36	17.59	14.46	14.98	15.41	15.95	17.18
	8H	15.02	15.51	15.98	16.47	17.72	14.61	15.10	15.56	16.06	17.30
	12H	15.10	15.54	16.07	16.52	17.77	14.68	15.12	15.65	16.10	17.35
8H	4H	14.55	15.04	15.51	16.01	17.25	14.19	14.68	15.15	15.64	16.89
	6H	15.19	15.59	16.17	16.60	17.84	14.82	15.23	15.81	16.24	17.48
	8H	15.41	15.77	16.40	16.76	18.02	15.04	15.40	16.03	16.39	17.65
	12H	15.55	15.86	16.54	16.85	18.15	15.16	15.48	16.15	16.46	17.77
12H	4H	14.54	14.98	15.52	15.96	17.21	14.19	14.63	15.16	15.61	16.86
	6H	15.22	15.58	16.21	16.57	17.83	14.87	15.22	15.86	16.22	17.48
	8H	15.47	15.78	16.46	16.77	18.07	15.11	15.42	16.10	16.41	17.72