

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913777

Luminaire Tested: DFN2DIP-PN2F0-020D060US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913777
REPORT IS A COMBINATION OF REPORTS P901021 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D060US927-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6274.1 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913777

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913777

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1335	1335	1335
5°	1335	1314	1324
10°	1322	1293	1304
15°	1301	1269	1274
20°	1272	1237	1243
25°	1244	1198	1208
30°	1209	1163	1164
35°	1176	1121	1118
40°	1135	1079	1073
45°	1094	1036	1028
50°	1050	992	975
55°	1003	940	926
60°	950	879	871
65°	892	816	805
70°	818	738	734
75°	716	645	665
80°	593	527	539
85°	401	333	339

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1474 cd/sqm

TEST NUMBER: P913777

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	0.9
10°-20°	163.3	2.6
20°-30°	239.9	3.8
30°-40°	278.7	4.4
40°-50°	278.3	4.4
50°-60°	242.7	3.9
60°-70°	179.4	2.9
70°-80°	101.5	1.6
80°-90°	29.6	0.5
90°-100°	52.9	0.8
100°-110°	197.2	3.1
110°-120°	523.0	8.3
120°-130°	867.4	13.8
130°-140°	921.3	14.7
140°-150°	856.3	13.6
150°-160°	688.4	11.0
160°-170°	443.6	7.1
170°-180°	152.7	2.4
0°-30°	461.2	7.4
0°-40°	739.9	11.8
0°-60°	1260.8	20.1
0°-90°	1571.4	25.0
90°-120°	773.0	12.3
90°-150°	3418.0	54.5
90°-180°	4703.0	75.0
0°-180°	6274.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	616	616	616	616	616	
5°	616	614	608	612	611	59
15°	587	583	576	578	575	165
25°	531	526	516	518	516	244
35°	458	452	443	439	436	286
45°	373	369	360	353	351	288
55°	282	279	272	264	261	252
65°	190	187	181	176	172	188
75°	100	98	95	92	93	106
85°	24	24	23	21	21	27
90°	1	14	23	29	31	6
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P913777

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	616.5	616.5	616.5	616.5	616.5
2.5°	620.0	617.1	610.5	616.5	615.4
5°	616.5	614.2	607.6	612.4	611.2
7.5°	612.4	608.8	602.3	607.0	605.9
10°	605.9	601.7	594.6	599.3	597.5
12.5°	596.9	593.4	586.3	589.2	588.0
15°	586.8	583.4	575.6	578.0	575.0
17.5°	574.4	570.9	563.2	566.1	563.2
20°	560.8	557.2	548.9	550.7	548.3
22.5°	547.2	541.9	534.1	534.1	532.9
25°	531.2	526.4	516.3	517.5	516.3
27.5°	513.3	509.2	501.5	499.8	496.8
30°	495.6	490.8	482.0	480.2	477.8
32.5°	476.6	473.1	463.6	460.0	457.6
35°	458.3	452.3	442.8	439.3	436.3
37.5°	437.5	432.1	422.6	418.5	415.5
40°	416.1	411.4	401.9	396.6	394.2
42.5°	395.4	390.6	381.2	375.3	371.7
45°	372.9	368.8	359.8	353.3	350.9
47.5°	350.9	346.8	337.3	330.7	327.3
50°	327.8	324.9	316.6	308.2	305.3
52.5°	305.3	301.1	293.4	286.9	282.8
55°	282.2	278.6	271.5	264.4	261.4
57.5°	259.0	256.1	248.3	241.3	238.8
60°	235.9	233.6	225.3	218.7	217.0
62.5°	213.4	209.2	203.4	197.4	195.0
65°	190.3	186.7	180.9	175.5	172.5
67.5°	166.6	163.6	158.3	154.2	151.8
70°	144.7	142.3	136.9	132.8	130.5
72.5°	122.2	119.8	116.8	112.6	110.9
75°	99.6	98.5	95.4	91.9	93.1
77.5°	79.5	77.1	75.8	74.1	72.3
80°	59.3	58.7	57.5	55.7	54.5
82.5°	40.3	40.3	39.8	37.4	37.4
85°	24.2	23.7	23.1	21.3	20.8
87.5°	10.7	9.5	8.3	6.6	5.9
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7

TEST NUMBER: P913777

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1

TEST NUMBER: P913777

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.22	5.89	6.36	7.03	8.61	4.78	5.46	5.93	6.59	8.18
	3H	6.84	7.45	8.00	8.59	10.19	6.36	6.97	7.52	8.11	9.71
	4H	7.41	7.98	8.57	9.13	10.73	6.93	7.50	8.09	8.64	10.25
	6H	7.78	8.31	8.95	9.46	11.08	7.30	7.83	8.47	8.97	10.59
	8H	7.87	8.38	9.05	9.54	11.15	7.39	7.89	8.56	9.05	10.66
	12H	7.91	8.39	9.09	9.54	11.17	7.42	7.89	8.59	9.05	10.68
4H	2H	5.65	6.22	6.82	7.36	8.97	5.30	5.87	6.47	7.01	8.62
	3H	7.47	7.95	8.65	9.12	10.74	7.07	7.55	8.25	8.72	10.34
	4H	8.16	8.60	9.34	9.76	11.40	7.75	8.19	8.92	9.35	10.98
	6H	8.65	9.02	9.83	10.20	11.83	8.23	8.60	9.41	9.78	11.41
	8H	8.78	9.13	9.96	10.31	11.95	8.36	8.71	9.54	9.88	11.53
	12H	8.84	9.16	10.03	10.34	11.99	8.40	8.72	9.60	9.90	11.55
8H	4H	8.33	8.68	9.51	9.85	11.50	7.96	8.32	9.14	9.49	11.13
	6H	8.93	9.22	10.13	10.43	12.08	8.56	8.85	9.76	10.06	11.70
	8H	9.14	9.39	10.34	10.58	12.24	8.76	9.01	9.96	10.20	11.86
	12H	9.24	9.47	10.45	10.66	12.35	8.85	9.07	10.06	10.26	11.95
12H	4H	8.31	8.63	9.50	9.81	11.46	7.95	8.26	9.14	9.45	11.10
	6H	8.95	9.21	10.16	10.40	12.06	8.59	8.84	9.80	10.03	11.70
	8H	9.17	9.39	10.38	10.58	12.28	8.80	9.02	10.01	10.21	11.91

END OF REPORT