

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913779

Luminaire Tested: DFN2DIP-PN2F0-020D060US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913779
REPORT IS A COMBINATION OF REPORTS P901022 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D060US927-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6052.2 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913779

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913779

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26
2	84	77	71	66	74	68	64	60	52	49	47	38	36	34	24	23	22
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1418	1418	1418
5°	1418	1393	1403
10°	1402	1362	1355
15°	1380	1314	1282
20°	1352	1250	1194
25°	1324	1177	1109
30°	1286	1104	1002
35°	1250	1025	908
40°	1212	943	800
45°	1169	854	703
50°	1124	763	608
55°	1076	667	517
60°	1022	567	423
65°	958	465	379
70°	881	370	340
75°	784	321	305
80°	646	260	258
85°	421	161	182

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1474 cd/sqm

TEST NUMBER: P913779

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	1.0
10°-20°	168.5	2.8
20°-30°	236.5	3.9
30°-40°	257.8	4.3
40°-50°	237.0	3.9
50°-60°	186.1	3.1
60°-70°	121.2	2.0
70°-80°	62.3	1.0
80°-90°	18.7	0.3
90°-100°	52.9	0.9
100°-110°	197.2	3.3
110°-120°	523.0	8.6
120°-130°	867.4	14.3
130°-140°	921.3	15.2
140°-150°	856.3	14.1
150°-160°	688.4	11.4
160°-170°	443.6	7.3
170°-180°	152.7	2.5
0°-30°	466.4	7.7
0°-40°	724.2	12.0
0°-60°	1147.3	19.0
0°-90°	1349.5	22.3
90°-120°	773.0	12.8
90°-150°	3418.0	56.5
90°-180°	4703.0	77.7
0°-180°	6052.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	650	648	62
15°	623	616	596	585	579	176
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	308
55°	303	257	193	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	29
90°	1	14	23	29	31	6
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P913779

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.8	654.8	654.8	654.8	654.8
2.5°	657.7	654.8	648.2	654.3	653.1
5°	654.8	651.9	644.1	649.5	647.7
7.5°	649.5	645.9	637.6	640.0	637.0
10°	642.4	638.2	626.4	624.6	621.1
12.5°	633.5	628.1	612.1	608.6	602.1
15°	622.8	616.2	596.1	584.9	579.0
17.5°	610.4	600.9	576.0	562.9	553.5
20°	596.1	584.2	554.7	539.9	526.8
22.5°	580.7	567.1	532.7	512.6	503.7
25°	565.4	546.4	507.2	483.0	474.0
27.5°	547.0	526.8	483.5	455.7	442.0
30°	527.4	504.9	457.5	427.3	411.2
32.5°	508.4	481.2	432.6	397.0	382.2
35°	487.1	456.9	404.8	367.4	354.3
37.5°	466.4	433.7	378.7	337.8	323.0
40°	444.4	408.9	351.4	309.3	293.9
42.5°	421.9	384.0	324.2	280.3	265.5
45°	398.2	358.5	296.4	254.2	240.0
47.5°	375.7	333.7	269.7	227.5	214.5
50°	350.9	308.8	243.6	202.6	190.3
52.5°	326.5	282.0	218.6	179.6	168.3
55°	302.8	256.6	192.6	157.1	145.8
57.5°	278.5	231.1	169.5	136.3	126.8
60°	253.7	206.2	145.2	115.0	105.5
62.5°	229.3	182.0	124.5	96.0	91.3
65°	204.5	156.5	103.1	83.0	81.2
67.5°	180.8	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.8	51.6
75°	109.0	67.5	47.4	43.3	42.7
77.5°	86.0	48.0	37.3	34.9	33.7
80°	64.6	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7

TEST NUMBER: P913779

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1

TEST NUMBER: P913779

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.82	5.46	5.99	6.61	8.23	0.79	1.43	1.95	2.58	4.20
	3H	6.46	7.04	7.64	8.20	9.83	1.94	2.52	3.12	3.68	5.31
	4H	7.05	7.60	8.23	8.75	10.39	2.37	2.92	3.56	4.08	5.72
	6H	7.44	7.95	8.63	9.11	10.76	2.67	3.17	3.86	4.33	5.98
	8H	7.56	8.03	8.75	9.21	10.85	2.75	3.23	3.94	4.40	6.04
	12H	7.60	8.06	8.80	9.23	10.89	2.78	3.23	3.97	4.40	6.06
4H	2H	4.81	5.36	6.00	6.52	8.15	1.35	1.90	2.54	3.05	4.69
	3H	6.60	7.05	7.79	8.24	9.89	2.66	3.12	3.86	4.30	5.95
	4H	7.27	7.69	8.46	8.86	10.53	3.19	3.61	4.38	4.78	6.45
	6H	7.75	8.11	8.95	9.31	10.96	3.58	3.94	4.78	5.13	6.79
	8H	7.91	8.25	9.11	9.43	11.11	3.69	4.03	4.89	5.21	6.89
	12H	7.99	8.29	9.20	9.49	11.17	3.74	4.05	4.95	5.24	6.92
8H	4H	7.22	7.55	8.41	8.74	10.41	3.44	3.78	4.64	4.96	6.64
	6H	7.75	8.03	8.97	9.26	10.93	3.93	4.21	5.15	5.43	7.10
	8H	7.96	8.20	9.18	9.40	11.09	4.11	4.35	5.33	5.55	7.24
	12H	8.07	8.28	9.30	9.48	11.21	4.20	4.42	5.43	5.62	7.34
12H	4H	7.16	7.46	8.37	8.66	10.34	3.43	3.74	4.65	4.93	6.61
	6H	7.73	7.97	8.95	9.17	10.86	3.97	4.21	5.19	5.42	7.11
	8H	7.92	8.14	9.15	9.34	11.06	4.16	4.37	5.39	5.57	7.30

END OF REPORT