

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913785

Luminaire Tested: DFN2DIP-PN2F0-030D030US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913785
REPORT IS A COMBINATION OF REPORTS P900993 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D030US927-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4705.6 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913785

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913785

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	47	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	40	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	34	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	29	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	26	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	23	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	20	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	18	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2003	2003	2003
5°	2003	1971	1985
10°	1983	1940	1956
15°	1951	1904	1910
20°	1908	1855	1865
25°	1866	1798	1812
30°	1813	1744	1746
35°	1763	1681	1676
40°	1702	1618	1610
45°	1642	1554	1541
50°	1575	1487	1463
55°	1504	1410	1390
60°	1425	1319	1306
65°	1338	1223	1207
70°	1227	1108	1100
75°	1074	968	998
80°	889	791	809
85°	603	500	507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1642 cd/sqm

TEST NUMBER: P913785

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.8
10°-20°	244.9	5.2
20°-30°	359.9	7.6
30°-40°	418.0	8.9
40°-50°	417.5	8.9
50°-60°	364.0	7.7
60°-70°	269.1	5.7
70°-80°	152.3	3.2
80°-90°	41.6	0.9
90°-100°	26.5	0.6
100°-110°	98.6	2.1
110°-120°	261.5	5.6
120°-130°	433.7	9.2
130°-140°	460.7	9.8
140°-150°	428.1	9.1
150°-160°	344.2	7.3
160°-170°	221.8	4.7
170°-180°	76.3	1.6
0°-30°	691.8	14.7
0°-40°	1109.8	23.6
0°-60°	1891.3	40.2
0°-90°	2354.2	50.0
90°-120°	386.5	8.2
90°-150°	1709.0	36.3
90°-180°	2351.0	50.0
0°-180°	4705.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	925	921	911	918	917	88
15°	880	875	863	867	862	248
25°	797	790	774	776	774	367
35°	687	678	664	659	654	429
45°	559	553	540	530	526	432
55°	423	418	407	397	392	378
65°	286	280	271	263	259	282
75°	149	148	143	138	140	159
85°	36	36	35	32	31	41
90°	1	7	12	15	16	4
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P913785

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	924.7	924.7	924.7	924.7	924.7
2.5°	930.1	925.7	915.8	924.7	923.0
5°	924.7	921.2	911.4	918.5	916.8
7.5°	918.5	913.2	903.4	910.6	908.8
10°	908.8	902.5	891.9	899.0	896.4
12.5°	895.4	890.1	879.5	883.8	882.1
15°	880.3	875.0	863.4	867.0	862.5
17.5°	861.6	856.3	844.7	849.1	844.7
20°	841.1	835.8	823.4	826.0	822.5
22.5°	820.8	812.8	801.1	801.1	799.3
25°	796.7	789.6	774.5	776.3	774.5
27.5°	770.0	763.7	752.3	749.6	745.2
30°	743.4	736.3	722.9	720.3	716.7
32.5°	714.9	709.6	695.4	690.0	686.4
35°	687.4	678.5	664.2	658.9	654.4
37.5°	656.2	648.2	634.0	627.7	623.3
40°	624.2	617.1	602.8	594.9	591.4
42.5°	593.1	586.0	571.8	562.8	557.5
45°	559.4	553.1	539.7	530.0	526.4
47.5°	526.4	520.2	506.0	496.1	490.8
50°	491.7	487.3	474.8	462.4	458.0
52.5°	458.0	451.7	440.2	430.4	424.1
55°	423.3	418.0	407.3	396.6	392.2
57.5°	388.6	384.1	372.6	361.9	358.3
60°	353.9	350.4	337.9	328.1	325.5
62.5°	320.1	313.9	305.0	296.1	292.6
65°	285.5	280.1	271.2	263.2	258.8
67.5°	249.9	245.4	237.4	231.2	227.7
70°	217.0	213.4	205.4	199.2	195.7
72.5°	183.2	179.6	175.2	169.0	166.4
75°	149.3	147.7	143.1	137.8	139.7
77.5°	119.1	115.6	113.8	111.1	108.5
80°	89.0	88.0	86.2	83.6	81.8
82.5°	60.4	60.4	59.7	56.0	56.0
85°	36.4	35.6	34.7	32.0	31.1
87.5°	16.0	14.3	12.4	9.8	8.9
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9



TEST NUMBER: P913785

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P913785

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.57	10.43	10.53	11.40	12.68	9.13	10.00	10.09	10.97	12.24
	3H	11.21	11.98	12.18	12.97	14.26	10.73	11.50	11.70	12.49	13.78
	4H	11.79	12.52	12.77	13.50	14.80	11.30	12.04	12.29	13.02	14.32
	6H	12.17	12.84	13.16	13.83	15.15	11.68	12.36	12.68	13.35	14.66
	8H	12.27	12.91	13.26	13.92	15.23	11.78	12.42	12.78	13.43	14.74
	12H	12.31	12.92	13.31	13.92	15.25	11.82	12.43	12.82	13.43	14.76
4H	2H	10.02	10.75	11.01	11.74	13.04	9.67	10.40	10.66	11.39	12.69
	3H	11.86	12.48	12.86	13.49	14.80	11.47	12.08	12.46	13.09	14.41
	4H	12.56	13.12	13.57	14.13	15.47	12.15	12.71	13.15	13.72	15.05
	6H	13.06	13.54	14.08	14.57	15.91	12.64	13.12	13.66	14.15	15.49
	8H	13.20	13.65	14.22	14.67	16.02	12.78	13.22	13.79	14.25	15.60
	12H	13.26	13.67	14.30	14.71	16.06	12.83	13.23	13.87	14.27	15.63
8H	4H	12.75	13.20	13.77	14.22	15.57	12.38	12.83	13.40	13.85	15.20
	6H	13.36	13.73	14.40	14.79	16.14	12.98	13.35	14.02	14.42	15.77
	8H	13.56	13.89	14.61	14.94	16.31	13.18	13.51	14.23	14.56	15.93
	12H	13.68	13.97	14.73	15.01	16.42	13.28	13.57	14.34	14.62	16.03
12H	4H	12.73	13.14	13.77	14.18	15.53	12.37	12.78	13.41	13.82	15.17
	6H	13.38	13.71	14.43	14.76	16.13	13.02	13.35	14.07	14.40	15.76
	8H	13.61	13.89	14.66	14.94	16.35	13.24	13.53	14.29	14.57	15.98