

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913787

Luminaire Tested: DFN2DIP-PN2F0-030D030US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913787
REPORT IS A COMBINATION OF REPORTS P900994 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D030US927-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4372.8 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913787

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913787

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2127	2127	2127
5°	2127	2089	2104
10°	2103	2044	2032
15°	2070	1972	1924
20°	2029	1874	1791
25°	1986	1766	1664
30°	1930	1655	1503
35°	1875	1537	1362
40°	1818	1415	1200
45°	1753	1280	1054
50°	1685	1145	911
55°	1614	1000	775
60°	1532	850	635
65°	1437	697	568
70°	1322	556	509
75°	1176	481	457
80°	968	391	387
85°	633	243	275

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1753 cd/sqm

TEST NUMBER: P913787

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.1	2.1
10°-20°	252.7	5.8
20°-30°	354.8	8.1
30°-40°	386.8	8.8
40°-50°	355.5	8.1
50°-60°	279.2	6.4
60°-70°	181.7	4.2
70°-80°	93.5	2.1
80°-90°	25.3	0.6
90°-100°	26.5	0.6
100°-110°	98.6	2.3
110°-120°	261.5	6.0
120°-130°	433.7	9.9
130°-140°	460.7	10.5
140°-150°	428.1	9.8
150°-160°	344.2	7.9
160°-170°	221.8	5.1
170°-180°	76.3	1.7
0°-30°	699.6	16.0
0°-40°	1086.3	24.8
0°-60°	1720.9	39.4
0°-90°	2021.5	46.2
90°-120°	386.5	8.8
90°-150°	1709.0	39.1
90°-180°	2351.0	53.8
0°-180°	4372.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	972	93
15°	934	924	894	877	868	263
25°	848	820	761	724	711	390
35°	731	685	607	551	532	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	44
90°	1	7	12	15	16	4
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P913787

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.2	982.2	982.2	982.2	982.2
2.5°	986.7	982.2	972.4	981.4	979.6
5°	982.2	977.8	966.2	974.2	971.5
7.5°	974.2	968.9	956.5	960.0	955.5
10°	963.5	957.4	939.6	936.8	931.6
12.5°	950.2	942.2	918.2	912.9	903.1
15°	934.2	924.4	894.2	877.3	868.5
17.5°	915.5	901.3	864.0	844.5	830.2
20°	894.2	876.4	831.9	809.8	790.2
22.5°	871.2	850.6	799.1	768.9	755.6
25°	848.0	819.5	760.9	724.4	711.1
27.5°	820.5	790.2	725.3	683.6	663.1
30°	791.2	757.3	686.2	641.0	616.9
32.5°	762.6	721.8	649.0	595.6	573.3
35°	730.7	685.3	607.1	551.1	531.6
37.5°	699.6	650.6	568.0	506.6	484.5
40°	666.7	613.4	527.1	464.0	440.9
42.5°	632.9	576.1	486.2	420.4	398.2
45°	597.4	537.7	444.5	381.3	360.0
47.5°	563.6	500.5	404.5	341.3	321.8
50°	526.2	463.1	365.4	304.0	285.3
52.5°	489.7	423.1	328.0	269.3	252.5
55°	454.2	384.8	288.8	235.6	218.7
57.5°	417.8	346.7	254.3	204.5	190.2
60°	380.4	309.3	217.8	172.5	158.3
62.5°	344.0	272.9	186.6	144.0	137.0
65°	306.7	234.6	154.6	124.5	121.8
67.5°	271.2	199.1	124.5	109.3	106.6
70°	233.8	164.5	103.1	94.2	90.6
72.5°	198.2	132.4	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.1	7.1	6.3	6.3
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9



TEST NUMBER: P913787

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P913787

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.29	10.09	10.29	11.09	12.42	5.26	6.06	6.25	7.06	8.39
	3H	10.95	11.66	11.95	12.67	14.02	6.43	7.14	7.43	8.15	9.50
	4H	11.54	12.22	12.56	13.23	14.59	6.86	7.54	7.88	8.56	9.91
	6H	11.94	12.56	12.97	13.58	14.95	7.17	7.79	8.20	8.81	10.18
	8H	12.06	12.65	13.09	13.69	15.05	7.25	7.84	8.28	8.88	10.24
	12H	12.11	12.67	13.15	13.70	15.09	7.29	7.85	8.32	8.88	10.26
4H	2H	9.30	9.98	10.33	10.99	12.35	5.84	6.52	6.86	7.53	8.89
	3H	11.10	11.67	12.14	12.71	14.08	7.17	7.73	8.20	8.77	10.14
	4H	11.78	12.29	12.82	13.33	14.72	7.70	8.21	8.74	9.25	10.64
	6H	12.27	12.71	13.32	13.77	15.16	8.10	8.54	9.15	9.60	10.98
	8H	12.44	12.85	13.49	13.90	15.30	8.22	8.63	9.27	9.68	11.08
	12H	12.52	12.89	13.59	13.96	15.36	8.27	8.64	9.34	9.71	11.12
8H	4H	11.74	12.15	12.79	13.20	14.61	7.96	8.38	9.01	9.43	10.83
	6H	12.28	12.62	13.36	13.72	15.12	8.46	8.80	9.53	9.89	11.29
	8H	12.49	12.78	13.57	13.86	15.28	8.64	8.93	9.72	10.01	11.43
	12H	12.61	12.87	13.69	13.94	15.40	8.74	9.00	9.82	10.07	11.54
12H	4H	11.69	12.06	12.76	13.13	14.53	7.96	8.34	9.03	9.40	10.81
	6H	12.26	12.56	13.34	13.63	15.05	8.50	8.80	9.58	9.88	11.30
	8H	12.46	12.72	13.55	13.80	15.26	8.70	8.96	9.78	10.03	11.49

END OF REPORT